

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P592673

Luminaire Tested: **HCC4W20D010MW-HM40525850-41WWWB**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P592673
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-18)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W20D010MW-HM40525850-41WWWB
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 5000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2108.2 lumens
Efficiency: N/A
Efficacy: 105.4 lumens/watt
Spacing Criteria (0/90/45): 1.13 / 1.07 / 1.15
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 20
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P592673
CATALOG NUMBER: HCC4W20D010MW-HM40525850-41WWWB

Luminous Intensity Polar Plot





TEST NUMBER: P592673

CATALOG NUMBER: HCC4W20D010MW-HM40525850-41WWWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87								
2	102	95	89	84	99	93	87	83	89	85	81	86	82	79	83	80	77	75								
3	94	85	77	72	92	83	76	71	80	75	70	78	73	69	75	71	68	66								
4	87	76	68	62	85	75	68	62	72	66	61	70	65	60	68	63	60	58								
5	81	69	61	55	79	68	60	55	66	59	54	64	58	53	62	57	53	51								
6	75	63	55	49	73	62	54	49	60	53	48	59	53	48	57	52	47	46								
7	70	58	50	44	68	57	49	44	55	48	43	54	48	43	53	47	43	41								
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37								
9	61	49	41	36	60	48	41	36	47	41	36	46	40	36	45	40	36	34								
10	58	46	38	33	57	45	38	33	44	38	33	43	37	33	42	37	33	31								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	134089	134089	134089
5°	140990	133908	128893
10°	145939	132312	123044
15°	150414	129906	117788
20°	150570	124554	111008
25°	144916	116417	104073
30°	134565	107134	97192
35°	120627	96445	89925
40°	105820	86063	83149
45°	92504	76194	76665
50°	81688	66663	69081
55°	72019	59116	62105
60°	64362	52323	54395
65°	57000	46026	46026
70°	49804	39274	39274
75°	42605	33217	37220
80°	33740	29762	33740
85°	21795	25616	31701



TEST NUMBER: P592673

CATALOG NUMBER: HCC4W20D010MW-HM40525850-41WWWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	103.0	4.9
10°-20°	290.1	13.8
20°-30°	406.4	19.3
30°-40°	418.6	19.9
40°-50°	356.4	16.9
50°-60°	264.1	12.5
60°-70°	165.7	7.9
70°-80°	82.3	3.9
80°-90°	21.6	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	799.4	37.9
0°-40°	1218.0	57.8
0°-60°	1838.5	87.2
0°-90°	2108.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2108.2	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1087	1087	1087	1087	1087	
5°	1139	1119	1082	1051	1041	109
15°	1178	1125	1017	943	922	331
25°	1065	991	855	782	765	487
35°	801	741	640	599	597	499
45°	530	494	437	428	440	411
55°	335	308	275	280	289	303
65°	195	176	158	155	158	195
75°	89	80	70	75	78	95
85°	15	15	18	21	22	20
90°	0	0	0	0	0	



TEST NUMBER: P592673

CATALOG NUMBER: HCC4W20D010MW-HM40525850-41WWWB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	1087.1	1087.1	1087.1	1087.1	1087.1	1087.1	1087.1	1087.1	1087.1
2.5°	1110.9	1106.6	1101.0	1091.3	1081.5	1073.1	1064.8	1060.6	1059.1
5°	1138.7	1130.4	1119.2	1101.0	1081.5	1064.8	1050.8	1043.9	1041.0
7.5°	1158.2	1149.9	1131.7	1103.9	1075.9	1050.8	1028.5	1018.8	1015.9
10°	1165.2	1155.5	1130.4	1092.6	1056.4	1025.6	1000.5	988.0	982.4
12.5°	1170.9	1158.2	1126.1	1081.5	1036.9	999.2	972.7	955.9	951.8
15°	1177.9	1163.9	1124.7	1070.4	1017.3	972.7	943.4	928.0	922.4
17.5°	1170.9	1155.5	1109.4	1048.0	988.0	939.2	907.0	893.2	887.5
20°	1147.1	1130.4	1078.8	1013.1	948.9	898.7	866.6	852.7	845.7
22.5°	1110.9	1092.6	1039.6	969.9	904.3	855.4	824.7	810.8	806.6
25°	1064.8	1046.6	990.8	919.7	855.4	807.9	781.5	768.9	764.7
27.5°	1010.4	992.2	937.8	868.0	806.6	762.0	741.0	728.5	725.7
30°	944.8	926.7	873.6	809.4	752.2	710.3	693.6	683.8	682.4
32.5°	872.2	856.8	807.9	749.3	695.0	660.1	647.5	640.5	639.1
35°	801.1	784.3	741.0	688.0	640.5	609.9	598.6	597.2	597.2
37.5°	728.5	711.7	676.8	628.0	587.5	559.6	555.4	556.8	556.8
40°	657.2	642.0	611.2	570.7	534.5	513.5	512.1	514.9	516.4
42.5°	590.2	577.7	549.9	514.9	484.3	467.5	468.9	474.5	478.6
45°	530.3	519.1	494.0	463.3	436.8	424.3	428.4	435.4	439.5
47.5°	475.9	466.1	442.4	414.4	392.2	383.8	389.3	397.7	403.3
50°	425.7	417.3	394.9	365.7	347.4	341.9	348.9	357.3	360.0
52.5°	380.9	372.5	348.9	323.8	309.8	307.1	313.9	320.9	325.2
55°	334.9	327.9	308.4	286.1	274.9	273.6	280.4	286.1	288.8
57.5°	297.2	290.3	272.1	252.6	242.8	241.4	248.4	252.6	253.9
60°	260.9	253.9	237.2	219.1	212.1	212.1	216.3	219.1	220.5
62.5°	227.5	220.5	205.1	189.8	184.2	184.2	184.2	185.6	189.8
65°	195.3	189.8	175.8	161.8	157.7	154.8	154.8	154.8	157.7
67.5°	166.1	160.5	149.3	136.7	132.6	128.3	127.0	129.7	129.7
70°	138.1	134.0	122.8	113.0	108.9	104.6	103.2	108.9	108.9
72.5°	113.0	108.9	101.9	92.1	87.9	86.5	89.4	92.1	93.5
75°	89.4	85.1	79.5	74.0	69.7	71.1	75.4	76.7	78.1
77.5°	67.0	65.6	60.0	55.9	55.9	57.2	60.0	62.7	64.2
80°	47.5	46.0	43.2	40.5	41.9	44.6	46.0	48.9	47.5
82.5°	29.2	29.2	27.9	27.9	29.2	32.1	33.5	34.9	36.2
85°	15.4	15.4	15.4	16.7	18.1	19.5	20.9	22.4	22.4
87.5°	4.1	5.6	5.6	7.0	8.4	8.4	9.7	9.7	9.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)