

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580016

Luminaire Tested: **HCC4W20D010MW-HM40525835-41WDW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580016
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-9)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W20D010MW-HM40525835-41WDW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2023.1 lumens
Efficiency: N/A
Efficacy: 101.2 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.07 / 1.04
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 20
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580016
CATALOG NUMBER: HCC4W20D010MW-HM40525835-41WDW

Luminous Intensity Polar Plot





TEST NUMBER: P580016

CATALOG NUMBER: HCC4W20D010MW-HM40525835-41WDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	89				
2	103	97	91	87	101	95	90	86	91	87	84	88	85	82	85	83	80	78				
3	96	87	81	76	94	86	80	75	83	78	74	81	76	72	78	74	71	69				
4	90	80	72	67	87	78	72	66	76	70	66	74	69	65	72	68	64	62				
5	84	73	65	60	82	72	65	59	70	64	59	68	63	58	66	62	58	56				
6	78	67	59	54	77	66	59	54	64	58	53	63	57	53	61	56	53	51				
7	73	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46				
8	69	57	50	45	68	57	50	45	55	49	45	54	49	44	53	48	44	42				
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	45	41	39				
10	61	50	43	38	60	49	43	38	48	42	38	48	42	38	47	42	38	36				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	161743	161743	161743
5°	161346	161519	161519
10°	159479	159629	159479
15°	157552	157552	157552
20°	151082	151450	151620
25°	141323	141513	141881
30°	126618	127017	127017
35°	102814	103627	103838
40°	77594	78028	78254
45°	59431	59204	59204
50°	48971	48702	48702
55°	42020	41741	41741
60°	37497	37176	37176
65°	35257	35257	35257
70°	32818	32818	32818
75°	29738	30405	29738
80°	27916	26992	27916
85°	23068	23068	23068



TEST NUMBER: P580016
 CATALOG NUMBER: HCC4W20D010MW-HM40525835-41WDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	123.5	6.1
10°-20°	345.7	17.1
20°-30°	475.1	23.5
30°-40°	427.2	21.1
40°-50°	269.9	13.3
50°-60°	176.2	8.7
60°-70°	119.4	5.9
70°-80°	67.2	3.3
80°-90°	18.9	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	944.3	46.7
0°-40°	1371.5	67.8
0°-60°	1817.6	89.8
0°-90°	2023.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2023.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1311	1311	1311	1311	1311	
5°	1303	1303	1304	1304	1304	123
15°	1234	1234	1234	1234	1234	345
25°	1038	1040	1040	1042	1042	474
35°	683	685	688	691	690	425
45°	341	339	339	339	339	270
55°	195	195	194	195	194	177
65°	121	121	121	121	121	120
75°	62	64	64	64	62	67
85°	16	16	16	16	16	19
90°	0	0	0	0	0	



TEST NUMBER: P580016

CATALOG NUMBER: HCC4W20D010MW-HM40525835-41WDW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1311.3	1311.3	1311.3	1311.3	1311.3
2.5°	1304.5	1304.5	1304.5	1304.5	1304.5
5°	1303.1	1303.1	1304.5	1304.5	1304.5
7.5°	1293.6	1295.0	1295.0	1295.0	1295.0
10°	1273.3	1273.3	1274.5	1274.5	1273.3
12.5°	1254.2	1254.2	1254.2	1255.6	1254.2
15°	1233.8	1233.8	1233.8	1233.8	1233.8
17.5°	1198.6	1199.9	1199.9	1199.9	1199.9
20°	1151.0	1153.8	1153.8	1155.1	1155.1
22.5°	1096.8	1098.1	1099.5	1100.9	1099.5
25°	1038.4	1039.8	1039.8	1042.5	1042.5
27.5°	970.5	971.9	974.6	974.6	974.6
30°	889.0	890.4	891.8	891.8	891.8
32.5°	792.7	792.7	795.4	796.8	795.4
35°	682.8	685.4	688.2	691.0	689.6
37.5°	578.2	581.0	582.3	582.3	583.7
40°	481.9	484.6	484.6	487.2	486.0
42.5°	405.8	404.5	404.5	407.2	405.8
45°	340.7	339.4	339.4	339.4	339.4
47.5°	293.2	291.8	291.8	291.8	291.8
50°	255.2	253.8	253.8	253.8	253.8
52.5°	224.0	222.6	222.6	222.6	221.3
55°	195.4	195.4	194.1	195.4	194.1
57.5°	169.6	169.6	169.6	169.6	169.6
60°	152.0	150.7	150.7	150.7	150.7
62.5°	135.7	135.7	135.7	135.7	135.7
65°	120.8	120.8	120.8	120.8	120.8
67.5°	105.9	104.5	105.9	105.9	104.5
70°	91.0	89.6	91.0	91.0	91.0
72.5°	76.0	76.0	76.0	77.4	76.0
75°	62.4	63.8	63.8	63.8	62.4
77.5°	50.2	51.6	50.2	50.2	50.2
80°	39.3	38.0	38.0	38.0	39.3
82.5°	27.2	27.2	27.2	27.2	27.2
85°	16.3	16.3	16.3	16.3	16.3
87.5°	6.8	6.8	6.8	6.8	6.8
90°	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)