

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580056

Luminaire Tested: **HCC4W20D010BZ-HM40525927-41WWWB**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580056
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-18)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W20D010BZ-HM40525927-41WWWB
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1563.4 lumens
Efficiency: N/A
Efficacy: 78.2 lumens/watt
Spacing Criteria (0/90/45): 1.13 / 1.07 / 1.15
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 20
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580056
CATALOG NUMBER: HCC4W20D010BZ-HM40525927-41WWWB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P580056

CATALOG NUMBER: HCC4W20D010BZ-HM40525927-41WWWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87								
2	102	95	89	84	99	93	87	83	89	85	81	86	82	79	83	80	77	75								
3	94	85	77	72	92	83	76	71	80	75	70	78	73	69	75	71	68	66								
4	87	76	68	62	85	75	68	62	72	66	61	70	65	60	68	63	60	58								
5	81	69	61	55	79	68	60	55	66	59	54	64	58	53	62	57	53	51								
6	75	63	55	49	73	62	54	49	60	53	48	59	53	48	57	52	47	46								
7	70	58	50	44	68	57	49	44	55	48	43	54	48	43	53	47	43	41								
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37								
9	61	49	41	36	60	48	41	36	47	41	36	46	40	36	45	40	36	34								
10	58	45	38	33	57	45	38	33	44	38	33	43	37	33	42	37	33	31								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	99429	99429	99429
5°	104551	99301	95587
10°	108227	98120	91256
15°	111530	96334	87357
20°	111651	92369	82327
25°	107462	86340	77181
30°	99785	79446	72082
35°	89443	71524	66706
40°	78495	63827	61653
45°	68589	56500	56866
50°	60580	49450	51235
55°	53396	43826	46084
60°	47735	38805	40359
65°	42291	34148	34148
70°	36929	29104	29104
75°	31549	24639	27593
80°	25003	22091	25003
85°	16134	18964	23351



TEST NUMBER: P580056

CATALOG NUMBER: HCC4W20D010BZ-HM40525927-41WWWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	76.4	4.9
10°-20°	215.1	13.8
20°-30°	301.3	19.3
30°-40°	310.5	19.9
40°-50°	264.3	16.9
50°-60°	195.8	12.5
60°-70°	122.9	7.9
70°-80°	61.1	3.9
80°-90°	16.0	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	592.8	37.9
0°-40°	903.3	57.8
0°-60°	1363.4	87.2
0°-90°	1563.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1563.4	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	806	806	806	806	806	
5°	844	830	802	779	772	81
15°	873	834	754	700	684	246
25°	790	735	634	580	567	361
35°	594	550	475	444	443	370
45°	393	366	324	318	326	305
55°	248	229	204	208	214	225
65°	145	130	117	115	117	145
75°	66	59	52	56	58	71
85°	11	11	13	16	16	15
90°	0	0	0	0	0	



TEST NUMBER: P580056

CATALOG NUMBER: HCC4W20D010BZ-HM40525927-41WWWB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	806.1	806.1	806.1	806.1	806.1	806.1	806.1	806.1	806.1
2.5°	823.8	820.7	816.5	809.2	802.0	795.8	789.6	786.5	785.5
5°	844.4	838.2	830.0	816.5	802.0	789.6	779.3	774.1	772.0
7.5°	859.0	852.7	839.3	818.6	797.9	779.3	762.6	755.4	753.3
10°	864.1	856.8	838.2	810.2	783.4	760.6	742.0	732.7	728.6
12.5°	868.3	859.0	835.1	802.0	768.9	741.0	721.3	708.8	705.7
15°	873.4	863.1	834.1	793.7	754.4	721.3	699.6	688.2	684.1
17.5°	868.3	856.8	822.7	777.2	732.7	696.5	672.7	662.3	658.1
20°	850.6	838.2	799.9	751.3	703.7	666.4	642.7	632.3	627.2
22.5°	823.8	810.2	771.0	719.3	670.5	634.4	611.6	601.3	598.2
25°	789.6	776.2	734.8	682.0	634.4	599.2	579.6	570.2	567.1
27.5°	749.2	735.8	695.4	643.7	598.2	565.0	549.5	540.2	538.2
30°	700.6	687.2	647.8	600.2	557.8	526.7	514.3	507.1	506.1
32.5°	646.8	635.4	599.2	555.7	515.3	489.5	480.1	475.0	473.9
35°	594.0	581.6	549.5	510.2	475.0	452.3	444.0	443.0	443.0
37.5°	540.2	527.7	501.9	465.7	435.6	415.0	411.9	412.9	412.9
40°	487.5	476.0	453.3	423.2	396.4	380.8	379.8	381.8	382.9
42.5°	437.7	428.4	407.8	381.8	359.1	346.6	347.8	351.9	355.0
45°	393.2	384.9	366.4	343.5	323.9	314.6	317.7	322.9	326.0
47.5°	352.9	345.6	328.0	307.4	290.8	284.6	288.7	294.9	299.0
50°	315.7	309.5	292.8	271.2	257.7	253.5	258.8	265.0	267.0
52.5°	282.5	276.3	258.8	240.1	229.7	227.7	232.8	238.0	241.1
55°	248.3	243.2	228.7	212.2	203.8	202.8	208.0	212.2	214.3
57.5°	220.5	215.3	201.8	187.3	180.1	179.0	184.2	187.3	188.3
60°	193.5	188.3	175.9	162.5	157.3	157.3	160.4	162.5	163.6
62.5°	168.7	163.6	152.1	140.7	136.6	136.6	136.6	137.6	140.7
65°	144.9	140.7	130.4	120.1	117.0	114.8	114.8	114.8	117.0
67.5°	123.2	119.1	110.7	101.4	98.3	95.2	94.2	96.2	96.2
70°	102.4	99.3	91.1	83.8	80.7	77.7	76.6	80.7	80.7
72.5°	83.8	80.7	75.6	68.2	65.1	64.1	66.2	68.2	69.3
75°	66.2	63.1	59.0	54.8	51.7	52.8	55.9	56.9	57.9
77.5°	49.7	48.6	44.5	41.4	41.4	42.4	44.5	46.6	47.6
80°	35.2	34.2	32.1	30.1	31.1	33.1	34.2	36.2	35.2
82.5°	21.7	21.7	20.6	20.6	21.7	23.9	24.9	25.9	27.0
85°	11.4	11.4	11.4	12.4	13.4	14.5	15.5	16.5	16.5
87.5°	3.1	4.1	4.1	5.2	6.2	6.2	7.2	7.2	7.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)