

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580055

Luminaire Tested: **HCC4W20D010BZ-HM40525927-41WWW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580055
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W20D010BZ-HM40525927-41WWW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1570.6 lumens
Efficiency: N/A
Efficacy: 78.5 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.03 / 1.1
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 20
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580055
CATALOG NUMBER: HCC4W20D010BZ-HM40525927-41WWW

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P580055

CATALOG NUMBER: HCC4W20D010BZ-HM40525927-41WWW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	106	103	100	108	104	101	98	100	97	95	96	94	92	93	91	89	87								
2	102	95	89	84	100	93	88	83	90	85	81	87	83	80	84	81	78	76								
3	94	85	78	72	92	84	77	72	81	75	71	78	73	69	76	72	68	66								
4	87	77	69	63	85	76	68	63	73	67	62	71	66	61	69	64	60	58								
5	81	70	62	56	79	69	61	56	67	60	55	65	59	54	63	58	54	52								
6	76	64	56	50	74	63	55	50	61	54	49	59	53	49	58	53	48	47								
7	71	58	50	45	69	58	50	45	56	49	44	55	49	44	53	48	44	42								
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38								
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35								
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	108482	108482	108482
5°	113255	108005	103003
10°	116118	105747	96554
15°	118528	102936	89579
20°	117886	97921	82039
25°	112947	90559	74636
30°	104342	82679	67653
35°	91446	73542	61225
40°	79639	64970	55148
45°	69304	56675	49278
50°	61751	48836	43483
55°	55181	42945	37612
60°	49264	37522	32415
65°	43779	32922	30791
70°	38444	28382	28743
75°	32502	24162	26640
80°	25003	20599	24293
85°	14577	16134	20521



TEST NUMBER: P580055

CATALOG NUMBER: HCC4W20D010BZ-HM40525927-41WWW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	82.4	5.2
10°-20°	227.4	14.5
20°-30°	310.7	19.8
30°-40°	312.0	19.9
40°-50°	258.1	16.4
50°-60°	187.0	11.9
60°-70°	118.5	7.5
70°-80°	59.9	3.8
80°-90°	14.6	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	620.5	39.5
0°-40°	932.5	59.4
0°-60°	1377.6	87.7
0°-90°	1570.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1570.6	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	880	880	880	880	880	
5°	915	901	872	843	832	88
15°	928	892	806	732	702	261
25°	830	775	665	582	548	379
35°	607	571	488	428	407	381
45°	397	375	325	293	282	309
55°	257	234	200	182	175	231
65°	150	134	113	101	106	149
75°	68	59	51	53	56	73
85°	10	10	11	13	14	14
90°	0	0	0	0	0	



TEST NUMBER: P580055

CATALOG NUMBER: HCC4W20D010BZ-HM40525927-41WWW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	879.5	879.5	879.5	879.5	879.5	879.5	879.5	879.5	879.5
2.5°	896.0	892.9	887.8	881.6	874.4	866.1	858.9	854.7	852.7
5°	914.7	910.6	901.3	887.8	872.3	856.8	843.3	835.0	831.9
7.5°	926.1	919.9	906.5	885.7	862.0	839.1	819.5	808.2	805.1
10°	927.1	919.9	902.3	874.4	844.3	814.4	790.5	774.0	770.9
12.5°	928.2	918.9	897.1	864.0	826.8	789.5	760.6	740.8	735.7
15°	928.2	918.9	891.9	852.7	806.1	763.7	731.6	708.8	701.5
17.5°	919.9	909.6	877.5	831.9	781.2	733.6	696.3	672.6	665.4
20°	898.1	886.7	850.5	800.8	746.0	696.3	659.2	634.3	625.0
22.5°	867.1	853.7	815.4	761.6	706.8	656.0	619.8	593.9	585.7
25°	829.9	816.4	775.0	722.3	665.4	617.8	581.5	557.7	548.4
27.5°	784.3	769.9	729.5	676.7	624.0	576.4	543.2	521.5	512.3
30°	732.6	717.1	678.8	628.1	580.5	535.0	502.8	485.3	475.0
32.5°	672.6	659.2	625.0	579.5	535.0	491.5	464.6	449.1	440.8
35°	607.3	600.1	571.2	531.9	488.4	452.1	428.4	414.0	406.6
37.5°	549.4	542.2	517.4	484.3	446.0	412.8	393.2	380.8	374.6
40°	494.6	488.4	464.6	436.7	403.5	374.6	358.0	348.7	342.5
42.5°	440.8	437.7	418.1	392.2	363.1	338.4	324.9	317.7	312.4
45°	397.3	393.2	374.6	349.7	324.9	304.2	292.8	287.7	282.5
47.5°	359.0	353.8	334.2	312.4	289.7	271.2	260.7	255.6	253.5
50°	321.8	316.7	299.0	277.3	254.5	241.1	232.8	227.7	226.6
52.5°	288.7	283.5	263.8	243.2	225.6	214.1	206.9	201.8	199.7
55°	256.6	250.4	233.9	214.1	199.7	189.4	182.1	177.0	174.9
57.5°	227.7	221.5	206.9	188.3	174.9	165.5	159.3	154.2	152.1
60°	199.7	194.5	181.1	163.4	152.1	143.8	137.6	133.5	131.4
62.5°	173.9	169.6	156.2	140.7	131.4	124.2	118.9	114.8	116.9
65°	150.0	145.9	133.5	120.0	112.8	105.5	101.4	101.4	105.5
67.5°	127.3	123.2	112.8	101.4	95.2	90.0	86.9	90.0	93.1
70°	106.6	102.4	93.1	83.8	78.7	74.6	74.6	77.7	79.7
72.5°	86.9	82.8	75.6	68.2	64.1	61.0	64.1	66.2	68.2
75°	68.2	65.1	59.0	53.8	50.7	49.7	52.8	54.8	55.9
77.5°	50.7	48.6	44.5	40.4	38.3	39.3	42.4	43.5	44.5
80°	35.2	34.2	31.1	29.0	29.0	30.1	32.1	33.1	34.2
82.5°	21.7	21.7	19.6	18.6	19.6	21.7	22.7	23.7	23.7
85°	10.3	11.4	10.3	10.3	11.4	13.4	13.4	14.5	14.5
87.5°	3.1	3.1	4.1	4.1	5.2	5.2	5.2	5.2	6.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)