

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580054

Luminaire Tested: **HCC4W20D010MB-HM40525927-41WWBB**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P580054  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-17)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC4W20D010MB-HM40525927-41WWBB  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1256.1 lumens  
Efficiency: N/A  
Efficacy: 62.8 lumens/watt  
Spacing Criteria (0/90/45): 1.11 / 1.04 / 1.12  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 20  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P580054  
CATALOG NUMBER: HCC4W20D010MB-HM40525927-41WWBB

### Luminous Intensity Polar Plot





TEST NUMBER: P580054

CATALOG NUMBER: HCC4W20D010MB-HM40525927-41WWBB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	108	104	101	109	105	102	100	101	99	97	97	95	94	94	92	91	89								
2	103	97	91	87	101	95	90	86	92	87	84	88	85	82	85	83	80	78								
3	96	87	80	75	94	86	79	74	83	78	73	80	76	72	78	74	71	69								
4	89	79	72	66	87	78	71	65	75	69	65	73	68	64	71	67	63	61								
5	83	72	64	58	81	71	64	58	69	62	58	67	61	57	65	60	56	55								
6	77	66	58	52	75	65	57	52	63	57	52	61	56	51	60	55	51	49								
7	72	60	53	47	71	59	52	47	58	51	47	57	51	46	55	50	46	44								
8	68	56	48	43	66	55	48	43	54	47	42	53	47	42	51	46	42	40								
9	64	52	44	39	62	51	44	39	50	43	39	49	43	39	48	43	39	37								
10	60	48	41	36	59	47	41	36	46	40	36	46	40	36	45	39	36	34								

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	89697	89697	89697
5°	95042	89396	84914
10°	98984	87974	79934
15°	102758	85863	75162
20°	103736	81737	69529
25°	100371	75602	63625
30°	93860	68522	57897
35°	83646	60893	52024
40°	73117	52974	46308
45°	63704	44935	40051
50°	55572	38129	34329
55°	48708	31590	27806
60°	42604	25533	20401
65°	37125	19000	11470
70°	32457	12334	3715
75°	26640	6386	1001
80°	19889	2912	710
85°	11746	1415	1415



TEST NUMBER: P580054  
 CATALOG NUMBER: HCC4W20D010MB-HM40525927-41WWBB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	68.6	5.5
10°-20°	192.1	15.3
20°-30°	265.6	21.1
30°-40°	267.0	21.3
40°-50°	215.5	17.2
50°-60°	145.7	11.6
60°-70°	74.2	5.9
70°-80°	23.7	1.9
80°-90°	3.6	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	526.3	41.9
0°-40°	793.4	63.2
0°-60°	1154.6	91.9
0°-90°	1256.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1256.1	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	727	727	727	727	727	
5°	768	753	722	696	686	74
15°	805	761	672	608	589	227
25°	738	673	556	487	468	338
35°	556	502	404	354	346	347
45°	365	327	258	230	230	283
55°	226	196	147	128	129	204
65°	127	104	65	42	39	128
75°	56	39	13	3	2	60
85°	8	4	1	1	1	11
90°	0	0	0	0	0	



TEST NUMBER: P580054

CATALOG NUMBER: HCC4W20D010MB-HM40525927-41WWBB

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	727.2	727.2	727.2	727.2	727.2	727.2	727.2	727.2	727.2
2.5°	746.8	742.7	738.6	731.3	723.1	714.8	709.6	705.5	703.5
5°	767.6	762.4	753.1	737.5	722.0	707.6	696.2	688.9	685.8
7.5°	784.1	776.9	761.4	739.6	715.8	693.0	678.6	668.2	664.1
10°	790.3	782.0	761.4	732.4	702.4	674.4	653.8	643.5	638.2
12.5°	797.5	788.2	762.4	726.2	688.9	655.9	632.0	618.6	613.4
15°	804.7	792.3	761.4	716.9	672.4	634.1	608.3	594.8	588.6
17.5°	804.7	790.3	753.1	701.4	650.7	610.3	581.3	565.8	560.7
20°	790.3	773.8	733.4	676.5	622.7	579.2	551.4	535.9	529.7
22.5°	767.6	748.9	705.5	646.6	589.7	547.2	519.2	504.8	498.6
25°	737.5	718.9	673.4	612.4	555.5	513.1	487.2	473.8	467.5
27.5°	702.4	681.7	636.1	575.1	519.2	479.0	455.1	442.7	437.6
30°	659.0	639.2	594.8	534.8	481.1	443.8	422.1	410.6	406.5
32.5°	608.3	591.7	548.3	492.4	441.7	407.5	387.9	378.6	374.5
35°	555.5	540.0	501.7	450.0	404.4	372.4	353.7	347.5	345.5
37.5°	505.8	492.4	455.1	407.5	366.2	338.3	321.7	317.6	315.5
40°	454.1	444.8	410.6	367.3	329.0	304.1	290.6	287.6	287.6
42.5°	407.5	397.2	367.3	327.9	293.7	269.0	259.7	256.6	257.6
45°	365.2	354.8	326.9	290.6	257.6	236.9	229.6	229.6	229.6
47.5°	325.9	316.6	290.6	253.5	226.5	210.0	202.8	202.8	203.8
50°	289.6	283.4	254.5	222.4	198.7	183.1	177.9	176.9	178.9
52.5°	255.6	248.2	222.4	193.4	170.7	158.3	153.1	152.1	153.1
55°	226.5	218.3	195.6	167.6	146.9	134.4	128.2	127.2	129.3
57.5°	198.7	192.4	168.6	143.8	124.1	111.7	106.6	104.5	105.5
60°	172.7	166.5	144.9	121.0	103.5	91.1	83.8	81.7	82.7
62.5°	149.0	143.8	123.1	100.4	82.7	71.3	64.1	59.0	61.0
65°	127.2	122.0	103.5	80.6	65.1	52.8	42.4	38.3	39.3
67.5°	108.6	102.4	84.9	64.1	48.6	35.2	23.7	21.7	21.7
70°	90.0	83.8	68.2	49.7	34.2	18.6	10.3	10.3	10.3
72.5°	72.4	67.2	52.8	37.3	21.7	8.3	4.1	4.1	4.1
75°	55.9	51.7	39.3	25.8	13.4	4.1	3.1	2.1	2.1
77.5°	41.4	37.3	28.0	17.5	8.3	2.1	2.1	2.1	2.1
80°	28.0	24.8	18.6	10.3	4.1	1.0	1.0	1.0	1.0
82.5°	16.5	14.5	10.3	5.2	2.1	1.0	1.0	1.0	1.0
85°	8.3	6.2	4.1	2.1	1.0	1.0	1.0	1.0	1.0
87.5°	2.1	1.0	1.0	1.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)