

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580072

Luminaire Tested: **HCC4S20D010MB-HM40525930-41WWBB**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580072
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-17)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4S20D010MB-HM40525930-41WWBB
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1397.5 lumens
Efficiency: N/A
Efficacy: 69.9 lumens/watt
Spacing Criteria (0/90/45): 1.11 / 1.04 / 1.12
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 20
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580072
CATALOG NUMBER: HCC4S20D010MB-HM40525930-41WWBB

Luminous Intensity Polar Plot





TEST NUMBER: P580072

CATALOG NUMBER: HCC4S20D010MB-HM40525930-41WWBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	111	108	104	101	109	105	102	100	101	99	97	97	95	94	94	92	91	89					89			
2	103	97	91	87	101	95	90	86	92	87	84	88	85	82	85	83	80	78					78			
3	96	87	80	75	94	86	79	74	83	78	73	80	76	72	78	74	71	69					69			
4	89	79	72	66	87	78	71	65	75	69	65	73	68	64	71	67	63	61					61			
5	83	72	64	58	81	71	64	58	69	62	58	67	61	57	65	60	56	55					55			
6	77	66	58	52	75	65	57	52	63	57	52	61	56	51	60	55	51	49					49			
7	72	60	53	47	71	59	52	47	58	51	47	57	51	46	55	50	46	44					44			
8	68	56	48	43	66	55	48	43	54	47	43	53	47	42	51	46	42	40					40			
9	64	52	44	39	62	51	44	39	50	43	39	49	43	39	48	43	39	37					37			
10	60	48	41	36	59	47	41	36	46	40	36	46	40	36	45	39	36	34					34			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	99799	99799	99799
5°	105727	99474	94472
10°	110131	97882	88939
15°	114327	95530	83616
20°	115418	90938	77339
25°	111681	84108	70798
30°	104428	76227	64420
35°	93057	67760	57882
40°	81362	58932	51509
45°	70874	49976	44586
50°	61828	42389	38206
55°	54192	35139	30924
60°	47414	28369	22720
65°	41298	21160	12754
70°	36100	13704	4147
75°	29643	7101	1096
80°	22091	3267	781
85°	13020	1557	1557



TEST NUMBER: P580072
 CATALOG NUMBER: HCC4S20D010MB-HM40525930-41WWBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	76.4	5.5
10°-20°	213.7	15.3
20°-30°	295.5	21.1
30°-40°	297.1	21.3
40°-50°	239.8	17.2
50°-60°	162.1	11.6
60°-70°	82.5	5.9
70°-80°	26.4	1.9
80°-90°	4.0	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	585.6	41.9
0°-40°	882.7	63.2
0°-60°	1284.5	91.9
0°-90°	1397.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1397.5	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	809	809	809	809	809	
5°	854	838	803	775	763	82
15°	895	847	748	677	655	252
25°	821	749	618	542	520	376
35°	618	558	450	394	384	386
45°	406	364	286	256	256	315
55°	252	218	163	143	144	226
65°	142	115	72	47	44	142
75°	62	44	15	3	2	67
85°	9	5	1	1	1	12
90°	0	0	0	0	0	



TEST NUMBER: P580072

CATALOG NUMBER: HCC4S20D010MB-HM40525930-41WWBB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	809.1	809.1	809.1	809.1	809.1	809.1	809.1	809.1	809.1
2.5°	830.9	826.3	821.7	813.7	804.5	795.2	789.5	784.9	782.6
5°	853.9	848.2	837.9	820.6	803.4	787.2	774.6	766.5	763.0
7.5°	872.4	864.3	847.1	822.9	796.4	771.1	755.0	743.5	738.9
10°	879.3	870.1	847.1	814.8	781.5	750.4	727.3	715.8	710.1
12.5°	887.3	877.0	848.2	807.9	766.5	729.6	703.2	688.2	682.5
15°	895.3	881.6	847.1	797.5	748.1	705.5	676.7	661.7	654.8
17.5°	895.3	879.3	837.9	780.3	723.9	679.0	646.8	629.5	623.7
20°	879.3	860.8	816.0	752.7	692.8	644.5	613.4	596.2	589.2
22.5°	853.9	833.2	784.9	719.3	656.0	608.8	577.7	561.6	554.7
25°	820.6	799.8	749.2	681.3	618.0	570.9	542.1	527.0	520.2
27.5°	781.5	758.4	707.8	639.9	577.7	532.9	506.4	492.5	486.8
30°	733.2	711.3	661.7	594.9	535.2	493.7	469.6	456.9	452.3
32.5°	676.7	658.3	610.0	547.8	491.4	453.4	431.6	421.2	416.6
35°	618.0	600.8	558.1	500.7	450.0	414.3	393.7	386.7	384.4
37.5°	562.8	547.8	506.4	453.4	407.4	376.3	358.0	353.3	351.0
40°	505.3	494.9	456.9	408.6	366.0	338.4	323.3	319.9	319.9
42.5°	453.4	441.9	408.6	364.9	326.9	299.3	288.8	285.4	286.5
45°	406.3	394.8	363.7	323.3	286.5	263.6	255.6	255.6	255.6
47.5°	362.6	352.1	323.3	281.9	252.0	233.6	225.6	225.6	226.8
50°	322.2	315.3	283.1	247.4	220.9	203.7	198.0	196.8	199.1
52.5°	284.2	276.2	247.4	215.2	189.9	176.1	170.3	169.2	170.3
55°	252.0	242.8	217.5	186.4	163.4	149.6	142.7	141.5	143.8
57.5°	220.9	214.0	187.6	160.0	138.1	124.3	118.5	116.2	117.3
60°	192.2	185.2	161.2	134.7	115.0	101.3	93.3	91.0	92.1
62.5°	165.7	160.0	137.0	111.6	92.1	79.4	71.3	65.6	67.9
65°	141.5	135.8	115.0	89.8	72.5	58.7	47.1	42.6	43.7
67.5°	120.9	113.9	94.4	71.3	54.1	39.1	26.5	24.2	24.2
70°	100.1	93.3	75.9	55.3	38.0	20.8	11.5	11.5	11.5
72.5°	80.5	74.8	58.7	41.4	24.2	9.2	4.6	4.6	4.6
75°	62.2	57.6	43.7	28.8	14.9	4.6	3.4	2.3	2.3
77.5°	46.0	41.4	31.1	19.6	9.2	2.3	2.3	2.3	2.3
80°	31.1	27.6	20.8	11.5	4.6	1.1	1.1	1.1	1.1
82.5°	18.5	16.1	11.5	5.7	2.3	1.1	1.1	1.1	1.1
85°	9.2	6.9	4.6	2.3	1.1	1.1	1.1	1.1	1.1
87.5°	2.3	1.1	1.1	1.1	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)