

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580085

Luminaire Tested: **HCC4W20D010SL-HM40525935-41NDW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580085
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-3)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W20D010SL-HM40525935-41NDW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" NARROW DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1668.5 lumens
Efficiency: N/A
Efficacy: 83.4 lumens/watt
Spacing Criteria (0/90/45): 1.03 / 1.03 / 1.01
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 20
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580085
CATALOG NUMBER: HCC4W20D010SL-HM40525935-41NDW

Luminous Intensity Polar Plot





TEST NUMBER: P580085
 CATALOG NUMBER: HCC4W20D010SL-HM40525935-41NDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	108	104	101	109	105	102	100	101	99	97	98	96	94	94	92	91	89																			
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79																			
3	97	88	82	77	95	87	81	76	84	79	75	82	77	74	79	76	73	71																			
4	90	81	74	68	88	80	73	68	77	72	67	75	70	66	73	69	65	64																			
5	85	74	67	61	83	73	66	61	71	65	60	69	64	60	68	63	59	58																			
6	79	68	61	56	78	67	60	55	66	60	55	64	59	55	63	58	54	52																			
7	75	63	56	51	73	62	56	51	61	55	50	60	54	50	59	53	50	48																			
8	70	59	52	47	69	58	51	46	57	51	46	56	50	46	55	50	46	44																			
9	66	55	48	43	65	54	47	43	53	47	43	52	47	43	51	46	42	41																			
10	63	51	44	40	62	51	44	40	50	44	40	49	43	39	48	43	39	38																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	146584
5°	145497
10°	141706
15°	137976
20°	131800
25°	122787
30°	108117
35°	85272
40°	61911
45°	45476
50°	36997
55°	31031
60°	28123
65°	25830
70°	24019
75°	21970
80°	19818
85°	17266



TEST NUMBER: P580085
 CATALOG NUMBER: HCC4W20D010SL-HM40525935-41NDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	110.8	6.6
10°-20°	303.1	18.2
20°-30°	410.8	24.6
30°-40°	352.5	21.1
40°-50°	208.2	12.5
50°-60°	131.9	7.9
60°-70°	88.6	5.3
70°-80°	48.9	2.9
80°-90°	13.7	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	824.7	49.4
0°-40°	1177.2	70.6
0°-60°	1517.3	90.9
0°-90°	1668.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1668.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1188	
5°	1175	111
15°	1080	303
25°	902	411
35°	566	353
45°	261	208
55°	144	132
65°	88	89
75°	46	49
85°	12	14
90°	0	



TEST NUMBER: P580085
CATALOG NUMBER: HCC4W20D010SL-HM40525935-41NDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1188.4
2.5°	1179.9
5°	1175.1
7.5°	1159.3
10°	1131.4
12.5°	1107.2
15°	1080.5
17.5°	1046.5
20°	1004.1
22.5°	956.8
25°	902.2
27.5°	838.0
30°	759.1
32.5°	665.7
35°	566.3
37.5°	470.5
40°	384.5
42.5°	312.9
45°	260.7
47.5°	223.1
50°	192.8
52.5°	167.3
55°	144.3
57.5°	126.2
60°	114.0
62.5°	101.9
65°	88.5
67.5°	77.7
70°	66.6
72.5°	55.7
75°	46.1
77.5°	36.4
80°	27.9
82.5°	19.4
85°	12.2
87.5°	4.8
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)