

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580109

Luminaire Tested: **HCC4S20D010SL-HM40525940-41WWW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580109
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4S20D010SL-HM40525940-41WWW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1907.3 lumens
Efficiency: N/A
Efficacy: 95.4 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.03 / 1.1
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 20
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580109
CATALOG NUMBER: HCC4S20D010SL-HM40525940-41WWW

Luminous Intensity Polar Plot





TEST NUMBER: P580109

CATALOG NUMBER: HCC4S20D010SL-HM40525940-41WWW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	111	106	103	100	108	104	101	98	100	97	95	96	94	92	93	91	89	87					87			
2	102	95	89	84	100	93	88	83	90	85	81	87	83	80	84	81	78	76					76			
3	94	85	78	72	92	84	77	72	81	75	71	78	73	69	76	72	68	66					66			
4	87	77	69	63	85	76	68	63	73	67	62	71	66	61	69	64	60	58					58			
5	81	70	62	56	79	69	61	56	67	60	55	65	59	54	63	58	54	52					52			
6	76	64	56	50	74	63	55	50	61	54	49	59	53	49	58	53	48	47					47			
7	71	58	50	45	69	58	50	45	56	49	44	55	49	44	53	48	44	42					42			
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38					38			
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35					35			
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32					32			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	131745	131745	131745
5°	137536	131159	125092
10°	141017	128417	117245
15°	143940	124990	108785
20°	143167	118910	99628
25°	137158	109953	90627
30°	126703	100397	82138
35°	111066	89307	74355
40°	96706	78898	66967
45°	84166	68833	59849
50°	74991	59314	52809
55°	67009	52149	45654
60°	59823	45564	39347
65°	53148	39985	37387
70°	46667	34441	34910
75°	39508	29357	32359
80°	30331	25003	29478
85°	17832	19672	24767



TEST NUMBER: P580109

CATALOG NUMBER: HCC4S20D010SL-HM40525940-41WWW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.1	5.2
10°-20°	276.2	14.5
20°-30°	377.3	19.8
30°-40°	378.9	19.9
40°-50°	313.4	16.4
50°-60°	227.1	11.9
60°-70°	143.9	7.5
70°-80°	72.7	3.8
80°-90°	17.8	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	753.5	39.5
0°-40°	1132.4	59.4
0°-60°	1672.9	87.7
0°-90°	1907.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1907.3	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1068	1068	1068	1068	1068	
5°	1111	1094	1059	1024	1010	106
15°	1127	1083	979	888	852	317
25°	1008	941	808	706	666	461
35°	738	694	593	520	494	462
45°	482	455	395	356	343	375
55°	312	284	242	221	212	280
65°	182	162	137	123	128	181
75°	83	72	62	64	68	89
85°	13	13	14	16	18	17
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P580109

CATALOG NUMBER: HCC4S20D010SL-HM40525940-41WWW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	1068.1	1068.1	1068.1	1068.1	1068.1	1068.1	1068.1	1068.1	1068.1
2.5°	1088.2	1084.4	1078.1	1070.6	1061.8	1051.7	1043.0	1037.9	1035.4
5°	1110.8	1105.7	1094.5	1078.1	1059.3	1040.4	1024.0	1014.1	1010.3
7.5°	1124.6	1117.1	1100.7	1075.5	1046.6	1019.0	995.1	981.4	977.6
10°	1125.9	1117.1	1095.7	1061.8	1025.3	988.8	960.0	939.9	936.1
12.5°	1127.2	1115.8	1089.4	1049.2	1004.0	958.8	923.6	899.7	893.4
15°	1127.2	1115.8	1083.1	1035.4	978.8	927.3	888.4	860.7	851.9
17.5°	1117.1	1104.4	1065.6	1010.3	948.7	890.9	845.7	816.8	807.9
20°	1090.7	1076.8	1032.9	972.5	905.9	845.7	800.4	770.2	759.0
22.5°	1052.9	1036.7	990.1	924.8	858.2	796.6	752.7	721.2	711.1
25°	1007.8	991.4	941.1	877.1	807.9	750.1	706.2	677.3	665.9
27.5°	952.5	934.8	885.8	821.7	757.7	699.9	659.6	633.3	622.0
30°	889.6	870.8	824.2	762.8	704.9	649.7	610.7	589.3	576.7
32.5°	816.8	800.4	759.0	703.7	649.7	596.9	564.2	545.3	535.3
35°	737.6	728.8	693.6	645.9	593.1	549.1	520.2	502.6	493.8
37.5°	667.2	658.4	628.2	588.1	541.6	501.4	477.5	462.4	454.9
40°	600.6	593.1	564.2	530.3	490.0	454.9	434.7	423.5	415.9
42.5°	535.3	531.5	507.7	476.2	441.0	410.9	394.6	385.7	379.4
45°	482.5	477.5	454.9	424.7	394.6	369.4	355.6	349.3	343.1
47.5°	436.0	429.8	405.8	379.4	351.8	329.2	316.7	310.4	307.9
50°	390.8	384.5	363.1	336.8	309.1	292.7	282.7	276.4	275.2
52.5°	350.5	344.3	320.4	295.2	273.9	260.1	251.3	245.0	242.5
55°	311.6	304.1	284.0	260.1	242.5	230.0	221.1	214.8	212.3
57.5°	276.4	268.9	251.3	228.7	212.3	201.1	193.5	187.2	184.7
60°	242.5	236.3	219.9	198.5	184.7	174.7	167.1	162.1	159.5
62.5°	211.0	206.1	189.7	170.9	159.5	150.8	144.5	139.5	142.0
65°	182.1	177.2	162.1	145.8	137.0	128.1	123.2	123.2	128.1
67.5°	154.5	149.6	137.0	123.2	115.6	109.3	105.5	109.3	113.1
70°	129.4	124.4	113.1	101.7	95.5	90.5	90.5	94.3	96.8
72.5°	105.5	100.5	91.8	82.9	77.9	74.1	77.9	80.4	82.9
75°	82.9	79.1	71.6	65.4	61.6	60.3	64.1	66.6	67.9
77.5°	61.6	59.1	54.0	49.0	46.5	47.7	51.5	52.8	54.0
80°	42.7	41.5	37.7	35.2	35.2	36.5	39.0	40.3	41.5
82.5°	26.4	26.4	23.9	22.6	23.9	26.4	27.6	28.9	28.9
85°	12.6	13.9	12.6	12.6	13.9	16.3	16.3	17.5	17.5
87.5°	3.8	3.8	5.0	5.0	6.3	6.3	6.3	6.3	7.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)