

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580091

Luminaire Tested: **HCC4W20D010MW-HM40525935-41WWW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580091
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W20D010MW-HM40525935-41WWW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1840.7 lumens
Efficiency: N/A
Efficacy: 92.0 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.03 / 1.1
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 20
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580091
CATALOG NUMBER: HCC4W20D010MW-HM40525935-41WWW

Luminous Intensity Polar Plot





TEST NUMBER: P580091

CATALOG NUMBER: HCC4W20D010MW-HM40525935-41WWW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	106	103	100	108	104	101	98	100	97	95	96	94	92	93	91	89	87								
2	102	95	89	84	100	93	88	83	90	85	81	87	83	80	84	81	78	76								
3	94	85	78	72	92	84	77	72	81	75	71	78	73	69	76	72	68	66								
4	87	77	69	63	85	76	68	63	73	67	62	71	66	61	69	64	60	58								
5	81	70	62	56	79	69	61	56	67	60	55	65	59	54	63	58	54	52								
6	76	64	56	50	74	63	55	50	61	54	49	59	53	49	58	53	48	47								
7	71	58	50	45	69	58	50	45	56	49	44	55	49	44	53	48	44	42								
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38								
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35								
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	127132	127132	127132
5°	132732	126566	120721
10°	136095	123933	113149
15°	138896	120635	104992
20°	138166	114775	96149
25°	132354	106115	87469
30°	122274	96893	79275
35°	107181	86190	71765
40°	93341	76145	64616
45°	81235	66426	57739
50°	72362	57241	50947
55°	64664	50321	44085
60°	57726	43960	37990
65°	51309	38555	36074
70°	45044	33215	33684
75°	38173	28308	31215
80°	29265	24151	28413
85°	17266	18823	24059



TEST NUMBER: P580091
 CATALOG NUMBER: HCC4W20D010MW-HM40525935-41WWW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	96.6	5.2
10°-20°	266.5	14.5
20°-30°	364.1	19.8
30°-40°	365.6	19.9
40°-50°	302.5	16.4
50°-60°	219.2	11.9
60°-70°	138.8	7.5
70°-80°	70.2	3.8
80°-90°	17.2	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	727.2	39.5
0°-40°	1092.9	59.4
0°-60°	1614.5	87.7
0°-90°	1840.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1840.7	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1031	1031	1031	1031	1031	
5°	1072	1056	1022	988	975	103
15°	1088	1045	945	857	822	306
25°	972	908	780	682	643	444
35°	712	669	572	502	477	446
45°	466	439	381	343	331	362
55°	301	274	234	214	205	270
65°	176	156	132	119	124	175
75°	80	69	59	62	66	85
85°	12	12	13	16	17	17
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P580091

CATALOG NUMBER: HCC4W20D010MW-HM40525935-41WWW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	1030.7	1030.7	1030.7	1030.7	1030.7	1030.7	1030.7	1030.7	1030.7
2.5°	1050.2	1046.5	1040.4	1033.2	1024.7	1015.0	1006.5	1001.7	999.3
5°	1072.0	1067.2	1056.3	1040.4	1022.2	1004.1	988.3	978.6	975.0
7.5°	1085.3	1078.1	1062.2	1038.0	1010.2	983.4	960.4	947.1	943.4
10°	1086.6	1078.1	1057.4	1024.7	989.5	954.3	926.4	907.0	903.4
12.5°	1087.7	1076.8	1051.3	1012.6	968.9	925.3	891.3	868.3	862.2
15°	1087.7	1076.8	1045.3	999.3	944.7	894.9	857.4	830.7	822.2
17.5°	1078.1	1065.9	1028.3	975.0	915.5	859.8	816.1	788.2	779.7
20°	1052.6	1039.2	996.7	938.6	874.4	816.1	772.5	743.4	732.5
22.5°	1016.2	1000.4	955.6	892.5	828.2	768.8	726.4	696.1	686.4
25°	972.5	956.8	908.3	846.4	779.7	724.0	681.5	653.6	642.7
27.5°	919.2	902.2	854.9	793.0	731.2	675.5	636.6	611.1	600.2
30°	858.5	840.4	795.4	736.0	680.3	627.0	589.3	568.7	556.6
32.5°	788.2	772.5	732.5	679.1	627.0	576.0	544.5	526.2	516.6
35°	711.8	703.3	669.4	623.3	572.4	529.9	502.0	485.1	476.6
37.5°	643.9	635.4	606.3	567.5	522.7	483.8	460.7	446.3	439.0
40°	579.7	572.4	544.5	511.8	472.9	439.0	419.6	408.7	401.3
42.5°	516.6	512.9	489.9	459.6	425.7	396.5	380.8	372.3	366.2
45°	465.7	460.7	439.0	409.8	380.8	356.5	343.2	337.1	331.0
47.5°	420.8	414.8	391.7	366.2	339.5	317.7	305.6	299.5	297.1
50°	377.1	371.1	350.4	324.9	298.3	282.5	272.9	266.8	265.5
52.5°	338.4	332.3	309.2	284.9	264.4	251.0	242.5	236.5	234.0
55°	300.7	293.5	274.0	251.0	234.0	221.9	213.5	207.4	205.0
57.5°	266.8	259.5	242.5	220.7	205.0	194.1	186.7	180.7	178.2
60°	234.0	228.0	212.2	191.5	178.2	168.6	161.3	156.5	154.0
62.5°	203.7	198.9	183.1	164.9	154.0	145.6	139.5	134.7	137.1
65°	175.8	171.0	156.5	140.6	132.1	123.6	118.8	118.8	123.6
67.5°	149.1	144.3	132.1	118.8	111.6	105.5	101.9	105.5	109.2
70°	124.9	120.1	109.2	98.2	92.1	87.3	87.3	91.0	93.4
72.5°	101.9	97.0	88.5	80.1	75.1	71.6	75.1	77.7	80.1
75°	80.1	76.4	69.2	63.1	59.4	58.2	61.8	64.2	65.5
77.5°	59.4	57.0	52.2	47.3	44.8	46.1	49.7	50.9	52.2
80°	41.2	40.0	36.4	34.0	34.0	35.2	37.6	38.8	40.0
82.5°	25.5	25.5	23.1	21.8	23.1	25.5	26.7	27.9	27.9
85°	12.2	13.3	12.2	12.2	13.3	15.7	15.7	17.0	17.0
87.5°	3.7	3.7	4.8	4.8	6.1	6.1	6.1	6.1	7.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)