

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580124

Luminaire Tested: **HCC4W25D010MB-HM40525827-41RWWC**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580124
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-14)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W25D010MB-HM40525827-41RWWC
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2276.5 lumens
Efficiency: N/A
Efficacy: 84.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.15 / 1.21
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580124
CATALOG NUMBER: HCC4W25D010MB-HM40525827-41RWWC

Luminous Intensity Polar Plot





TEST NUMBER: P580124

CATALOG NUMBER: HCC4W25D010MB-HM40525827-41RWWC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	103	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88								
2	102	95	90	85	100	94	88	84	90	86	82	87	83	80	84	81	78	76								
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67								
4	87	77	69	63	85	76	68	63	73	67	62	71	66	61	69	64	60	58								
5	81	70	62	56	79	68	61	55	66	60	55	65	59	54	63	58	54	52								
6	75	63	55	49	74	62	55	49	61	54	49	59	53	48	58	52	48	46								
7	70	58	50	44	69	57	49	44	56	49	44	54	48	44	53	47	43	41								
8	66	53	45	40	64	53	45	40	51	44	40	50	44	39	49	43	39	37								
9	62	49	42	36	60	49	41	36	47	41	36	46	40	36	45	40	36	34								
10	58	46	38	33	57	45	38	33	44	38	33	43	37	33	42	37	33	31								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	134743	134743	134743
5°	140198	135988	134527
10°	144775	137197	134241
15°	149865	137606	134222
20°	150373	134294	132548
25°	145066	127577	128598
30°	134993	118799	122160
35°	121606	108702	112692
40°	107205	98896	103405
45°	93742	89102	93481
50°	82993	80153	84432
55°	73008	70793	73653
60°	65200	60464	62265
65°	57292	49120	48274
70°	50057	36208	33034
75°	41462	21779	17585
80°	31467	8453	5185
85°	14718	2123	2123



TEST NUMBER: P580124
 CATALOG NUMBER: HCC4W25D010MB-HM40525827-41RWWC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	105.4	4.6
10°-20°	307.5	13.5
20°-30°	445.3	19.6
30°-40°	469.8	20.6
40°-50°	406.6	17.9
50°-60°	301.2	13.2
60°-70°	173.6	7.6
70°-80°	60.6	2.7
80°-90°	6.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	858.2	37.7
0°-40°	1328.0	58.3
0°-60°	2035.8	89.4
0°-90°	2276.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2276.5	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1092	1092	1092	1092	1092	
5°	1132	1118	1098	1090	1086	109
15°	1174	1135	1078	1053	1051	330
25°	1066	1013	937	932	945	488
35°	808	771	722	738	748	504
45°	537	523	511	530	536	417
55°	340	332	329	341	342	306
65°	196	184	168	159	165	196
75°	87	74	46	37	37	94
85°	10	6	2	2	2	16
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P580124

CATALOG NUMBER: HCC4W25D010MB-HM40525827-41RWWC

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	1092.4	1092.4	1092.4	1092.4	1092.4	1092.4	1092.4	1092.4	1092.4
2.5°	1108.7	1105.7	1101.3	1095.4	1089.5	1085.1	1083.6	1082.1	1082.1
5°	1132.3	1126.4	1117.5	1105.7	1098.3	1093.9	1089.5	1086.5	1086.5
7.5°	1148.5	1142.7	1129.3	1113.1	1102.8	1093.9	1088.0	1083.6	1083.6
10°	1155.9	1148.5	1132.3	1111.6	1095.4	1083.6	1074.7	1071.8	1071.8
12.5°	1164.8	1155.9	1133.7	1107.2	1086.5	1071.8	1063.0	1060.0	1060.0
15°	1173.6	1163.3	1135.2	1104.3	1077.6	1060.0	1052.6	1051.1	1051.1
17.5°	1169.2	1155.9	1123.5	1086.5	1057.0	1039.2	1031.9	1031.9	1033.4
20°	1145.6	1132.3	1095.4	1054.0	1023.1	1009.8	1003.9	1006.8	1009.8
22.5°	1110.1	1093.9	1054.0	1014.2	981.7	969.9	969.9	974.3	978.7
25°	1065.9	1051.1	1012.7	968.5	937.4	928.6	931.5	938.9	944.9
27.5°	1015.6	999.4	959.5	918.2	887.3	882.8	890.2	900.5	903.4
30°	947.8	934.5	900.5	860.6	834.1	832.6	842.9	850.4	857.7
32.5°	882.8	868.1	835.6	797.2	778.0	779.5	791.3	800.1	804.5
35°	807.6	794.3	770.7	739.6	721.9	724.8	738.1	746.9	748.4
37.5°	736.7	727.8	704.2	680.6	667.2	673.2	685.0	695.4	695.4
40°	665.8	658.4	640.7	621.5	614.2	621.5	633.4	642.2	642.2
42.5°	597.9	593.5	578.7	565.4	561.0	571.3	581.7	589.0	587.5
45°	537.4	532.9	522.6	512.2	510.8	521.1	530.0	534.4	535.9
47.5°	482.8	479.8	470.9	463.6	463.6	473.8	481.3	485.7	487.2
50°	432.5	429.6	422.2	416.3	417.7	428.1	434.0	438.5	440.0
52.5°	382.4	380.9	374.9	367.6	372.0	379.5	386.8	389.7	391.2
55°	339.5	339.5	332.2	326.3	329.2	336.6	341.1	342.5	342.5
57.5°	301.1	299.6	290.8	285.0	286.4	293.8	296.7	298.2	298.2
60°	264.3	262.8	253.9	245.1	245.1	249.5	251.0	252.4	252.4
62.5°	228.8	227.4	217.0	209.7	206.7	205.3	205.3	208.2	214.1
65°	196.3	194.9	184.5	172.7	168.3	163.8	159.4	162.4	165.4
67.5°	166.9	163.8	153.5	143.2	132.9	125.4	118.1	122.5	128.5
70°	138.8	135.8	124.0	112.2	100.4	88.6	82.6	88.6	91.6
72.5°	112.2	109.3	97.4	85.6	70.9	59.0	57.6	59.0	60.5
75°	87.0	85.6	73.8	60.5	45.7	36.9	36.9	36.9	36.9
77.5°	64.9	62.0	50.2	38.4	26.5	20.7	19.2	19.2	19.2
80°	44.3	41.3	31.0	22.1	11.9	8.8	8.8	7.3	7.3
82.5°	25.1	23.6	16.3	8.8	4.4	2.9	2.9	2.9	2.9
85°	10.4	8.8	5.9	2.9	1.5	1.5	1.5	1.5	1.5
87.5°	1.5	1.5	1.5	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)