

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580125

Luminaire Tested: **HCC4W25D010MW-HM40525827-41RWWH**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580125
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-15)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W25D010MW-HM40525827-41RWWH
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2264.7 lumens
Efficiency: N/A
Efficacy: 84.5 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.08 / 1.16
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580125
CATALOG NUMBER: HCC4W25D010MW-HM40525827-41RWWH

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P580125

CATALOG NUMBER: HCC4W25D010MW-HM40525827-41RWWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	104	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88																			
2	103	96	90	85	100	94	89	84	90	86	82	87	84	80	84	81	79	77																			
3	95	86	79	73	92	84	78	73	81	76	71	79	74	70	76	72	69	67																			
4	88	77	70	64	86	76	69	63	74	67	62	71	66	62	69	65	61	59																			
5	81	70	62	56	79	69	61	56	67	60	55	65	59	55	63	58	54	52																			
6	76	64	56	50	74	63	55	50	61	54	49	60	54	49	58	53	49	47																			
7	71	58	51	45	69	58	50	45	56	49	45	55	49	44	54	48	44	42																			
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38																			
9	62	50	42	37	61	49	42	37	48	41	37	47	41	37	46	41	37	35																			
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32																			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	146559	146559	146559
5°	150400	146574	143826
10°	153805	145313	139564
15°	158140	143250	135895
20°	157711	137746	130382
25°	151054	128965	124134
30°	138966	118770	117517
35°	122239	107798	108687
40°	105772	96497	100522
45°	91911	85736	90882
50°	81573	75625	80729
55°	72385	66320	69202
60°	64460	57553	57553
65°	57292	47807	44801
70°	49516	36208	31917
75°	41462	23876	19682
80°	31467	11578	10513
85°	16841	4104	4104



TEST NUMBER: P580125

CATALOG NUMBER: HCC4W25D010MW-HM40525827-41RWWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	112.5	5.0
10°-20°	319.0	14.1
20°-30°	449.9	19.9
30°-40°	464.8	20.5
40°-50°	394.0	17.4
50°-60°	286.7	12.7
60°-70°	167.5	7.4
70°-80°	62.2	2.7
80°-90°	8.1	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	881.4	38.9
0°-40°	1346.2	59.4
0°-60°	2026.8	89.5
0°-90°	2264.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2264.7	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1188	1188	1188	1188	1188	
5°	1215	1204	1184	1166	1162	116
15°	1238	1200	1122	1074	1064	348
25°	1110	1048	948	914	912	508
35°	812	776	716	717	722	507
45°	527	512	492	509	521	410
55°	337	320	308	319	322	303
65°	196	180	164	154	154	195
75°	87	72	50	40	41	94
85°	12	7	3	3	3	16
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P580125

CATALOG NUMBER: HCC4W25D010MW-HM40525827-41RWWH

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	1188.2	1188.2	1188.2	1188.2	1188.2	1188.2	1188.2	1188.2	1188.2
2.5°	1198.5	1195.5	1192.6	1188.2	1182.3	1177.9	1173.4	1170.4	1170.4
5°	1214.7	1210.3	1204.4	1194.0	1183.8	1174.8	1166.0	1161.6	1161.6
7.5°	1226.5	1220.7	1208.8	1194.0	1176.4	1163.1	1149.8	1143.9	1141.0
10°	1228.0	1222.1	1205.9	1183.8	1160.2	1139.5	1124.7	1115.9	1114.3
12.5°	1230.9	1223.6	1202.9	1171.9	1141.0	1115.9	1099.6	1090.7	1087.8
15°	1238.4	1228.0	1200.0	1160.2	1121.8	1092.2	1074.5	1067.1	1064.2
17.5°	1230.9	1216.2	1182.3	1135.0	1092.2	1059.8	1042.1	1034.6	1034.6
20°	1201.5	1186.7	1146.8	1095.1	1049.4	1018.5	1000.7	996.3	993.3
22.5°	1160.2	1143.9	1101.1	1046.5	1000.7	972.6	960.9	955.0	953.4
25°	1109.9	1093.7	1047.9	991.8	947.6	924.0	913.6	913.6	912.1
27.5°	1053.8	1033.1	986.0	937.3	894.4	876.8	872.3	872.3	873.7
30°	975.7	960.9	921.0	873.7	833.9	822.1	822.1	825.1	825.1
32.5°	891.5	881.2	845.7	804.4	773.4	766.0	769.0	774.9	776.4
35°	811.8	800.0	776.4	739.5	715.9	712.9	717.4	721.8	721.8
37.5°	733.5	721.8	705.5	676.0	658.3	659.8	665.7	671.5	676.0
40°	656.9	647.9	636.2	612.5	599.3	605.1	612.5	618.5	624.3
42.5°	588.9	580.1	571.2	553.5	544.6	552.0	560.9	566.8	572.6
45°	526.9	521.0	512.1	497.4	491.5	498.9	509.2	515.2	521.0
47.5°	473.8	470.8	459.1	445.7	442.8	450.1	459.1	466.4	470.8
50°	425.1	420.7	410.3	397.1	394.1	405.9	411.7	416.3	420.7
52.5°	377.9	373.5	361.6	349.8	349.8	358.7	363.1	364.6	369.0
55°	336.6	332.2	320.3	311.4	308.4	315.9	318.8	318.8	321.8
57.5°	298.2	293.8	281.9	271.6	270.1	274.6	274.6	274.6	276.0
60°	261.3	256.8	245.0	236.2	233.3	234.7	233.3	231.8	233.3
62.5°	227.3	222.9	211.0	200.7	197.8	197.8	193.4	191.9	193.4
65°	196.3	188.9	180.1	169.7	163.8	159.4	153.5	153.5	153.5
67.5°	165.3	159.4	149.0	138.8	131.4	124.0	115.2	118.1	119.6
70°	137.3	132.9	121.0	110.8	100.4	91.6	84.1	87.0	88.5
72.5°	112.2	106.2	96.0	84.1	75.3	63.4	59.0	62.0	62.0
75°	87.0	81.2	72.4	60.5	50.1	39.9	39.9	41.3	41.3
77.5°	64.9	59.0	50.1	39.9	31.0	23.6	25.1	25.1	25.1
80°	44.3	39.9	32.5	23.6	16.3	13.3	13.3	13.3	14.8
82.5°	25.1	22.1	17.7	11.9	7.3	7.3	7.3	7.3	7.3
85°	11.9	8.8	7.3	4.4	2.9	2.9	2.9	2.9	2.9
87.5°	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)