

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580127

Luminaire Tested: **HCC4W25D010MB-HM40525827-41WWW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580127
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W25D010MB-HM40525827-41WWW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2241.1 lumens
Efficiency: N/A
Efficacy: 83.6 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.03 / 1.1
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580127
CATALOG NUMBER: HCC4W25D010MB-HM40525827-41WWW

Luminous Intensity Polar Plot





TEST NUMBER: P580127

CATALOG NUMBER: HCC4W25D010MB-HM40525827-41WWW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100				
1	111	106	103	100	108	104	101	98	100	97	95	96	94	92	93	91	89	87				87				
2	102	95	89	84	100	93	88	83	90	85	81	87	83	80	84	81	78	76				76				
3	94	85	78	72	92	84	77	72	81	75	71	78	73	69	76	72	68	66				66				
4	87	77	69	63	85	76	68	63	73	67	62	71	66	61	69	64	60	58				58				
5	81	70	62	56	79	69	61	56	67	60	55	65	59	54	63	58	54	52				52				
6	76	64	56	50	74	63	55	50	61	54	49	59	53	49	58	53	48	47				47				
7	71	58	50	45	69	58	50	45	56	49	44	55	49	44	53	48	44	42				42				
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38				38				
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35				35				
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32				32				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	154786	154786	154786
5°	161593	154102	146971
10°	165679	150899	137761
15°	169109	146864	127824
20°	168212	139728	117059
25°	161152	129210	106496
30°	148879	117958	96509
35°	130490	104922	87365
40°	113629	92713	78673
45°	98906	80869	70316
50°	88117	69695	62039
55°	78729	61288	53654
60°	70307	53532	46255
65°	62487	46960	43954
70°	54853	40464	41005
75°	46418	34504	37983
80°	35658	29336	34664
85°	20945	23068	29295



TEST NUMBER: P580127
 CATALOG NUMBER: HCC4W25D010MB-HM40525827-41WWW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	117.6	5.2
10°-20°	324.5	14.5
20°-30°	443.3	19.8
30°-40°	445.1	19.9
40°-50°	368.2	16.4
50°-60°	266.9	11.9
60°-70°	169.0	7.5
70°-80°	85.5	3.8
80°-90°	20.9	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	885.4	39.5
0°-40°	1330.5	59.4
0°-60°	1965.6	87.7
0°-90°	2241.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2241.1	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1255	1255	1255	1255	1255	
5°	1305	1286	1245	1203	1187	125
15°	1324	1273	1150	1044	1001	372
25°	1184	1106	949	830	782	541
35°	867	815	697	611	580	543
45°	567	534	464	418	403	441
55°	366	334	285	260	250	329
65°	214	190	161	145	151	213
75°	97	84	72	75	80	104
85°	15	15	16	19	21	20
90°	0	0	0	0	0	



TEST NUMBER: P580127

CATALOG NUMBER: HCC4W25D010MB-HM40525827-41WWW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	1254.9	1254.9	1254.9	1254.9	1254.9	1254.9	1254.9	1254.9	1254.9
2.5°	1278.6	1274.1	1266.7	1257.9	1247.5	1235.7	1225.4	1219.5	1216.5
5°	1305.1	1299.3	1285.9	1266.7	1244.6	1222.5	1203.3	1191.4	1187.0
7.5°	1321.4	1312.5	1293.3	1263.8	1229.8	1197.3	1169.3	1153.0	1148.6
10°	1322.8	1312.5	1287.4	1247.5	1204.8	1162.0	1128.0	1104.4	1099.9
12.5°	1324.3	1311.0	1280.1	1232.8	1179.7	1126.5	1085.2	1057.1	1049.7
15°	1324.3	1311.0	1272.6	1216.5	1150.1	1089.6	1043.8	1011.4	1001.0
17.5°	1312.5	1297.8	1251.9	1187.0	1114.7	1046.8	993.6	959.6	949.4
20°	1281.5	1265.3	1213.6	1142.8	1064.5	993.6	940.5	905.0	891.8
22.5°	1237.3	1218.1	1163.4	1086.7	1008.4	936.1	884.3	847.4	835.7
25°	1184.1	1164.9	1105.9	1030.6	949.4	881.4	829.7	795.8	782.5
27.5°	1119.1	1098.4	1040.8	965.5	890.2	822.4	775.1	744.1	730.8
30°	1045.3	1023.1	968.6	896.2	828.2	763.3	717.5	692.4	677.6
32.5°	959.6	940.5	891.8	826.8	763.3	701.3	662.9	640.7	629.0
35°	866.6	856.3	815.0	758.9	696.8	645.2	611.2	590.6	580.2
37.5°	784.0	773.6	738.1	690.9	636.3	589.1	561.0	543.3	534.5
40°	705.7	696.8	662.9	623.0	575.8	534.5	510.9	497.6	488.6
42.5°	629.0	624.6	596.5	559.5	518.2	482.8	463.6	453.3	445.8
45°	567.0	561.0	534.5	499.0	463.6	434.1	417.8	410.4	403.1
47.5°	512.3	504.9	476.9	445.8	413.4	386.8	372.0	364.7	361.7
50°	459.2	451.8	426.6	395.7	363.2	344.0	332.2	324.8	323.3
52.5°	411.9	404.5	376.5	346.9	321.9	305.6	295.2	287.9	285.0
55°	366.1	357.3	333.6	305.6	285.0	270.2	259.9	252.4	249.5
57.5°	324.8	315.9	295.2	268.7	249.5	236.2	227.4	219.9	217.0
60°	285.0	277.5	258.3	233.3	217.0	205.3	196.3	190.5	187.5
62.5°	248.0	242.2	223.0	200.7	187.5	177.1	169.8	163.9	166.9
65°	214.1	208.2	190.5	171.3	160.9	150.6	144.7	144.7	150.6
67.5°	181.5	175.7	160.9	144.7	135.8	128.5	124.0	128.5	132.9
70°	152.1	146.2	132.9	119.6	112.2	106.4	106.4	110.8	113.7
72.5°	124.0	118.1	107.8	97.4	91.6	87.2	91.6	94.5	97.4
75°	97.4	93.0	84.1	76.8	72.4	70.9	75.3	78.2	79.7
77.5°	72.4	69.4	63.4	57.6	54.6	56.1	60.5	62.0	63.4
80°	50.2	48.8	44.3	41.3	41.3	42.8	45.7	47.2	48.8
82.5°	31.0	31.0	28.0	26.5	28.0	31.0	32.5	34.0	34.0
85°	14.8	16.3	14.8	14.8	16.3	19.2	19.2	20.7	20.7
87.5°	4.4	4.4	5.9	5.9	7.3	7.3	7.3	7.3	8.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)