

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580147

Luminaire Tested: **HCC4S25D010SL-HM40525835-41WDBB**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P580147  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-11)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC4S25D010SL-HM40525835-41WDBB  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, BLACK BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2149.7 lumens  
Efficiency: N/A  
Efficacy: 80.2 lumens/watt  
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.03  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 26.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P580147  
CATALOG NUMBER: HCC4S25D010SL-HM40525835-41WDBB

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P580147

CATALOG NUMBER: HCC4S25D010SL-HM40525835-41WDBB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20								
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	99	97	97	96	94	94	93	93	91	91	89	89	87	87	85										
	1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93	93	91	89	87	85	82	80	78	78	75	75	72	72	72	72											
	2	107	102	97	94	105	100	96	93	97	93	91	94	91	89	91	89	87	85	85	82	80	78	78	75	72	72	72	72	72	72	72	72	72											
	3	101	94	89	84	99	93	88	84	90	86	82	87	84	81	85	82	80	78	78	75	75	72	72	72	72	72	72	72	72	72	72	72	72	72										
	4	95	87	81	77	93	86	80	76	84	79	75	82	78	74	80	76	73	72	72	72	72	72	72	72	72	72	72	72	72	72	72	72	72	72	72									
	5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66	66	66	66	66	66	66	66	66	66	66	66	66	66	66	66	66	66									
	6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61	61	61	61	61	61	61	61	61	61	61	61	61	61	61	61	61	61									
	7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56	56	56	56	56	56	56	56	56	56	56	56	56	56	56	56	56	56									
	8	76	65	59	55	74	65	59	54	64	58	54	63	58	54	62	57	54	52	52	52	52	52	52	52	52	52	52	52	52	52	52	52	52	52	52									
	9	72	61	55	51	71	61	55	51	60	54	50	59	54	50	58	53	50	49	49	49	49	49	49	49	49	49	49	49	49	49	49	49	49	49	49									
	10	68	58	51	47	67	57	51	47	56	51	47	55	50	47	55	50	47	45	45	45	45	45	45	45	45	45	45	45	45	45	45	45	45	45	45									

**AVERAGE LUMINANCE (cd/sqm):**

	0°	
0°	214387	
5°	214587	
10°	214989	
15°	218144	
20°	212710	
25°	199559	
30°	176524	
35°	134240	
40°	84566	
45°	48563	
50°	25752	
55°	10688	
60°	2862	
65°	2393	
70°	1803	
75°	1573	
80°	1208	
85°	2406	



TEST NUMBER: P580147  
 CATALOG NUMBER: HCC4S25D010SL-HM40525835-41WDBB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	164.8	7.7
10°-20°	478.3	22.3
20°-30°	667.6	31.1
30°-40°	549.4	25.6
40°-50°	226.3	10.5
50°-60°	50.9	2.4
60°-70°	8.2	0.4
70°-80°	3.1	0.1
80°-90°	1.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1310.7	61.0
0°-40°	1860.1	86.5
0°-60°	2137.3	99.4
0°-90°	2149.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2149.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1738	
5°	1733	165
15°	1708	478
25°	1466	668
35°	892	549
45°	278	226
55°	50	51
65°	8	8
75°	3	3
85°	2	1
90°	0	



TEST NUMBER: P580147  
CATALOG NUMBER: HCC4S25D010SL-HM40525835-41WDBB

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1738.1
2.5°	1729.9
5°	1733.1
7.5°	1726.5
10°	1716.5
12.5°	1711.6
15°	1708.3
17.5°	1678.5
20°	1620.5
22.5°	1547.5
25°	1466.3
27.5°	1368.6
30°	1239.4
32.5°	1080.3
35°	891.5
37.5°	700.9
40°	525.2
42.5°	382.7
45°	278.4
47.5°	198.8
50°	134.2
52.5°	84.4
55°	49.7
57.5°	24.8
60°	11.6
62.5°	9.9
65°	8.2
67.5°	6.7
70°	5.0
72.5°	3.3
75°	3.3
77.5°	1.7
80°	1.7
82.5°	1.7
85°	1.7
87.5°	0.0
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)