

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580145

Luminaire Tested: **HCC4S25D010BZ-HM40525830-41WWW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580145
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4S25D010BZ-HM40525830-41WWW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2427.3 lumens
Efficiency: N/A
Efficacy: 90.6 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.03 / 1.1
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580145
CATALOG NUMBER: HCC4S25D010BZ-HM40525830-41WWW

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P580145

CATALOG NUMBER: HCC4S25D010BZ-HM40525830-41WWW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	106	103	100	108	104	101	98	100	97	95	96	94	92	93	91	89	87								
2	102	95	89	84	100	93	88	83	90	85	81	87	83	80	84	81	78	76								
3	94	85	78	72	92	84	77	72	81	75	71	78	73	69	76	72	68	66								
4	87	77	69	63	85	76	68	63	73	67	62	71	66	61	69	64	60	58								
5	81	70	62	56	79	69	61	56	67	60	55	65	59	54	63	58	54	52								
6	76	64	56	50	74	63	55	50	61	54	49	59	53	49	58	53	48	47								
7	71	58	50	45	69	58	50	45	56	49	44	55	49	44	53	48	44	42								
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38								
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35								
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	167651	167651	167651
5°	175027	166905	159191
10°	179456	163437	149208
15°	183168	159072	138449
20°	182191	151332	126786
25°	174531	139935	115342
30°	161256	127771	104542
35°	141347	113641	94623
40°	123065	100426	85226
45°	107122	87585	76159
50°	95428	75471	67200
55°	85287	66385	58127
60°	76154	57997	50103
65°	67682	50871	47602
70°	59397	43818	44431
75°	50326	37363	41176
80°	38641	31822	37434
85°	22644	24908	31701



TEST NUMBER: P580145
 CATALOG NUMBER: HCC4S25D010BZ-HM40525830-41WWW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	127.4	5.2
10°-20°	351.4	14.5
20°-30°	480.1	19.8
30°-40°	482.1	19.9
40°-50°	398.8	16.4
50°-60°	289.0	11.9
60°-70°	183.1	7.5
70°-80°	92.6	3.8
80°-90°	22.7	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	959.0	39.5
0°-40°	1441.1	59.4
0°-60°	2129.0	87.7
0°-90°	2427.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2427.3	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1359	1359	1359	1359	1359	
5°	1414	1393	1348	1303	1286	135
15°	1434	1378	1246	1131	1084	403
25°	1282	1198	1028	899	848	586
35°	939	883	755	662	628	588
45°	614	579	502	452	437	478
55°	397	361	309	282	270	357
65°	232	206	174	157	163	231
75°	106	91	78	82	86	113
85°	16	16	18	21	22	22
90°	0	0	0	0	0	



TEST NUMBER: P580145

CATALOG NUMBER: HCC4S25D010BZ-HM40525830-41WWW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	1359.2	1359.2	1359.2	1359.2	1359.2	1359.2	1359.2	1359.2	1359.2
2.5°	1384.8	1380.0	1372.1	1362.5	1351.2	1338.4	1327.3	1320.8	1317.7
5°	1413.6	1407.2	1392.8	1372.1	1348.0	1324.1	1303.3	1290.4	1285.7
7.5°	1431.2	1421.6	1400.9	1368.8	1332.1	1296.9	1266.5	1248.9	1244.0
10°	1432.8	1421.6	1394.4	1351.2	1304.9	1258.5	1221.7	1196.2	1191.3
12.5°	1434.4	1420.1	1386.4	1335.3	1277.7	1220.1	1175.3	1144.9	1137.0
15°	1434.4	1420.1	1378.4	1317.7	1245.7	1180.1	1130.6	1095.4	1084.2
17.5°	1421.6	1405.6	1356.0	1285.7	1207.4	1133.7	1076.2	1039.5	1028.2
20°	1388.0	1370.4	1314.5	1237.7	1152.9	1076.2	1018.6	980.2	965.9
22.5°	1340.0	1319.2	1260.1	1177.0	1092.2	1013.8	957.8	917.9	905.1
25°	1282.4	1261.7	1197.8	1116.1	1028.2	954.7	898.7	861.9	847.5
27.5°	1212.1	1189.7	1127.4	1045.8	964.3	890.7	839.5	806.0	791.5
30°	1132.2	1108.2	1049.0	970.6	897.1	826.8	777.2	750.0	734.0
32.5°	1039.5	1018.6	965.9	895.5	826.8	759.6	718.0	694.0	681.2
35°	938.7	927.5	882.7	821.9	754.7	698.9	662.0	639.7	628.4
37.5°	849.1	837.9	799.6	748.4	689.3	638.0	607.6	588.4	578.8
40°	764.3	754.7	718.0	674.8	623.7	578.8	553.3	538.9	529.3
42.5°	681.2	676.4	646.0	606.0	561.3	523.0	502.1	490.9	482.9
45°	614.1	607.6	578.8	540.5	502.1	470.1	452.5	444.6	436.6
47.5°	554.9	546.9	516.5	482.9	447.8	419.0	402.9	394.9	391.8
50°	497.3	489.3	462.1	428.6	393.3	372.6	359.8	351.8	350.2
52.5°	446.2	438.2	407.8	375.8	348.6	331.0	319.8	311.8	308.7
55°	396.6	387.0	361.4	331.0	308.7	292.6	281.5	273.4	270.3
57.5°	351.8	342.2	319.8	291.1	270.3	255.8	246.2	238.2	235.1
60°	308.7	300.7	279.9	252.7	235.1	222.3	212.7	206.3	203.1
62.5°	268.7	262.3	241.5	217.4	203.1	191.9	183.9	177.5	180.8
65°	231.9	225.5	206.3	185.5	174.3	163.1	156.7	156.7	163.1
67.5°	196.7	190.3	174.3	156.7	147.1	139.1	134.4	139.1	143.9
70°	164.7	158.3	143.9	129.5	121.5	115.2	115.2	119.9	123.2
72.5°	134.4	127.9	116.7	105.6	99.1	94.4	99.1	102.3	105.6
75°	105.6	100.7	91.1	83.2	78.4	76.8	81.5	84.8	86.4
77.5°	78.4	75.2	68.8	62.3	59.2	60.7	65.6	67.2	68.8
80°	54.4	52.7	48.0	44.8	44.8	46.4	49.6	51.1	52.7
82.5°	33.5	33.5	30.4	28.8	30.4	33.5	35.2	36.8	36.8
85°	16.0	17.6	16.0	16.0	17.6	20.8	20.8	22.4	22.4
87.5°	4.7	4.7	6.4	6.4	8.0	8.0	8.0	8.0	9.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)