

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580161

Luminaire Tested: **HCC4W25D010MB-HM40525835-41RWWH**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580161
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-15)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W25D010MB-HM40525835-41RWWH
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2542.5 lumens
Efficiency: N/A
Efficacy: 94.9 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.08 / 1.16
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580161
CATALOG NUMBER: HCC4W25D010MB-HM40525835-41RWWH

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P580161

CATALOG NUMBER: HCC4W25D010MB-HM40525835-41RWWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	111	107	104	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88				88
2	103	96	90	85	100	94	89	84	90	86	82	87	84	80	84	81	79	77				77
3	95	86	79	73	92	84	78	73	81	76	71	79	74	70	76	72	69	67				67
4	88	77	70	64	86	76	69	63	74	67	62	71	66	62	69	65	61	59				59
5	81	70	62	56	79	69	61	56	67	60	55	65	59	55	63	58	54	52				52
6	76	64	56	50	74	63	55	50	61	54	49	60	54	49	58	53	49	47				47
7	71	58	51	45	69	58	50	45	56	49	45	55	49	44	54	48	44	42				42
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38				38
9	62	50	42	37	61	49	42	37	48	41	37	47	41	37	46	41	37	35				35
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32				32

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	164531	164531	164531
5°	168861	164540	161469
10°	172680	163124	156686
15°	177537	160821	152559
20°	177046	154653	146383
25°	169590	144793	139377
30°	156015	133355	131930
35°	137236	121019	122013
40°	118717	108332	112872
45°	103197	96272	102028
50°	91571	84912	90630
55°	81245	74492	77696
60°	72355	64584	64584
65°	64326	53673	50288
70°	55574	40644	35884
75°	46609	26831	22113
80°	35303	12928	11791
85°	18681	4670	4670



TEST NUMBER: P580161
 CATALOG NUMBER: HCC4W25D010MB-HM40525835-41RWWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.3	5.0
10°-20°	358.1	14.1
20°-30°	505.1	19.9
30°-40°	521.8	20.5
40°-50°	442.3	17.4
50°-60°	321.8	12.7
60°-70°	188.0	7.4
70°-80°	69.9	2.7
80°-90°	9.1	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	989.6	38.9
0°-40°	1511.3	59.4
0°-60°	2275.4	89.5
0°-90°	2542.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2542.5	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1334	1334	1334	1334	1334	
5°	1364	1352	1329	1309	1304	131
15°	1390	1347	1259	1206	1195	391
25°	1246	1176	1064	1026	1024	570
35°	911	872	804	805	810	569
45°	592	575	552	572	585	460
55°	378	360	346	358	361	340
65°	220	202	184	172	172	219
75°	98	81	56	45	46	105
85°	13	8	3	3	3	18
90°	0	0	0	0	0	



TEST NUMBER: P580161

CATALOG NUMBER: HCC4W25D010MB-HM40525835-41RWWH

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	1333.9	1333.9	1333.9	1333.9	1333.9	1333.9	1333.9	1333.9	1333.9
2.5°	1345.5	1342.3	1338.9	1333.9	1327.4	1322.4	1317.4	1314.0	1314.0
5°	1363.8	1358.8	1352.2	1340.6	1328.9	1319.0	1309.1	1304.1	1304.1
7.5°	1377.0	1370.4	1357.2	1340.6	1320.7	1305.8	1290.9	1284.2	1281.0
10°	1378.7	1372.1	1353.8	1328.9	1302.4	1279.3	1262.7	1252.7	1251.0
12.5°	1382.0	1373.8	1350.5	1315.7	1281.0	1252.7	1234.6	1224.6	1221.2
15°	1390.3	1378.7	1347.2	1302.4	1259.4	1226.2	1206.3	1198.1	1194.7
17.5°	1382.0	1365.4	1327.4	1274.3	1226.2	1189.7	1169.9	1161.6	1161.6
20°	1348.8	1332.3	1287.5	1229.6	1178.2	1143.3	1123.5	1118.5	1115.2
22.5°	1302.4	1284.2	1236.1	1174.8	1123.5	1092.0	1078.8	1072.1	1070.5
25°	1246.1	1227.9	1176.5	1113.5	1063.9	1037.3	1025.7	1025.7	1024.1
27.5°	1183.2	1159.9	1107.0	1052.2	1004.2	984.3	979.3	979.3	981.0
30°	1095.4	1078.8	1034.1	981.0	936.3	923.0	923.0	926.3	926.3
32.5°	1000.9	989.2	949.5	903.1	868.3	860.1	863.3	870.0	871.6
35°	911.4	898.1	871.6	830.2	803.7	800.3	805.3	810.3	810.3
37.5°	823.6	810.3	792.1	758.9	739.0	740.7	747.4	753.9	758.9
40°	737.3	727.4	714.2	687.7	672.8	679.4	687.7	694.3	701.0
42.5°	661.1	651.2	641.3	621.4	611.5	619.7	629.6	636.3	643.0
45°	591.6	584.9	575.0	558.4	551.9	560.1	571.7	578.3	584.9
47.5°	531.9	528.6	515.4	500.5	497.1	505.5	515.4	523.6	528.6
50°	477.2	472.3	460.6	445.7	442.5	455.7	462.3	467.3	472.3
52.5°	424.2	419.2	406.0	392.8	392.8	402.7	407.7	409.3	414.2
55°	377.8	372.8	359.6	349.7	346.4	354.6	357.9	357.9	361.3
57.5°	334.7	329.8	316.5	304.9	303.2	308.2	308.2	308.2	309.9
60°	293.3	288.3	275.0	265.1	261.8	263.5	261.8	260.1	261.8
62.5°	255.2	250.2	237.0	225.3	222.1	222.1	217.1	215.4	217.1
65°	220.4	212.1	202.2	190.6	183.9	178.9	172.3	172.3	172.3
67.5°	185.6	178.9	167.3	155.8	147.4	139.2	129.3	132.5	134.2
70°	154.1	149.1	135.9	124.3	112.7	102.7	94.5	97.8	99.5
72.5°	125.9	119.3	107.7	94.5	84.6	71.2	66.3	69.5	69.5
75°	97.8	91.1	81.2	68.0	56.3	44.7	44.7	46.4	46.4
77.5°	72.9	66.3	56.3	44.7	34.8	26.5	28.2	28.2	28.2
80°	49.7	44.7	36.5	26.5	18.2	14.9	14.9	14.9	16.6
82.5°	28.2	24.8	19.9	13.2	8.2	8.2	8.2	8.2	8.2
85°	13.2	9.9	8.2	5.0	3.3	3.3	3.3	3.3	3.3
87.5°	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)