

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580142

Luminaire Tested: **HCC4W25D010SL-HM40525830-41RWWC**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580142
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-14)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W25D010SL-HM40525830-41RWWC
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2465.7 lumens
Efficiency: N/A
Efficacy: 92.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.15 / 1.21
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580142
CATALOG NUMBER: HCC4W25D010SL-HM40525830-41RWWC

Luminous Intensity Polar Plot





TEST NUMBER: P580142

CATALOG NUMBER: HCC4W25D010SL-HM40525830-41RWWC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	111	107	103	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88	88	88	88
2	102	95	90	85	100	94	88	84	90	86	82	87	83	80	84	81	78	76	76	76	76
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67	67	67	67
4	87	77	69	63	85	76	68	63	73	67	62	71	66	61	69	64	60	58	58	58	58
5	81	70	61	56	79	68	61	55	66	60	55	65	59	54	63	58	54	52	52	52	52
6	75	63	55	49	74	62	55	49	61	54	49	59	53	48	58	52	48	46	46	46	46
7	70	58	50	44	69	57	49	44	56	49	44	54	48	44	53	47	43	41	41	41	41
8	66	53	45	40	64	53	45	40	51	44	40	50	44	39	49	43	39	37	37	37	37
9	62	49	42	36	60	49	41	36	47	41	36	46	40	36	45	40	36	34	34	34	34
10	58	46	38	33	57	45	38	33	44	38	33	43	37	33	42	37	33	31	31	31	31

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	145943	145943	145943
5°	151849	147292	145720
10°	156799	148607	145388
15°	162315	149060	145383
20°	162869	145451	143561
25°	157110	138179	139268
30°	146202	128669	132329
35°	131695	117736	122058
40°	116109	107108	112003
45°	101522	96499	101243
50°	89901	86831	91417
55°	79073	76664	79782
60°	70603	65472	67445
65°	62079	53206	52272
70°	54204	39201	35739
75°	44988	23638	19063
80°	34095	9092	5683
85°	15851	2264	2264



TEST NUMBER: P580142

CATALOG NUMBER: HCC4W25D010SL-HM40525830-41RWWC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	114.1	4.6
10°-20°	333.1	13.5
20°-30°	482.3	19.6
30°-40°	508.9	20.6
40°-50°	440.4	17.9
50°-60°	326.3	13.2
60°-70°	188.1	7.6
70°-80°	65.7	2.7
80°-90°	6.9	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	929.5	37.7
0°-40°	1438.4	58.3
0°-60°	2205.1	89.4
0°-90°	2465.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2465.7	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1183	1183	1183	1183	1183	
5°	1226	1210	1190	1180	1177	118
15°	1271	1230	1167	1140	1138	358
25°	1154	1097	1015	1009	1023	528
35°	875	835	782	799	811	546
45°	582	566	553	574	580	452
55°	368	360	356	369	371	332
65°	213	200	182	173	179	212
75°	94	80	50	40	40	102
85°	11	6	2	2	2	17
90°	0	0	0	0	0	



TEST NUMBER: P580142

CATALOG NUMBER: HCC4W25D010SL-HM40525830-41RWWC

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	1183.2	1183.2	1183.2	1183.2	1183.2	1183.2	1183.2	1183.2	1183.2
2.5°	1200.8	1197.6	1192.8	1186.5	1180.0	1175.3	1173.6	1172.0	1172.0
5°	1226.4	1220.0	1210.4	1197.6	1189.6	1184.9	1180.0	1176.9	1176.9
7.5°	1244.0	1237.6	1223.2	1205.7	1194.5	1184.9	1178.5	1173.6	1173.6
10°	1251.9	1244.0	1226.4	1204.1	1186.5	1173.6	1164.0	1160.8	1160.8
12.5°	1261.5	1251.9	1228.0	1199.2	1176.9	1160.8	1151.2	1148.1	1148.1
15°	1271.1	1260.0	1229.6	1196.1	1167.3	1148.1	1140.1	1138.5	1138.5
17.5°	1266.4	1251.9	1216.8	1176.9	1144.9	1125.7	1117.7	1117.7	1119.3
20°	1240.8	1226.4	1186.5	1141.6	1108.1	1093.7	1087.3	1090.5	1093.7
22.5°	1202.4	1184.9	1141.6	1098.5	1063.3	1050.5	1050.5	1055.3	1060.1
25°	1154.4	1138.5	1096.9	1049.0	1015.3	1005.7	1009.0	1016.9	1023.3
27.5°	1100.1	1082.5	1039.4	994.5	961.0	956.2	964.2	975.3	978.6
30°	1026.5	1012.1	975.3	932.2	903.4	901.8	913.0	921.0	929.1
32.5°	956.2	940.2	905.0	863.5	842.7	844.3	857.0	866.6	871.5
35°	874.6	860.3	834.7	801.1	781.9	785.1	799.4	809.0	810.6
37.5°	797.9	788.3	762.8	737.1	722.8	729.1	741.9	753.2	753.2
40°	721.1	713.2	694.0	673.2	665.2	673.2	686.0	695.6	695.6
42.5°	647.6	642.7	626.8	612.4	607.6	618.8	630.0	638.0	636.4
45°	582.0	577.3	566.1	554.8	553.2	564.4	574.0	578.8	580.4
47.5°	522.8	519.7	510.1	502.1	502.1	513.2	521.3	526.1	527.7
50°	468.5	465.3	457.4	450.9	452.5	463.7	470.1	474.9	476.4
52.5°	414.1	412.5	406.1	398.2	402.9	411.0	419.0	422.1	423.7
55°	367.7	367.7	359.8	353.4	356.5	364.6	369.4	371.0	371.0
57.5°	326.2	324.6	315.0	308.6	310.2	318.2	321.4	323.0	323.0
60°	286.2	284.6	275.0	265.4	265.4	270.2	271.9	273.4	273.4
62.5°	247.8	246.2	235.1	227.0	223.9	222.3	222.3	225.5	231.9
65°	212.7	211.0	199.8	187.1	182.3	177.5	172.7	175.9	179.1
67.5°	180.6	177.5	166.3	155.1	143.9	135.9	127.9	132.8	139.1
70°	150.3	147.1	134.4	121.5	108.7	96.0	89.5	96.0	99.1
72.5°	121.5	118.3	105.6	92.7	76.8	64.0	62.3	64.0	65.6
75°	94.4	92.7	79.9	65.6	49.6	40.0	40.0	40.0	40.0
77.5°	70.3	67.2	54.4	41.5	28.8	22.4	20.8	20.8	20.8
80°	48.0	44.8	33.5	23.9	12.8	9.6	9.6	8.0	8.0
82.5°	27.2	25.6	17.6	9.6	4.7	3.2	3.2	3.2	3.2
85°	11.2	9.6	6.4	3.2	1.6	1.6	1.6	1.6	1.6
87.5°	1.6	1.6	1.6	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)