

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580151

Luminaire Tested: **HCC4S25D010BZ-HM40525835-41WDH**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580151
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-8)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4S25D010BZ-HM40525835-41WDH
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2647.0 lumens
Efficiency: N/A
Efficacy: 98.8 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.11
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580151
CATALOG NUMBER: HCC4S25D010BZ-HM40525835-41WDH

Luminous Intensity Polar Plot





TEST NUMBER: P580151
 CATALOG NUMBER: HCC4S25D010BZ-HM40525835-41WDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	107	104	110	108	105	103	103	101	100	100	98	97	96	95	94	92			92																
2	106	101	96	92	104	99	95	91	96	92	89	93	90	87	90	88	86	84			84																
3	100	93	87	82	98	91	86	82	88	84	80	86	82	79	84	81	78	76			76																
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69			69																
5	88	79	72	67	86	78	72	67	76	70	66	74	69	66	72	68	65	63			63																
6	83	73	66	61	81	72	66	61	70	65	61	69	64	60	68	63	60	58			58																
7	78	68	61	56	77	67	60	56	65	60	55	64	59	55	63	58	55	53			53																
8	74	63	56	51	72	62	56	51	61	55	51	60	55	51	59	54	51	49			49																
9	69	59	52	47	68	58	52	47	57	51	47	56	51	47	55	50	47	45			45																
10	66	55	48	44	65	54	48	44	53	48	44	53	47	44	52	47	43	42			42																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	222553
5°	224220
10°	227025
15°	232727
20°	234446
25°	227731
30°	208798
35°	171809
40°	125238
45°	81270
50°	45824
55°	21763
60°	8585
65°	5341
70°	3570
75°	2383
80°	1208
85°	2406



TEST NUMBER: P580151
 CATALOG NUMBER: HCC4S25D010BZ-HM40525835-41WDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	172.9	6.5
10°-20°	513.8	19.4
20°-30°	762.1	28.8
30°-40°	703.9	26.6
40°-50°	367.5	13.9
50°-60°	100.7	3.8
60°-70°	19.4	0.7
70°-80°	5.5	0.2
80°-90°	1.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1448.8	54.7
0°-40°	2152.7	81.3
0°-60°	2621.0	99.0
0°-90°	2647.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2647.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1804	
5°	1811	173
15°	1822	514
25°	1673	762
35°	1141	704
45°	466	368
55°	101	101
65°	18	19
75°	5	5
85°	2	1
90°	0	



TEST NUMBER: P580151
CATALOG NUMBER: HCC4S25D010BZ-HM40525835-41WDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1804.3
2.5°	1799.3
5°	1810.9
7.5°	1815.9
10°	1812.6
12.5°	1815.9
15°	1822.5
17.5°	1815.9
20°	1786.1
22.5°	1738.0
25°	1673.3
27.5°	1585.3
30°	1466.0
32.5°	1315.1
35°	1141.0
37.5°	958.5
40°	777.8
42.5°	611.9
45°	465.9
47.5°	341.6
50°	238.8
52.5°	159.2
55°	101.2
57.5°	59.7
60°	34.8
62.5°	24.8
65°	18.3
67.5°	13.3
70°	9.9
72.5°	6.7
75°	5.0
77.5°	3.3
80°	1.7
82.5°	1.7
85°	1.7
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)