

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580163

Luminaire Tested: **HCC4W25D010MW-HM40525835-41WWW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580163
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W25D010MW-HM40525835-41WWW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2516.0 lumens
Efficiency: N/A
Efficacy: 93.9 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.03 / 1.1
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580163
CATALOG NUMBER: HCC4W25D010MW-HM40525835-41WWW

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P580163

CATALOG NUMBER: HCC4W25D010MW-HM40525835-41WWW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100				
1	111	106	103	100	108	104	101	98	100	97	95	96	94	92	93	91	89	87				87				
2	102	95	89	84	100	93	88	83	90	85	81	87	83	80	84	81	78	76				76				
3	94	85	78	72	92	84	77	72	81	75	71	78	73	69	76	72	68	66				66				
4	87	77	69	63	85	76	68	63	73	67	62	71	66	61	69	64	60	58				58				
5	81	70	62	56	79	69	61	56	67	60	55	65	59	54	63	58	54	52				52				
6	76	64	56	50	74	63	55	50	61	54	49	59	53	49	58	53	48	47				47				
7	71	58	50	45	69	58	50	45	56	49	44	55	49	44	53	48	44	42				42				
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38				38				
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35				35				
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32				32				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	173782	173782	173782
5°	181416	173009	165011
10°	186019	169399	154669
15°	189860	164882	143506
20°	188846	156858	131419
25°	180927	145052	119561
30°	167138	132429	108359
35°	146512	117812	98086
40°	127573	104097	88350
45°	111029	90794	78933
50°	98920	78253	69657
55°	88406	68815	60235
60°	78941	60094	51953
65°	70163	52710	49354
70°	61561	45440	46017
75°	52137	38698	42653
80°	39991	32959	38783
85°	23493	25757	32975



TEST NUMBER: P580163

CATALOG NUMBER: HCC4W25D010MW-HM40525835-41WWW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	132.1	5.2
10°-20°	364.3	14.5
20°-30°	497.7	19.8
30°-40°	499.8	19.9
40°-50°	413.4	16.4
50°-60°	299.6	11.9
60°-70°	189.8	7.5
70°-80°	95.9	3.8
80°-90°	23.5	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	994.0	39.5
0°-40°	1493.8	59.4
0°-60°	2206.8	87.7
0°-90°	2516.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2516.0	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1409	1409	1409	1409	1409	
5°	1465	1444	1397	1351	1333	140
15°	1487	1429	1291	1172	1124	418
25°	1329	1241	1066	932	878	608
35°	973	915	782	686	651	610
45°	636	600	520	469	452	495
55°	411	375	320	292	280	370
65°	240	214	181	162	169	239
75°	109	94	81	85	90	117
85°	17	17	18	22	23	23
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P580163

CATALOG NUMBER: HCC4W25D010MW-HM40525835-41WWW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	1408.9	1408.9	1408.9	1408.9	1408.9	1408.9	1408.9	1408.9	1408.9
2.5°	1435.4	1430.4	1422.2	1412.3	1400.6	1387.3	1375.8	1369.1	1365.8
5°	1465.2	1458.7	1443.8	1422.2	1397.3	1372.4	1350.8	1337.6	1332.7
7.5°	1483.5	1473.6	1452.0	1418.8	1380.8	1344.3	1312.8	1294.5	1289.5
10°	1485.2	1473.6	1445.3	1400.6	1352.5	1304.4	1266.4	1239.9	1234.9
12.5°	1486.8	1471.9	1437.1	1384.0	1324.3	1264.7	1218.3	1186.8	1178.5
15°	1486.8	1471.9	1428.7	1365.8	1291.2	1223.3	1171.9	1135.4	1123.8
17.5°	1473.6	1457.0	1405.6	1332.7	1251.4	1175.2	1115.6	1077.4	1065.8
20°	1438.7	1420.5	1362.5	1282.9	1195.0	1115.6	1055.8	1016.1	1001.2
22.5°	1389.0	1367.4	1306.1	1220.0	1132.0	1050.9	992.8	951.4	938.2
25°	1329.4	1307.8	1241.4	1157.0	1065.8	989.6	931.5	893.4	878.5
27.5°	1256.5	1233.2	1168.5	1084.1	999.5	923.3	870.2	835.3	820.4
30°	1173.5	1148.6	1087.3	1006.2	929.8	856.9	805.5	777.4	760.8
32.5°	1077.4	1055.8	1001.2	928.3	856.9	787.4	744.2	719.4	706.1
35°	973.0	961.3	914.9	851.9	782.4	724.4	686.2	663.1	651.4
37.5°	880.2	868.5	828.8	775.7	714.4	661.4	629.9	610.0	600.1
40°	792.3	782.4	744.2	699.5	646.5	600.1	573.5	558.6	548.7
42.5°	706.1	701.1	669.6	628.2	581.8	542.0	520.5	508.8	500.6
45°	636.5	629.9	600.1	560.2	520.5	487.3	469.1	460.7	452.5
47.5°	575.1	566.9	535.4	500.6	464.1	434.3	417.7	409.4	406.1
50°	515.5	507.3	479.0	444.3	407.8	386.2	372.9	364.7	363.0
52.5°	462.4	454.2	422.7	389.5	361.4	343.1	331.5	323.2	320.0
55°	411.1	401.1	374.6	343.1	320.0	303.4	291.7	283.5	280.1
57.5°	364.7	354.7	331.5	301.7	280.1	265.2	255.3	247.0	243.6
60°	320.0	311.6	290.0	261.9	243.6	230.4	220.5	213.8	210.6
62.5°	278.4	271.9	250.3	225.5	210.6	198.9	190.6	184.0	187.3
65°	240.4	233.7	213.8	192.3	180.6	169.1	162.5	162.5	169.1
67.5°	203.9	197.2	180.6	162.5	152.5	144.2	139.2	144.2	149.1
70°	170.7	164.0	149.1	134.2	126.0	119.3	119.3	124.3	127.6
72.5°	139.2	132.7	121.0	109.4	102.7	97.8	102.7	106.1	109.4
75°	109.4	104.4	94.5	86.1	81.2	79.6	84.6	87.8	89.5
77.5°	81.2	77.9	71.2	64.7	61.3	63.0	68.0	69.7	71.2
80°	56.3	54.6	49.7	46.4	46.4	48.1	51.4	53.1	54.6
82.5°	34.8	34.8	31.5	29.8	31.5	34.8	36.5	38.2	38.2
85°	16.6	18.2	16.6	16.6	18.2	21.6	21.6	23.3	23.3
87.5°	5.0	5.0	6.7	6.7	8.2	8.2	8.2	8.2	9.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)