

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P592709

Luminaire Tested: **HCC4W25D010MW-HM40525850-41WWWB**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P592709
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-18)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W25D010MW-HM40525850-41WWWB
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 5000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2573.6 lumens
Efficiency: N/A
Efficacy: 96.0 lumens/watt
Spacing Criteria (0/90/45): 1.13 / 1.07 / 1.15
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P592709
CATALOG NUMBER: HCC4W25D010MW-HM40525850-41WWWB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P592709

CATALOG NUMBER: HCC4W25D010MW-HM40525850-41WWWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87								
2	102	95	89	84	99	93	87	83	89	85	81	86	82	79	83	80	77	75								
3	94	85	77	72	92	83	76	71	80	75	70	78	73	69	75	71	68	66								
4	87	76	68	62	85	75	68	62	72	66	61	70	65	60	68	63	60	58								
5	81	69	61	55	79	68	60	55	66	59	54	64	58	53	62	57	53	51								
6	75	63	55	49	73	62	54	49	60	53	48	59	53	48	57	52	47	46								
7	70	58	50	44	68	57	49	44	55	48	43	54	48	43	53	47	43	41								
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37								
9	61	49	41	36	60	48	41	36	47	41	36	46	40	36	45	40	36	34								
10	58	45	38	33	57	45	38	33	44	38	33	43	37	33	42	37	33	31								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	163680	163680	163680
5°	172105	163475	157346
10°	178153	161508	150198
15°	183602	158587	143799
20°	183806	152054	135515
25°	176899	142112	127060
30°	164261	130777	118642
35°	147234	117736	109786
40°	129199	105047	101489
45°	112931	93010	93603
50°	99707	81400	84336
55°	87911	72148	75825
60°	78596	63868	66409
65°	69580	56183	56183
70°	60840	47929	47929
75°	51994	40556	45465
80°	41127	36297	41127
85°	26465	31277	38494



TEST NUMBER: P592709

CATALOG NUMBER: HCC4W25D010MW-HM40525850-41WWWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	125.7	4.9
10°-20°	354.1	13.8
20°-30°	496.0	19.3
30°-40°	511.1	19.9
40°-50°	435.1	16.9
50°-60°	322.4	12.5
60°-70°	202.3	7.9
70°-80°	100.5	3.9
80°-90°	26.4	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	975.8	37.9
0°-40°	1486.9	57.8
0°-60°	2244.4	87.2
0°-90°	2573.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2573.6	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1327	1327	1327	1327	1327	
5°	1390	1366	1320	1283	1271	134
15°	1438	1373	1242	1152	1126	404
25°	1300	1210	1044	954	934	594
35°	978	905	782	731	729	610
45°	647	603	533	523	537	502
55°	409	376	336	342	353	370
65°	238	215	192	189	192	238
75°	109	97	85	92	95	116
85°	19	19	22	26	27	24
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P592709

CATALOG NUMBER: HCC4W25D010MW-HM40525850-41WWWB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	1327.0	1327.0	1327.0	1327.0	1327.0	1327.0	1327.0	1327.0	1327.0
2.5°	1356.0	1350.8	1344.1	1332.1	1320.3	1310.0	1299.8	1294.6	1292.9
5°	1390.0	1379.9	1366.2	1344.1	1320.3	1299.8	1282.8	1274.2	1270.8
7.5°	1414.0	1403.7	1381.6	1347.5	1313.4	1282.8	1255.4	1243.6	1240.2
10°	1422.4	1410.5	1379.9	1333.8	1289.5	1252.1	1221.5	1206.1	1199.2
12.5°	1429.2	1414.0	1374.8	1320.3	1265.7	1219.7	1187.4	1166.9	1161.7
15°	1437.8	1420.7	1373.0	1306.6	1241.9	1187.4	1151.6	1132.8	1126.1
17.5°	1429.2	1410.5	1354.2	1279.4	1206.1	1146.5	1107.3	1090.3	1083.4
20°	1400.3	1379.9	1316.9	1236.7	1158.4	1097.0	1057.9	1040.8	1032.4
22.5°	1356.0	1333.8	1269.1	1184.0	1103.8	1044.2	1006.7	989.7	984.6
25°	1299.8	1277.6	1209.5	1122.6	1044.2	986.3	954.0	938.7	933.6
27.5°	1233.3	1211.2	1144.8	1059.6	984.6	930.1	904.6	889.2	885.8
30°	1153.3	1131.1	1066.3	988.0	918.2	867.1	846.6	834.7	833.0
32.5°	1064.6	1045.9	986.3	914.8	848.3	805.8	790.4	781.9	780.3
35°	977.8	957.4	904.6	839.9	781.9	744.5	730.8	729.1	729.1
37.5°	889.2	868.8	826.2	766.6	717.1	683.2	678.0	679.7	679.7
40°	802.4	783.6	746.2	696.7	652.4	626.9	625.2	628.6	630.3
42.5°	720.5	705.3	671.2	628.6	591.1	570.7	572.4	579.2	584.3
45°	647.4	633.7	603.0	565.5	533.2	517.9	523.0	531.5	536.6
47.5°	580.9	569.0	540.0	505.9	478.7	468.4	475.3	485.5	492.4
50°	519.6	509.4	482.1	446.3	424.2	417.4	425.9	436.1	439.5
52.5°	465.0	454.9	425.9	395.3	378.2	374.8	383.3	391.8	397.0
55°	408.8	400.3	376.5	349.2	335.5	333.8	342.4	349.2	352.6
57.5°	362.9	354.3	332.2	308.3	296.4	294.7	303.2	308.3	310.0
60°	318.6	310.0	289.6	267.5	258.9	258.9	264.1	267.5	269.2
62.5°	277.6	269.2	250.4	231.7	224.9	224.9	224.9	226.6	231.7
65°	238.4	231.7	214.6	197.6	192.5	189.1	189.1	189.1	192.5
67.5°	202.8	195.9	182.2	167.0	161.8	156.7	155.0	158.4	158.4
70°	168.7	163.6	149.9	138.0	132.9	127.8	126.1	132.9	132.9
72.5°	138.0	132.9	124.3	112.4	107.4	105.6	109.1	112.4	114.1
75°	109.1	103.9	97.1	90.3	85.1	86.9	92.0	93.7	95.4
77.5°	81.7	80.0	73.3	68.2	68.2	69.9	73.3	76.7	78.4
80°	57.9	56.2	52.8	49.5	51.1	54.5	56.2	59.6	57.9
82.5°	35.8	35.8	34.1	34.1	35.8	39.2	40.9	42.6	44.3
85°	18.7	18.7	18.7	20.4	22.1	23.8	25.5	27.2	27.2
87.5°	5.1	6.8	6.8	8.5	10.3	10.3	12.0	12.0	12.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)