

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580189

Luminaire Tested: **HCC4S25D010MB-HM40525927-41MDC**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P580189  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-4)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC4S25D010MB-HM40525927-41MDC  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" MEDIUM DISTRIBUTION, SPECULAR TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1950.1 lumens  
Efficiency: N/A  
Efficacy: 72.8 lumens/watt  
Spacing Criteria (0/90/45): 1 / 1 / 0.96  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 26.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P580189  
CATALOG NUMBER: HCC4S25D010MB-HM40525927-41MDC

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P580189

CATALOG NUMBER: HCC4S25D010MB-HM40525927-41MDC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20																		
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																												
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93																												
2	108	103	99	95	105	101	97	94	98	95	92	95	92	90	92	90	88	86																												
3	102	95	90	86	100	94	89	86	91	87	84	89	86	83	87	84	82	80																												
4	97	89	83	79	95	88	82	78	86	81	77	84	80	77	82	78	76	74																												
5	91	83	77	72	90	82	76	72	80	75	72	78	74	71	77	73	70	69																												
6	87	78	71	67	85	77	71	67	75	70	66	74	69	66	72	68	65	64																												
7	82	73	66	62	81	72	66	62	71	65	62	69	65	61	68	64	61	60																												
8	78	68	62	58	77	68	62	58	67	61	57	65	61	57	65	60	57	56																												
9	74	64	58	54	73	64	58	54	63	57	54	62	57	54	61	57	53	52																												
10	70	61	55	51	69	60	54	51	59	54	50	58	54	50	58	53	50	49																												

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	225895
5°	230039
10°	237120
15°	234502
20°	215322
25°	185772
30°	151400
35°	112105
40°	64294
45°	31085
50°	14795
55°	5161
60°	1875
65°	1109
70°	902
75°	572
80°	0
85°	0



TEST NUMBER: P580189  
 CATALOG NUMBER: HCC4S25D010MB-HM40525927-41MDC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	178.7	9.2
10°-20°	509.1	26.1
20°-30°	621.7	31.9
30°-40°	457.1	23.4
40°-50°	151.5	7.8
50°-60°	26.8	1.4
60°-70°	4.0	0.2
70°-80°	1.3	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1309.5	67.1
0°-40°	1766.6	90.6
0°-60°	1944.8	99.7
0°-90°	1950.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1950.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1831	
5°	1858	179
15°	1836	509
25°	1365	622
35°	744	457
45°	178	151
55°	24	27
65°	4	4
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P580189  
CATALOG NUMBER: HCC4S25D010MB-HM40525927-41MDC

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1831.4
2.5°	1832.6
5°	1857.9
7.5°	1885.7
10°	1893.2
12.5°	1875.6
15°	1836.4
17.5°	1755.5
20°	1640.4
22.5°	1506.5
25°	1365.0
27.5°	1217.1
30°	1063.0
32.5°	908.7
35°	744.5
37.5°	577.6
40°	399.3
42.5°	264.2
45°	178.2
47.5°	118.8
50°	77.1
52.5°	45.5
55°	24.0
57.5°	10.2
60°	7.6
62.5°	5.1
65°	3.8
67.5°	2.5
70°	2.5
72.5°	1.2
75°	1.2
77.5°	1.2
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)