

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580225

Luminaire Tested: **HCC4S25D010MB-HM40525935-41MDC**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P580225  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-4)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC4S25D010MB-HM40525935-41MDC  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" MEDIUM DISTRIBUTION, SPECULAR TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2285.4 lumens  
Efficiency: N/A  
Efficacy: 85.3 lumens/watt  
Spacing Criteria (0/90/45): 1 / 1 / 0.96  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 26.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P580225  
CATALOG NUMBER: HCC4S25D010MB-HM40525935-41MDC

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P580225

CATALOG NUMBER: HCC4S25D010MB-HM40525935-41MDC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93					93			
2	108	103	99	95	105	101	97	94	98	95	92	95	92	90	92	90	88	86					86			
3	102	95	90	86	100	94	89	86	91	87	84	89	86	83	87	84	82	80					80			
4	97	89	83	79	95	88	82	78	86	81	77	84	80	77	82	78	76	74					74			
5	91	83	77	72	90	82	76	72	80	75	72	78	74	71	77	73	70	69					69			
6	87	78	71	67	85	77	71	67	75	70	66	74	69	66	72	68	65	64					64			
7	82	73	66	62	81	72	66	62	71	65	62	69	65	61	68	64	61	60					60			
8	78	68	62	58	77	68	62	58	67	61	57	65	61	57	65	60	57	56					56			
9	74	64	58	54	73	64	58	54	63	57	54	62	57	54	61	57	53	52					52			
10	70	61	55	51	69	60	54	51	59	54	50	58	54	50	58	53	50	49					49			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	264724
5°	269586
10°	277901
15°	274816
20°	252364
25°	217714
30°	177407
35°	131364
40°	75372
45°	36440
50°	17328
55°	6043
60°	2196
65°	1284
70°	1046
75°	715
80°	0
85°	0



TEST NUMBER: P580225  
 CATALOG NUMBER: HCC4S25D010MB-HM40525935-41MDC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	209.4	9.2
10°-20°	596.6	26.1
20°-30°	728.6	31.9
30°-40°	535.6	23.4
40°-50°	177.5	7.8
50°-60°	31.3	1.4
60°-70°	4.7	0.2
70°-80°	1.6	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1534.7	67.1
0°-40°	2070.3	90.6
0°-60°	2279.2	99.7
0°-90°	2285.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2285.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2146	
5°	2177	209
15°	2152	597
25°	1600	729
35°	872	536
45°	209	178
55°	28	31
65°	4	5
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P580225  
CATALOG NUMBER: HCC4S25D010MB-HM40525935-41MDC

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2146.2
2.5°	2147.7
5°	2177.3
7.5°	2209.9
10°	2218.8
12.5°	2198.1
15°	2152.1
17.5°	2057.4
20°	1922.6
22.5°	1765.5
25°	1599.7
27.5°	1426.4
30°	1245.6
32.5°	1065.0
35°	872.4
37.5°	676.8
40°	468.1
42.5°	309.6
45°	208.9
47.5°	139.2
50°	90.3
52.5°	53.3
55°	28.1
57.5°	11.9
60°	8.9
62.5°	5.9
65°	4.4
67.5°	2.9
70°	2.9
72.5°	1.5
75°	1.5
77.5°	1.5
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)