

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580229

Luminaire Tested: **HCC4W25D010SL-HM40525935-41NDW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580229
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-3)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W25D010SL-HM40525935-41NDW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" NARROW DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2036.7 lumens
Efficiency: N/A
Efficacy: 76.0 lumens/watt
Spacing Criteria (0/90/45): 1.03 / 1.03 / 1.01
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580229
CATALOG NUMBER: HCC4W25D010SL-HM40525935-41NDW

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P580229

CATALOG NUMBER: HCC4W25D010SL-HM40525935-41NDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20								
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																											
1	111	108	104	101	109	105	102	100	101	99	97	98	96	94	94	92	91	89																											
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79																											
3	97	88	82	77	95	87	81	76	84	79	75	82	77	74	79	76	73	71																											
4	90	81	74	68	88	80	73	68	77	72	67	75	70	66	73	69	65	64																											
5	85	74	67	61	83	73	66	61	71	65	60	69	64	60	68	63	59	58																											
6	79	68	61	56	78	67	60	55	66	60	55	64	59	55	63	58	54	52																											
7	75	63	56	51	73	62	56	51	61	55	50	60	54	50	59	53	50	48																											
8	70	59	52	47	69	58	51	46	57	51	46	56	50	46	55	50	46	44																											
9	66	55	48	43	65	54	47	43	53	47	43	52	47	43	51	46	42	41																											
10	63	51	44	40	62	51	44	40	50	44	40	49	43	39	48	43	39	38																											

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	178950
5°	177603
10°	172981
15°	168432
20°	160901
25°	149883
30°	131987
35°	104094
40°	75549
45°	55523
50°	45171
55°	37870
60°	34339
65°	31521
70°	29356
75°	26783
80°	24222
85°	20945



TEST NUMBER: P580229
 CATALOG NUMBER: HCC4W25D010SL-HM40525935-41NDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	135.2	6.6
10°-20°	370.0	18.2
20°-30°	501.5	24.6
30°-40°	430.3	21.1
40°-50°	254.1	12.5
50°-60°	161.0	7.9
60°-70°	108.1	5.3
70°-80°	59.7	2.9
80°-90°	16.7	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1006.7	49.4
0°-40°	1437.0	70.6
0°-60°	1852.1	90.9
0°-90°	2036.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2036.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1451	
5°	1434	135
15°	1319	370
25°	1101	502
35°	691	430
45°	318	254
55°	176	161
65°	108	108
75°	56	60
85°	15	17
90°	0	



TEST NUMBER: P580229
CATALOG NUMBER: HCC4W25D010SL-HM40525935-41NDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1450.8
2.5°	1440.4
5°	1434.4
7.5°	1415.2
10°	1381.1
12.5°	1351.5
15°	1319.0
17.5°	1277.6
20°	1225.8
22.5°	1168.0
25°	1101.3
27.5°	1022.9
30°	926.7
32.5°	812.7
35°	691.3
37.5°	574.3
40°	469.2
42.5°	381.9
45°	318.3
47.5°	272.4
50°	235.4
52.5°	204.2
55°	176.1
57.5°	154.0
60°	139.2
62.5°	124.3
65°	108.0
67.5°	94.7
70°	81.4
72.5°	68.1
75°	56.2
77.5°	44.4
80°	34.1
82.5°	23.7
85°	14.8
87.5°	5.9
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)