

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580271

Luminaire Tested: **HCC4W30D010SL-HM43040827-41WWW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580271
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W30D010SL-HM43040827-41WWW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2753.1 lumens
Efficiency: N/A
Efficacy: 98.3 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.03 / 1.1
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580271
CATALOG NUMBER: HCC4W30D010SL-HM43040827-41WWW

Luminous Intensity Polar Plot





TEST NUMBER: P580271

CATALOG NUMBER: HCC4W30D010SL-HM43040827-41WWW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	111	106	103	100	108	104	101	98	100	97	95	96	94	92	93	91	89	87				87
2	102	95	89	84	100	93	88	83	90	85	81	87	83	80	84	81	78	76				76
3	94	85	78	72	92	84	77	72	81	75	71	78	73	69	76	72	68	66				66
4	87	77	69	63	85	76	68	63	73	67	62	71	66	61	69	64	60	58				58
5	81	70	62	56	79	69	61	56	67	60	55	65	59	54	63	58	54	52				52
6	76	64	56	50	74	63	55	50	61	54	49	59	53	49	58	53	48	47				47
7	71	58	50	45	69	58	50	45	56	49	44	55	49	44	53	48	44	42				42
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38				38
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35				35
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32				32

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	190150	190150	190150
5°	198515	189316	180562
10°	203541	185368	169236
15°	207750	180423	157029
20°	206645	171651	143797
25°	197966	158716	130830
30°	182891	144920	118571
35°	160304	128894	107331
40°	139601	113903	96658
45°	121478	99342	86381
50°	108246	85603	76219
55°	96728	75266	65912
60°	86342	65793	56813
65°	76730	57701	53994
70°	67367	49696	50345
75°	57046	42367	46656
80°	43827	36084	42548
85°	25757	28305	35947



TEST NUMBER: P580271
 CATALOG NUMBER: HCC4W30D010SL-HM43040827-41WWW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	144.5	5.2
10°-20°	398.6	14.5
20°-30°	544.6	19.8
30°-40°	546.8	19.9
40°-50°	452.4	16.4
50°-60°	327.8	11.9
60°-70°	207.7	7.5
70°-80°	105.0	3.8
80°-90°	25.7	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1087.7	39.5
0°-40°	1634.6	59.4
0°-60°	2414.8	87.7
0°-90°	2753.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2753.1	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1542	1542	1542	1542	1542	
5°	1603	1580	1529	1478	1458	154
15°	1627	1563	1413	1282	1230	458
25°	1455	1358	1166	1019	961	665
35°	1065	1001	856	751	713	667
45°	696	657	570	513	495	542
55°	450	410	350	319	306	405
65°	263	234	198	178	185	262
75°	120	103	89	92	98	128
85°	18	18	20	24	25	25
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P580271

CATALOG NUMBER: HCC4W30D010SL-HM43040827-41WWW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	1541.6	1541.6	1541.6	1541.6	1541.6	1541.6	1541.6	1541.6	1541.6
2.5°	1570.6	1565.2	1556.2	1545.2	1532.6	1518.1	1505.4	1498.1	1494.5
5°	1603.3	1596.1	1579.8	1556.2	1529.0	1501.7	1478.1	1463.7	1458.3
7.5°	1623.3	1612.4	1588.8	1552.6	1510.8	1470.9	1436.5	1416.5	1411.1
10°	1625.1	1612.4	1581.6	1532.6	1480.0	1427.4	1385.6	1356.6	1351.2
12.5°	1626.9	1610.6	1572.5	1514.5	1449.1	1383.8	1333.1	1298.7	1289.5
15°	1626.9	1610.6	1563.4	1494.5	1412.9	1338.5	1282.3	1242.4	1229.7
17.5°	1612.4	1594.3	1538.0	1458.3	1369.4	1285.9	1220.6	1178.9	1166.2
20°	1574.3	1554.4	1490.9	1403.8	1307.7	1220.6	1155.3	1111.8	1095.5
22.5°	1519.9	1496.3	1429.2	1334.9	1238.8	1149.9	1086.4	1041.0	1026.6
25°	1454.6	1431.0	1358.5	1266.0	1166.2	1082.8	1019.3	977.6	961.3
27.5°	1374.8	1349.4	1278.7	1186.2	1093.7	1010.2	952.3	914.1	897.8
30°	1284.1	1256.9	1189.8	1100.9	1017.5	937.7	881.4	850.6	832.5
32.5°	1178.9	1155.3	1095.5	1015.7	937.7	861.6	814.4	787.1	772.7
35°	1064.6	1052.0	1001.2	932.3	856.0	792.6	750.9	725.5	712.8
37.5°	963.1	950.3	906.9	848.8	781.7	723.7	689.2	667.4	656.6
40°	867.0	856.0	814.4	765.3	707.4	656.6	627.5	611.3	600.3
42.5°	772.7	767.2	732.7	687.4	636.6	593.1	569.5	556.8	547.8
45°	696.4	689.2	656.6	613.1	569.5	533.2	513.2	504.2	495.2
47.5°	629.3	620.3	585.9	547.8	507.8	475.2	457.1	448.0	444.3
50°	564.1	555.0	524.2	486.1	446.1	422.5	408.1	399.0	397.2
52.5°	506.0	497.0	462.5	426.3	395.4	375.4	362.8	353.6	350.0
55°	449.8	438.9	409.9	375.4	350.0	331.9	319.2	310.2	306.5
57.5°	399.0	388.1	362.8	330.1	306.5	290.2	279.3	270.3	266.7
60°	350.0	341.0	317.4	286.5	266.7	252.1	241.3	233.9	230.3
62.5°	304.7	297.5	273.9	246.7	230.3	217.6	208.6	201.3	205.0
65°	262.9	255.7	233.9	210.4	197.7	185.0	177.8	177.8	185.0
67.5°	223.1	215.8	197.7	177.8	166.8	157.8	152.4	157.8	163.2
70°	186.8	179.6	163.2	146.9	137.8	130.6	130.6	136.0	139.6
72.5°	152.4	145.1	132.4	119.7	112.5	107.0	112.5	116.1	119.7
75°	119.7	114.3	103.4	94.3	88.9	87.1	92.5	96.1	97.9
77.5°	88.9	85.3	77.9	70.7	67.1	68.9	74.3	76.1	77.9
80°	61.7	59.9	54.4	50.8	50.8	52.6	56.2	58.1	59.9
82.5°	38.1	38.1	34.5	32.6	34.5	38.1	39.9	41.7	41.7
85°	18.2	20.0	18.2	18.2	20.0	23.6	23.6	25.4	25.4
87.5°	5.4	5.4	7.2	7.2	9.0	9.0	9.0	9.0	10.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)