

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580272

Luminaire Tested: **HCC4W30D010SL-HM43040827-41WWWB**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580272
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-18)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W30D010SL-HM43040827-41WWWB
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2740.4 lumens
Efficiency: N/A
Efficacy: 97.9 lumens/watt
Spacing Criteria (0/90/45): 1.13 / 1.07 / 1.15
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580272
CATALOG NUMBER: HCC4W30D010SL-HM43040827-41WWWB

Luminous Intensity Polar Plot





TEST NUMBER: P580272

CATALOG NUMBER: HCC4W30D010SL-HM43040827-41WWWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87								
2	102	95	89	84	99	93	87	83	89	85	81	86	82	79	83	80	77	75								
3	94	85	77	72	92	83	76	71	80	75	70	78	73	69	75	71	68	66								
4	87	76	68	62	85	75	68	62	72	66	61	70	65	60	68	63	60	58								
5	81	69	61	55	79	68	60	55	66	59	54	64	58	53	62	57	53	51								
6	75	63	55	49	73	62	54	49	60	53	48	59	53	48	57	52	47	46								
7	70	58	50	44	68	57	49	44	55	48	43	54	48	43	53	47	43	41								
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37								
9	61	49	41	36	60	48	41	36	47	41	36	46	40	36	45	40	36	34								
10	58	45	38	33	57	45	38	33	44	38	33	43	37	33	42	37	33	31								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	174287	174287	174287
5°	183274	174062	167536
10°	189714	171979	159942
15°	195491	168866	153121
20°	195724	161911	144283
25°	188372	151340	135280
30°	174915	139265	126347
35°	156766	125371	116908
40°	137556	111858	108074
45°	120239	99028	99673
50°	106174	86677	89805
55°	93610	76858	80750
60°	83678	68013	70702
65°	74103	59831	59831
70°	64771	51030	51030
75°	55330	43225	48420
80°	43827	38641	43827
85°	28305	33399	41042



TEST NUMBER: P580272
 CATALOG NUMBER: HCC4W30D010SL-HM43040827-41WWWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	133.9	4.9
10°-20°	377.0	13.8
20°-30°	528.2	19.3
30°-40°	544.2	19.9
40°-50°	463.3	16.9
50°-60°	343.3	12.5
60°-70°	215.4	7.9
70°-80°	107.0	3.9
80°-90°	28.1	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1039.1	37.9
0°-40°	1583.3	57.8
0°-60°	2389.9	87.2
0°-90°	2740.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2740.4	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1413	1413	1413	1413	1413	
5°	1480	1455	1406	1366	1353	142
15°	1531	1462	1322	1226	1199	430
25°	1384	1288	1112	1016	994	633
35°	1041	963	833	778	776	649
45°	689	642	568	557	571	535
55°	435	401	357	365	376	394
65°	254	228	205	201	205	253
75°	116	103	91	98	102	124
85°	20	20	24	27	29	26
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P580272

CATALOG NUMBER: HCC4W30D010SL-HM43040827-41WWWB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	1413.0	1413.0	1413.0	1413.0	1413.0	1413.0	1413.0	1413.0	1413.0
2.5°	1443.8	1438.4	1431.2	1418.5	1405.8	1394.9	1384.1	1378.6	1376.7
5°	1480.2	1469.3	1454.8	1431.2	1405.8	1384.1	1365.9	1356.9	1353.1
7.5°	1505.5	1494.7	1471.1	1434.8	1398.5	1365.9	1336.9	1324.2	1320.5
10°	1514.7	1501.9	1469.3	1420.3	1373.1	1333.3	1300.6	1284.2	1277.0
12.5°	1521.9	1505.5	1463.8	1405.8	1347.7	1298.8	1264.3	1242.5	1237.1
15°	1530.9	1512.9	1462.0	1391.3	1322.4	1264.3	1226.2	1206.3	1199.1
17.5°	1521.9	1501.9	1442.0	1362.3	1284.2	1220.8	1179.1	1160.9	1153.7
20°	1491.1	1469.3	1402.2	1316.9	1233.5	1168.2	1126.4	1108.3	1099.2
22.5°	1443.8	1420.3	1351.3	1260.7	1175.4	1112.0	1072.1	1053.9	1048.5
25°	1384.1	1360.5	1288.0	1195.3	1112.0	1050.3	1015.8	999.5	994.0
27.5°	1313.3	1289.8	1218.9	1128.2	1048.5	990.4	963.2	946.8	943.2
30°	1228.1	1204.5	1135.6	1052.1	977.8	923.3	901.5	888.9	887.1
32.5°	1133.8	1113.8	1050.3	974.0	903.3	858.0	841.7	832.6	830.8
35°	1041.1	1019.5	963.2	894.3	832.6	792.6	778.2	776.4	776.4
37.5°	946.8	925.1	879.7	816.2	763.7	727.3	721.9	723.7	723.7
40°	854.3	834.4	794.5	741.9	694.7	667.6	665.7	669.4	671.2
42.5°	767.3	751.0	714.7	669.4	629.4	607.7	609.5	616.8	622.2
45°	689.3	674.8	642.2	602.2	567.7	551.5	556.9	565.9	571.4
47.5°	618.6	605.8	575.1	538.7	509.7	498.8	506.1	517.0	524.2
50°	553.3	542.3	513.4	475.2	451.7	444.4	453.5	464.4	468.0
52.5°	495.2	484.4	453.5	420.9	402.7	399.1	408.1	417.2	422.7
55°	435.3	426.3	400.9	371.9	357.4	355.5	364.6	371.9	375.5
57.5°	386.3	377.3	353.7	328.4	315.6	313.8	322.8	328.4	330.2
60°	339.2	330.2	308.4	284.8	275.7	275.7	281.2	284.8	286.6
62.5°	295.6	286.6	266.7	246.7	239.5	239.5	239.5	241.3	246.7
65°	253.9	246.7	228.5	210.4	205.0	201.3	201.3	201.3	205.0
67.5°	215.9	208.6	194.1	177.8	172.4	166.8	165.0	168.7	168.7
70°	179.6	174.2	159.6	147.0	141.5	136.0	134.2	141.5	141.5
72.5°	147.0	141.5	132.4	119.7	114.3	112.5	116.1	119.7	121.5
75°	116.1	110.7	103.4	96.1	90.7	92.5	97.9	99.7	101.6
77.5°	87.1	85.3	77.9	72.5	72.5	74.3	77.9	81.7	83.5
80°	61.7	59.9	56.3	52.6	54.4	58.1	59.9	63.5	61.7
82.5°	38.1	38.1	36.3	36.3	38.1	41.7	43.5	45.3	47.2
85°	20.0	20.0	20.0	21.8	23.6	25.4	27.2	29.0	29.0
87.5°	5.4	7.2	7.2	9.0	10.8	10.8	12.7	12.7	12.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)