

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580295

Luminaire Tested: **HCC4S30D010BZ-HM43040835-41WDH**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P580295  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-8)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC4S30D010BZ-HM43040835-41WDH  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, HAZE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3142.4 lumens  
Efficiency: N/A  
Efficacy: 112.2 lumens/watt  
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.1  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P580295  
CATALOG NUMBER: HCC4S30D010BZ-HM43040835-41WDH

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P580295

CATALOG NUMBER: HCC4S30D010BZ-HM43040835-41WDH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	107	104	110	108	105	103	103	101	100	100	98	97	96	95	94	92			92																
2	106	101	96	92	104	99	95	91	96	92	89	93	90	87	90	88	86	84			84																
3	100	93	87	82	98	91	86	82	88	84	80	86	82	79	84	81	78	76			76																
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69			69																
5	88	79	72	67	86	78	72	67	76	70	66	74	69	66	72	68	65	63			63																
6	83	73	66	61	81	72	66	61	70	65	61	69	64	60	68	63	60	58			58																
7	78	68	61	56	77	67	60	56	65	60	55	64	59	55	63	58	55	53			53																
8	74	63	56	51	72	62	56	51	61	55	51	60	55	51	59	54	51	49			49																
9	69	59	52	47	68	58	52	47	57	51	47	56	51	47	55	50	47	45			45																
10	66	55	48	44	65	54	48	44	53	48	44	53	47	44	52	47	43	42			42																

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	264219
5°	266194
10°	269522
15°	276298
20°	278327
25°	270356
30°	247880
35°	203957
40°	148682
45°	96499
50°	54401
55°	25827
60°	10213
65°	6333
70°	4256
75°	2812
80°	1350
85°	2689



TEST NUMBER: P580295  
 CATALOG NUMBER: HCC4S30D010BZ-HM43040835-41WDH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	205.3	6.5
10°-20°	610.0	19.4
20°-30°	904.8	28.8
30°-40°	835.7	26.6
40°-50°	436.3	13.9
50°-60°	119.6	3.8
60°-70°	23.1	0.7
70°-80°	6.5	0.2
80°-90°	1.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1720.0	54.7
0°-40°	2555.7	81.3
0°-60°	3111.6	99.0
0°-90°	3142.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3142.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2142	
5°	2150	205
15°	2164	610
25°	1986	905
35°	1354	836
45°	553	436
55°	120	120
65°	22	23
75°	6	6
85°	2	1
90°	0	



TEST NUMBER: P580295  
CATALOG NUMBER: HCC4S30D010BZ-HM43040835-41WDH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2142.1
2.5°	2136.1
5°	2149.9
7.5°	2155.8
10°	2151.9
12.5°	2155.8
15°	2163.7
17.5°	2155.8
20°	2120.4
22.5°	2063.3
25°	1986.5
27.5°	1882.2
30°	1740.4
32.5°	1561.3
35°	1354.5
37.5°	1137.9
40°	923.4
42.5°	726.4
45°	553.2
47.5°	405.5
50°	283.5
52.5°	189.1
55°	120.1
57.5°	70.8
60°	41.4
62.5°	29.6
65°	21.7
67.5°	15.8
70°	11.8
72.5°	7.9
75°	5.9
77.5°	3.9
80°	1.9
82.5°	1.9
85°	1.9
87.5°	0.0
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)