

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580286

Luminaire Tested: **HCC4W30D010MW-HM43040830-41RWWC**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580286
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-14)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W30D010MW-HM43040830-41RWWC
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3025.6 lumens
Efficiency: N/A
Efficacy: 108.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.15 / 1.21
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580286
CATALOG NUMBER: HCC4W30D010MW-HM43040830-41RWWC

Luminous Intensity Polar Plot





TEST NUMBER: P580286

CATALOG NUMBER: HCC4W30D010MW-HM43040830-41RWWC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	103	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88								
2	102	95	90	85	100	94	88	84	90	86	82	87	83	80	84	81	78	76								
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67								
4	87	77	69	63	85	76	68	63	73	67	62	71	66	61	69	64	60	58								
5	81	70	62	56	79	68	61	55	66	60	55	65	59	54	63	58	54	52								
6	75	63	55	49	74	62	55	49	61	54	49	59	53	48	58	52	48	46								
7	70	58	50	44	69	57	49	44	56	49	44	54	48	44	53	47	43	41								
8	66	53	45	40	64	53	45	40	51	44	40	50	44	39	49	43	39	37								
9	62	49	42	36	60	49	41	36	47	41	36	46	40	36	45	40	36	34								
10	58	46	38	33	57	45	38	33	44	38	33	43	37	33	42	37	33	31								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	179098	179098	179098
5°	186332	180735	178804
10°	192419	182337	178404
15°	199181	182900	178392
20°	199859	178476	176166
25°	192808	169563	170897
30°	179401	157895	162367
35°	161615	144479	149794
40°	142483	131421	137411
45°	124566	118408	124234
50°	110299	106557	112180
55°	97051	94104	97868
60°	86663	80347	82765
65°	76146	65289	64122
70°	66502	48109	43854
75°	55139	28976	23400
80°	41838	11152	6961
85°	19530	2689	2689



TEST NUMBER: P580286
 CATALOG NUMBER: HCC4W30D010MW-HM43040830-41RWWC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	140.0	4.6
10°-20°	408.7	13.5
20°-30°	591.9	19.6
30°-40°	624.4	20.6
40°-50°	540.4	17.9
50°-60°	400.3	13.2
60°-70°	230.8	7.6
70°-80°	80.6	2.7
80°-90°	8.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1140.6	37.7
0°-40°	1765.0	58.3
0°-60°	2705.8	89.4
0°-90°	3025.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3025.6	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1452	1452	1452	1452	1452	
5°	1505	1485	1460	1448	1444	145
15°	1560	1509	1432	1399	1397	439
25°	1417	1346	1246	1238	1256	648
35°	1073	1024	960	981	995	670
45°	714	695	679	704	712	554
55°	451	442	438	453	455	407
65°	261	245	224	212	220	261
75°	116	98	61	49	49	125
85°	14	8	2	2	2	21
90°	0	0	0	0	0	



TEST NUMBER: P580286

CATALOG NUMBER: HCC4W30D010MW-HM43040830-41RWWC

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	1452.0	1452.0	1452.0	1452.0	1452.0	1452.0	1452.0	1452.0	1452.0
2.5°	1473.5	1469.6	1463.7	1455.8	1448.0	1442.1	1440.1	1438.2	1438.2
5°	1504.9	1497.1	1485.2	1469.6	1459.7	1453.9	1448.0	1444.1	1444.1
7.5°	1526.5	1518.6	1500.9	1479.4	1465.6	1453.9	1446.0	1440.1	1440.1
10°	1536.3	1526.5	1504.9	1477.5	1455.8	1440.1	1428.4	1424.4	1424.4
12.5°	1548.1	1536.3	1506.9	1471.6	1444.1	1424.4	1412.7	1408.8	1408.8
15°	1559.8	1546.1	1508.8	1467.6	1432.3	1408.8	1398.9	1397.0	1397.0
17.5°	1553.9	1536.3	1493.1	1444.1	1404.8	1381.2	1371.4	1371.4	1373.5
20°	1522.6	1504.9	1455.8	1400.9	1359.7	1342.1	1334.2	1338.1	1342.1
22.5°	1475.4	1453.9	1400.9	1348.0	1304.8	1289.1	1289.1	1294.9	1300.8
25°	1416.7	1397.0	1345.9	1287.2	1245.9	1234.1	1238.1	1247.9	1255.7
27.5°	1349.9	1328.3	1275.3	1220.4	1179.2	1173.3	1183.2	1196.8	1200.8
30°	1259.6	1241.9	1196.8	1143.9	1108.6	1106.6	1120.3	1130.1	1140.0
32.5°	1173.3	1153.7	1110.5	1059.5	1034.0	1036.0	1051.6	1063.5	1069.3
35°	1073.3	1055.6	1024.2	982.9	959.5	963.3	981.0	992.8	994.8
37.5°	979.1	967.3	935.9	904.5	886.8	894.7	910.4	924.2	924.2
40°	884.9	875.1	851.5	826.0	816.2	826.0	841.7	853.4	853.4
42.5°	794.7	788.7	769.1	751.5	745.6	759.4	773.0	782.8	780.9
45°	714.1	708.3	694.6	680.9	678.8	692.6	704.3	710.3	712.2
47.5°	641.6	637.7	625.9	616.1	616.1	629.9	639.6	645.6	647.5
50°	574.8	571.0	561.2	553.3	555.3	569.0	576.9	582.7	584.6
52.5°	508.2	506.2	498.4	488.5	494.4	504.2	514.0	518.0	519.9
55°	451.3	451.3	441.5	433.6	437.6	447.4	453.2	455.1	455.1
57.5°	400.2	398.3	386.6	378.7	380.6	390.4	394.3	396.4	396.4
60°	351.3	349.2	337.5	325.7	325.7	331.6	333.5	335.5	335.5
62.5°	304.1	302.2	288.4	278.6	274.7	272.8	272.8	276.7	284.5
65°	260.9	259.0	245.2	229.5	223.7	217.8	212.0	215.8	219.7
67.5°	221.8	217.8	204.1	190.3	176.5	166.7	157.0	162.9	170.7
70°	184.4	180.5	164.8	149.1	133.4	117.8	109.9	117.8	121.6
72.5°	149.1	145.2	129.5	113.8	94.2	78.5	76.5	78.5	80.4
75°	115.7	113.8	98.1	80.4	60.8	49.1	49.1	49.1	49.1
77.5°	86.3	82.5	66.7	51.0	35.3	27.5	25.5	25.5	25.5
80°	58.9	54.9	41.2	29.4	15.7	11.7	11.7	9.8	9.8
82.5°	33.4	31.4	21.5	11.7	5.9	3.9	3.9	3.9	3.9
85°	13.8	11.7	7.9	3.9	1.9	1.9	1.9	1.9	1.9
87.5°	1.9	1.9	1.9	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)