

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580304

Luminaire Tested: **HCC4S30D010MW-HM43040835-41RWWC**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580304
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-14)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4S30D010MW-HM43040835-41RWWC
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3034.3 lumens
Efficiency: N/A
Efficacy: 108.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.15 / 1.21
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580304
CATALOG NUMBER: HCC4S30D010MW-HM43040835-41RWWC

Luminous Intensity Polar Plot





TEST NUMBER: P580304

CATALOG NUMBER: HCC4S30D010MW-HM43040835-41RWWC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	103	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88								
2	102	95	90	85	100	94	88	84	90	86	82	87	83	80	84	81	78	76								
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67								
4	87	77	69	63	85	76	68	63	73	67	62	71	66	61	69	64	60	58								
5	81	70	61	56	79	68	61	55	66	60	55	65	59	54	63	58	54	52								
6	75	63	55	49	74	62	55	49	61	54	49	59	53	48	58	52	48	46								
7	70	58	50	44	69	57	49	44	56	49	44	54	48	44	53	47	43	41								
8	66	53	45	40	64	53	45	40	51	44	40	50	44	39	49	43	39	37								
9	62	49	42	36	60	49	41	36	47	41	36	46	40	36	45	40	36	34								
10	58	46	38	33	57	45	38	33	44	38	33	43	37	33	42	37	33	31								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	179591	179591	179591
5°	186864	181255	179311
10°	192970	182863	178917
15°	199756	183424	178903
20°	200423	178988	176665
25°	193339	170053	171387
30°	179914	158351	162823
35°	162066	144885	150216
40°	142886	131808	137814
45°	124949	118774	124583
50°	110626	106865	112506
55°	97330	94362	98169
60°	86885	80594	83012
65°	76380	65494	64326
70°	66718	48253	43998
75°	55330	29071	23447
80°	41909	11223	6961
85°	19530	2689	2689



TEST NUMBER: P580304

CATALOG NUMBER: HCC4S30D010MW-HM43040835-41RWWC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	140.4	4.6
10°-20°	409.9	13.5
20°-30°	593.6	19.6
30°-40°	626.2	20.6
40°-50°	542.0	17.9
50°-60°	401.5	13.2
60°-70°	231.4	7.6
70°-80°	80.8	2.7
80°-90°	8.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1143.8	37.7
0°-40°	1770.1	58.3
0°-60°	2713.5	89.4
0°-90°	3034.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3034.3	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1456	1456	1456	1456	1456	
5°	1509	1490	1464	1452	1448	145
15°	1564	1513	1436	1403	1401	440
25°	1421	1350	1250	1242	1259	650
35°	1076	1027	962	984	998	672
45°	716	696	681	706	714	556
55°	453	443	439	455	456	408
65°	262	246	224	212	220	261
75°	116	98	61	49	49	125
85°	14	8	2	2	2	21
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P580304

CATALOG NUMBER: HCC4S30D010MW-HM43040835-41RWWC

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	1456.0	1456.0	1456.0	1456.0	1456.0	1456.0	1456.0	1456.0	1456.0
2.5°	1477.7	1473.7	1467.9	1460.0	1452.2	1446.2	1444.3	1442.3	1442.3
5°	1509.2	1501.4	1489.5	1473.7	1463.9	1458.1	1452.2	1448.2	1448.2
7.5°	1530.8	1523.0	1505.3	1483.7	1469.9	1458.1	1450.2	1444.3	1444.3
10°	1540.7	1530.8	1509.2	1481.6	1460.0	1444.3	1432.4	1428.5	1428.5
12.5°	1552.5	1540.7	1511.2	1475.8	1448.2	1428.5	1416.8	1412.8	1412.8
15°	1564.3	1550.5	1513.1	1471.8	1436.4	1412.8	1402.9	1401.0	1401.0
17.5°	1558.4	1540.7	1497.4	1448.2	1408.9	1385.2	1375.4	1375.4	1377.4
20°	1526.9	1509.2	1460.0	1404.9	1363.6	1345.9	1338.0	1342.0	1345.9
22.5°	1479.7	1458.1	1404.9	1351.8	1308.5	1292.8	1292.8	1298.7	1304.5
25°	1420.6	1401.0	1349.8	1290.8	1249.5	1237.6	1241.6	1251.4	1259.3
27.5°	1353.7	1332.1	1279.0	1223.9	1182.6	1176.6	1186.5	1200.3	1204.3
30°	1263.2	1245.5	1200.3	1147.2	1111.8	1109.7	1123.5	1133.4	1143.2
32.5°	1176.6	1157.0	1113.7	1062.6	1037.0	1038.9	1054.7	1066.5	1072.4
35°	1076.3	1058.6	1027.2	985.8	962.2	966.1	983.8	995.7	997.6
37.5°	981.8	970.1	938.6	907.1	889.4	897.2	913.0	926.8	926.8
40°	887.4	877.6	854.0	828.4	818.6	828.4	844.1	855.9	855.9
42.5°	796.9	791.0	771.3	753.6	747.8	761.5	775.3	785.1	783.2
45°	716.3	710.3	696.5	682.8	680.9	694.6	706.4	712.3	714.2
47.5°	643.4	639.5	627.7	617.8	617.8	631.6	641.5	647.4	649.3
50°	576.5	572.6	562.8	554.9	556.9	570.7	578.4	584.4	586.3
52.5°	509.6	507.7	499.8	490.0	495.9	505.7	515.5	519.4	521.5
55°	452.6	452.6	442.7	434.8	438.8	448.6	454.6	456.5	456.5
57.5°	401.5	399.4	387.6	379.8	381.7	391.5	395.5	397.5	397.5
60°	352.2	350.2	338.4	326.7	326.7	332.5	334.5	336.5	336.5
62.5°	305.0	303.0	289.2	279.4	275.5	273.5	273.5	277.5	285.3
65°	261.7	259.8	245.9	230.2	224.4	218.4	212.5	216.5	220.4
67.5°	222.3	218.4	204.6	190.9	177.1	167.3	157.5	163.3	171.2
70°	185.0	181.0	165.3	149.6	133.8	118.1	110.2	118.1	122.0
72.5°	149.6	145.6	129.8	114.2	94.4	78.7	76.7	78.7	80.7
75°	116.1	114.2	98.4	80.7	61.0	49.2	49.2	49.2	49.2
77.5°	86.6	82.7	66.9	51.2	35.4	27.5	25.6	25.6	25.6
80°	59.0	55.0	41.3	29.6	15.8	11.8	11.8	9.8	9.8
82.5°	33.5	31.5	21.7	11.8	5.9	3.9	3.9	3.9	3.9
85°	13.8	11.8	7.9	3.9	1.9	1.9	1.9	1.9	1.9
87.5°	1.9	1.9	1.9	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)