

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580306

Luminaire Tested: **HCC4W30D010MB-HM43040835-41WWBB**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580306
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-17)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W30D010MB-HM43040835-41WWBB
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2388.8 lumens
Efficiency: N/A
Efficacy: 85.3 lumens/watt
Spacing Criteria (0/90/45): 1.11 / 1.04 / 1.12
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580306
CATALOG NUMBER: HCC4W30D010MB-HM43040835-41WWBB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P580306

CATALOG NUMBER: HCC4W30D010MB-HM43040835-41WWBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	111	108	104	101	109	105	102	100	101	99	97	97	95	94	94	92	91	89					89			
2	103	97	91	87	101	95	90	86	92	87	84	88	85	82	85	83	80	78					78			
3	96	87	80	75	94	86	79	74	83	78	73	80	76	72	78	74	71	69					69			
4	89	79	72	66	87	78	71	65	75	69	65	73	68	64	71	67	63	61					61			
5	83	72	64	58	81	71	64	58	69	62	58	67	61	57	65	60	56	55					55			
6	77	66	58	52	75	65	57	52	63	57	52	61	56	51	60	55	51	49					49			
7	72	60	53	47	71	59	52	47	58	51	47	57	51	46	55	50	46	44					44			
8	68	56	48	43	66	55	48	43	54	47	42	53	47	42	51	46	42	40					40			
9	64	52	44	39	62	51	44	39	50	43	39	49	43	39	48	43	39	37					37			
10	60	48	41	36	59	47	41	36	46	40	36	46	40	36	45	39	36	34					34			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	170575	170575	170575
5°	180735	170013	161494
10°	188236	167307	152027
15°	195440	163286	142931
20°	197273	155453	132207
25°	190903	143773	121017
30°	178476	130292	110111
35°	159070	115824	98944
40°	139054	100732	88060
45°	121129	85457	76194
50°	105694	72497	65301
55°	92642	60084	52880
60°	81063	48524	38829
65°	70630	36191	21831
70°	61705	23442	7069
75°	50659	12200	1859
80°	37718	5612	1350
85°	22361	2689	2689



TEST NUMBER: P580306
 CATALOG NUMBER: HCC4W30D010MB-HM43040835-41WWBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	130.5	5.5
10°-20°	365.3	15.3
20°-30°	505.1	21.1
30°-40°	507.9	21.3
40°-50°	409.8	17.2
50°-60°	277.1	11.6
60°-70°	141.0	5.9
70°-80°	45.2	1.9
80°-90°	6.9	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1000.9	41.9
0°-40°	1508.8	63.2
0°-60°	2195.7	91.9
0°-90°	2388.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2388.8	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1383	1383	1383	1383	1383	
5°	1460	1432	1373	1324	1304	141
15°	1530	1448	1279	1157	1119	431
25°	1403	1281	1056	926	889	642
35°	1056	954	769	673	657	660
45°	694	622	490	437	437	538
55°	431	372	279	244	246	387
65°	242	197	124	81	75	243
75°	106	75	26	6	4	115
85°	16	8	2	2	2	21
90°	0	0	0	0	0	



TEST NUMBER: P580306

CATALOG NUMBER: HCC4W30D010MB-HM43040835-41WWBB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	1382.9	1382.9	1382.9	1382.9	1382.9	1382.9	1382.9	1382.9	1382.9
2.5°	1420.4	1412.5	1404.6	1390.8	1375.1	1359.4	1349.5	1341.6	1337.7
5°	1459.7	1449.8	1432.1	1402.7	1373.1	1345.6	1323.9	1310.2	1304.3
7.5°	1491.2	1477.5	1447.9	1406.6	1361.4	1318.1	1290.5	1270.8	1263.0
10°	1502.9	1487.3	1447.9	1392.9	1335.8	1282.6	1243.3	1223.7	1213.8
12.5°	1516.7	1499.0	1449.8	1381.0	1310.2	1247.2	1202.0	1176.4	1166.6
15°	1530.5	1506.9	1447.9	1363.3	1278.7	1205.9	1156.8	1131.2	1119.3
17.5°	1530.5	1502.9	1432.1	1333.7	1237.4	1160.7	1105.6	1076.1	1066.3
20°	1502.9	1471.5	1394.8	1286.6	1184.3	1101.6	1048.6	1019.0	1007.2
22.5°	1459.7	1424.3	1341.6	1229.5	1121.3	1040.7	987.6	960.0	948.2
25°	1402.7	1367.2	1280.7	1164.7	1056.4	975.7	926.5	901.0	889.2
27.5°	1335.8	1296.4	1209.9	1093.8	987.6	910.9	865.6	841.9	832.1
30°	1253.1	1215.8	1131.2	1017.1	914.8	844.0	802.7	781.0	773.1
32.5°	1156.8	1125.3	1042.6	936.5	840.0	775.0	737.7	720.0	712.1
35°	1056.4	1026.9	954.1	855.7	769.2	708.2	672.9	661.0	657.1
37.5°	962.0	936.5	865.6	775.0	696.4	643.3	611.8	603.9	600.0
40°	863.6	845.9	781.0	698.3	625.6	578.3	552.8	546.9	546.9
42.5°	775.0	755.4	698.3	623.7	558.7	511.4	493.7	487.9	489.9
45°	694.4	674.8	621.6	552.8	489.9	450.5	436.8	436.8	436.8
47.5°	619.7	602.0	552.8	482.0	430.8	399.3	385.6	385.6	387.6
50°	550.8	539.1	483.9	423.0	377.8	348.2	338.4	336.4	340.3
52.5°	485.9	472.2	423.0	367.8	324.6	301.0	291.1	289.2	291.1
55°	430.8	415.1	371.8	318.7	279.4	255.7	244.0	242.0	245.9
57.5°	377.8	365.9	320.7	273.4	236.1	212.5	202.6	198.6	200.7
60°	328.6	316.7	275.5	230.1	196.7	173.1	159.4	155.4	157.4
62.5°	283.2	273.4	234.1	190.9	157.4	135.7	121.9	112.1	116.1
65°	242.0	232.1	196.7	153.4	124.0	100.3	80.7	72.8	74.8
67.5°	206.5	194.8	161.3	121.9	92.5	66.9	45.2	41.3	41.3
70°	171.1	159.4	129.8	94.4	65.0	35.4	19.6	19.6	19.6
72.5°	137.7	127.9	100.3	70.8	41.3	15.8	7.9	7.9	7.9
75°	106.3	98.4	74.8	49.2	25.6	7.9	5.9	3.9	3.9
77.5°	78.7	70.8	53.1	33.4	15.8	3.9	3.9	3.9	3.9
80°	53.1	47.3	35.4	19.6	7.9	1.9	1.9	1.9	1.9
82.5°	31.5	27.5	19.6	9.8	3.9	1.9	1.9	1.9	1.9
85°	15.8	11.8	7.9	3.9	1.9	1.9	1.9	1.9	1.9
87.5°	3.9	1.9	1.9	1.9	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)