

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580308

Luminaire Tested: **HCC4W30D010SL-HM43040835-41WWWB**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580308
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-18)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W30D010SL-HM43040835-41WWWB
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2973.3 lumens
Efficiency: N/A
Efficacy: 106.2 lumens/watt
Spacing Criteria (0/90/45): 1.13 / 1.07 / 1.15
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580308
CATALOG NUMBER: HCC4W30D010SL-HM43040835-41WWWB

Luminous Intensity Polar Plot





TEST NUMBER: P580308

CATALOG NUMBER: HCC4W30D010SL-HM43040835-41WWWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20				
RC	80					70					50					30				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87		
2	102	95	89	84	99	93	87	83	89	85	81	86	82	79	83	80	77	75		
3	94	85	77	72	92	83	76	71	80	75	70	78	73	69	75	71	68	66		
4	87	76	68	62	85	75	68	62	72	66	61	70	65	60	68	63	60	58		
5	81	69	61	55	79	68	60	55	66	59	54	64	58	53	62	57	53	51		
6	75	63	55	49	73	62	54	49	60	53	48	59	53	48	57	52	47	46		
7	70	58	50	44	68	57	49	44	55	48	43	54	48	43	53	47	43	41		
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37		
9	61	49	41	36	60	48	41	36	47	41	36	46	40	36	45	40	36	34		
10	58	45	38	33	57	45	38	33	44	38	33	43	37	33	42	37	33	31		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	189101	189101	189101
5°	198837	188858	181788
10°	205833	186608	173532
15°	212117	183207	166121
20°	212355	175667	156543
25°	204363	164187	146780
30°	189770	151087	137072
35°	170107	136016	126831
40°	149262	121358	117252
45°	130461	107453	108134
50°	115173	94027	97423
55°	101566	83374	87610
60°	90807	73785	76721
65°	80437	64910	64910
70°	70252	55358	55358
75°	60048	46895	52518
80°	47520	41909	47520
85°	30711	36230	44580



TEST NUMBER: P580308
 CATALOG NUMBER: HCC4W30D010SL-HM43040835-41WWWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	145.3	4.9
10°-20°	409.1	13.8
20°-30°	573.1	19.3
30°-40°	590.4	19.9
40°-50°	502.7	16.9
50°-60°	372.4	12.5
60°-70°	233.7	7.9
70°-80°	116.1	3.9
80°-90°	30.5	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1127.4	37.9
0°-40°	1717.8	57.8
0°-60°	2592.9	87.2
0°-90°	2973.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2973.3	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1533	1533	1533	1533	1533	
5°	1606	1578	1525	1482	1468	154
15°	1661	1586	1435	1330	1301	467
25°	1502	1397	1206	1102	1078	687
35°	1130	1045	903	844	842	704
45°	748	697	616	604	620	580
55°	472	435	388	396	407	427
65°	276	248	222	218	222	275
75°	126	112	98	106	110	135
85°	22	22	26	30	32	28
90°	0	0	0	0	0	



TEST NUMBER: P580308

CATALOG NUMBER: HCC4W30D010SL-HM43040835-41WWWB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	1533.1	1533.1	1533.1	1533.1	1533.1	1533.1	1533.1	1533.1	1533.1
2.5°	1566.6	1560.7	1552.8	1539.0	1525.3	1513.4	1501.6	1495.7	1493.8
5°	1605.9	1594.1	1578.4	1552.8	1525.3	1501.6	1482.0	1472.2	1468.2
7.5°	1633.5	1621.7	1596.1	1556.8	1517.4	1482.0	1450.5	1436.7	1432.8
10°	1643.4	1629.5	1594.1	1541.0	1489.9	1446.5	1411.1	1393.4	1385.5
12.5°	1651.2	1633.5	1588.2	1525.3	1462.2	1409.1	1371.8	1348.1	1342.2
15°	1661.1	1641.4	1586.3	1509.5	1434.7	1371.8	1330.4	1308.7	1300.9
17.5°	1651.2	1629.5	1564.6	1478.0	1393.4	1324.5	1279.3	1259.5	1251.7
20°	1617.8	1594.1	1521.3	1428.8	1338.3	1267.4	1222.2	1202.4	1192.6
22.5°	1566.6	1541.0	1466.2	1367.8	1275.3	1206.4	1163.1	1143.5	1137.6
25°	1501.6	1476.1	1397.4	1297.0	1206.4	1139.5	1102.2	1084.3	1078.5
27.5°	1424.9	1399.3	1322.6	1224.1	1137.6	1074.5	1045.1	1027.4	1023.4
30°	1332.4	1306.8	1232.0	1141.4	1060.8	1001.8	978.1	964.3	962.4
32.5°	1230.1	1208.4	1139.5	1056.8	980.1	930.9	913.2	903.3	901.4
35°	1129.7	1106.0	1045.1	970.3	903.3	860.0	844.3	842.3	842.3
37.5°	1027.4	1003.7	954.5	885.6	828.5	789.1	783.3	785.2	785.2
40°	927.0	905.3	862.0	804.9	753.7	724.3	722.3	726.2	728.2
42.5°	832.5	814.8	775.4	726.2	682.9	659.3	661.2	669.1	675.0
45°	747.9	732.1	696.7	653.5	616.0	598.3	604.2	614.1	619.9
47.5°	671.2	657.3	623.9	584.5	553.1	541.2	549.1	560.8	568.7
50°	600.2	588.5	557.0	515.6	490.0	482.2	492.0	503.9	507.7
52.5°	537.3	525.4	492.0	456.6	436.9	432.9	442.9	452.7	458.5
55°	472.3	462.5	435.0	403.5	387.7	385.8	395.6	403.5	407.4
57.5°	419.2	409.4	383.7	356.2	342.5	340.4	350.4	356.2	358.1
60°	368.1	358.1	334.6	309.0	299.1	299.1	305.0	309.0	311.0
62.5°	320.8	311.0	289.3	267.7	259.8	259.8	259.8	261.7	267.7
65°	275.6	267.7	247.9	228.3	222.4	218.5	218.5	218.5	222.4
67.5°	234.2	226.3	210.6	192.9	186.9	181.0	179.1	183.1	183.1
70°	194.8	188.9	173.1	159.4	153.5	147.7	145.6	153.5	153.5
72.5°	159.4	153.5	143.7	129.9	124.0	122.0	126.0	129.9	131.9
75°	126.0	120.0	112.1	104.3	98.4	100.4	106.3	108.3	110.2
77.5°	94.4	92.5	84.6	78.7	78.7	80.7	84.6	88.5	90.6
80°	66.9	65.0	61.0	57.1	59.0	62.9	65.0	68.9	66.9
82.5°	41.3	41.3	39.4	39.4	41.3	45.2	47.3	49.2	51.2
85°	21.7	21.7	21.7	23.6	25.6	27.5	29.6	31.5	31.5
87.5°	5.9	7.9	7.9	9.8	11.8	11.8	13.8	13.8	13.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)