

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P592732

Luminaire Tested: **HCC4S30D010SL-HM43040850-41WDH**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P592732  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-8)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC4S30D010SL-HM43040850-41WDH  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, HAZE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 5000K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3288.0 lumens  
Efficiency: N/A  
Efficacy: 117.4 lumens/watt  
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.1  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P592732  
CATALOG NUMBER: HCC4S30D010SL-HM43040850-41WDH

### Luminous Intensity Polar Plot





TEST NUMBER: P592732

CATALOG NUMBER: HCC4S30D010SL-HM43040850-41WDH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	107	104	110	108	105	103	103	101	100	100	98	97	96	95	94	92			92																
2	106	101	96	92	104	99	95	91	96	92	89	93	90	87	90	88	86	84			84																
3	100	93	87	82	98	91	86	82	88	84	80	86	82	79	84	81	78	76			76																
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69			69																
5	88	79	72	67	86	78	72	67	76	70	66	74	69	66	72	68	65	63			63																
6	83	73	66	61	81	72	66	61	70	65	61	69	64	60	68	63	60	58			58																
7	78	68	61	56	77	67	60	56	65	60	55	64	59	55	63	58	55	53			53																
8	74	63	56	51	72	62	56	51	61	55	51	60	55	51	59	54	51	49			49																
9	69	59	52	47	68	58	52	47	57	51	47	56	51	47	55	50	47	45			45																
10	66	55	48	44	65	54	48	44	53	48	44	53	47	44	52	47	43	42			42																

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	276442
5°	278526
10°	281997
15°	289093
20°	291217
25°	282877
30°	259346
35°	213398
40°	155558
45°	100982
50°	56934
55°	27031
60°	10657
65°	6625
70°	4472
75°	2955
80°	1421
85°	2830



TEST NUMBER: P592732  
 CATALOG NUMBER: HCC4S30D010SL-HM43040850-41WDH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	214.8	6.5
10°-20°	638.3	19.4
20°-30°	946.6	28.8
30°-40°	874.3	26.6
40°-50°	456.6	13.9
50°-60°	125.1	3.8
60°-70°	24.1	0.7
70°-80°	6.8	0.2
80°-90°	1.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1799.7	54.7
0°-40°	2674.0	81.3
0°-60°	3255.7	99.0
0°-90°	3288.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3288.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2241	
5°	2250	215
15°	2264	638
25°	2078	947
35°	1417	874
45°	579	457
55°	126	125
65°	23	24
75°	6	7
85°	2	1
90°	0	



TEST NUMBER: P592732

CATALOG NUMBER: HCC4S30D010SL-HM43040850-41WDH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2241.2
2.5°	2235.0
5°	2249.5
7.5°	2255.7
10°	2251.5
12.5°	2255.7
15°	2263.9
17.5°	2255.7
20°	2218.6
22.5°	2158.8
25°	2078.5
27.5°	1969.3
30°	1820.9
32.5°	1633.6
35°	1417.2
37.5°	1190.6
40°	966.1
42.5°	760.2
45°	578.9
47.5°	424.4
50°	296.7
52.5°	197.7
55°	125.7
57.5°	74.1
60°	43.2
62.5°	30.9
65°	22.7
67.5°	16.5
70°	12.4
72.5°	8.2
75°	6.2
77.5°	4.2
80°	2.0
82.5°	2.0
85°	2.0
87.5°	0.0
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)