

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P592745

Luminaire Tested: **HCC4W30D010BZ-HM43040850-41WWWB**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P592745
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-18)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W30D010BZ-HM43040850-41WWWB
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 5000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3110.9 lumens
Efficiency: N/A
Efficacy: 111.1 lumens/watt
Spacing Criteria (0/90/45): 1.13 / 1.07 / 1.15
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P592745
CATALOG NUMBER: HCC4W30D010BZ-HM43040850-41WWWB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P592745

CATALOG NUMBER: HCC4W30D010BZ-HM43040850-41WWWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87								
2	102	95	89	84	99	93	87	83	89	85	81	86	82	79	83	80	77	75								
3	94	85	77	72	92	83	76	71	80	75	70	78	73	69	75	71	68	66								
4	87	76	68	62	85	75	68	62	72	66	61	70	65	60	68	63	60	58								
5	81	69	61	55	79	68	60	55	66	59	54	64	58	53	62	57	53	51								
6	75	63	55	49	73	62	54	49	60	53	48	59	53	48	57	52	47	46								
7	70	58	50	44	68	57	49	44	55	48	43	54	48	43	53	47	43	41								
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37								
9	61	49	41	36	60	48	41	36	47	41	36	46	40	36	45	40	36	34								
10	58	45	38	33	57	45	38	33	44	38	33	43	37	33	42	37	33	31								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	197859	197859	197859
5°	208049	197599	190195
10°	215352	195237	181573
15°	221924	191686	173821
20°	222187	183793	163801
25°	213835	171781	153585
30°	198558	158066	143424
35°	177967	142326	132704
40°	156170	126994	122678
45°	136497	112425	113140
50°	120527	98383	101952
55°	106276	87223	91674
60°	95001	77214	80249
65°	84143	67916	67916
70°	73498	57919	57919
75°	62812	49087	54949
80°	49722	43898	49722
85°	32126	37787	46561



TEST NUMBER: P592745
 CATALOG NUMBER: HCC4W30D010BZ-HM43040850-41WWWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	152.0	4.9
10°-20°	428.0	13.8
20°-30°	599.6	19.3
30°-40°	617.7	19.9
40°-50°	525.9	16.9
50°-60°	389.7	12.5
60°-70°	244.5	7.9
70°-80°	121.5	3.9
80°-90°	31.9	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1179.6	37.9
0°-40°	1797.3	57.8
0°-60°	2712.9	87.2
0°-90°	3110.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3110.9	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1604	1604	1604	1604	1604	
5°	1680	1652	1596	1550	1536	162
15°	1738	1660	1501	1392	1361	489
25°	1571	1462	1262	1153	1128	719
35°	1182	1093	945	883	881	737
45°	782	729	644	632	649	607
55°	494	455	406	414	426	447
65°	288	259	233	228	233	288
75°	132	117	103	111	115	141
85°	23	23	27	31	33	29
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P592745

CATALOG NUMBER: HCC4W30D010BZ-HM43040850-41WWWB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	1604.1	1604.1	1604.1	1604.1	1604.1	1604.1	1604.1	1604.1	1604.1
2.5°	1639.1	1632.9	1624.7	1610.2	1595.9	1583.5	1571.2	1565.0	1563.0
5°	1680.3	1668.0	1651.5	1624.7	1595.9	1571.2	1550.5	1540.3	1536.1
7.5°	1709.1	1696.7	1670.0	1628.8	1587.7	1550.5	1517.6	1503.2	1499.1
10°	1719.4	1705.0	1668.0	1612.4	1558.8	1513.4	1476.4	1457.9	1449.7
12.5°	1727.6	1709.1	1661.8	1595.9	1529.9	1474.4	1435.3	1410.6	1404.4
15°	1737.9	1717.4	1659.7	1579.4	1501.1	1435.3	1392.0	1369.4	1361.2
17.5°	1727.6	1705.0	1637.1	1546.5	1457.9	1385.9	1338.5	1317.8	1309.6
20°	1692.7	1668.0	1591.7	1494.9	1400.2	1326.1	1278.7	1258.2	1247.9
22.5°	1639.1	1612.4	1534.1	1431.1	1334.3	1262.2	1217.0	1196.4	1190.2
25°	1571.2	1544.3	1462.0	1357.0	1262.2	1192.3	1153.2	1134.7	1128.5
27.5°	1490.9	1464.0	1383.7	1280.8	1190.2	1124.3	1093.4	1074.9	1070.8
30°	1394.1	1367.2	1289.1	1194.3	1109.8	1048.1	1023.4	1009.0	1007.0
32.5°	1286.9	1264.4	1192.3	1105.8	1025.5	974.0	955.4	945.2	943.1
35°	1181.9	1157.2	1093.4	1015.2	945.2	899.8	883.3	881.3	881.3
37.5°	1074.9	1050.2	998.7	926.7	866.9	825.7	819.5	821.6	821.6
40°	969.9	947.2	901.9	842.2	788.7	757.8	755.8	759.8	761.9
42.5°	871.0	852.5	811.3	759.8	714.5	689.8	691.9	700.1	706.2
45°	782.5	766.0	728.9	683.7	644.5	626.0	632.1	642.5	648.6
47.5°	702.2	687.7	652.8	611.6	578.7	566.3	574.5	586.9	595.1
50°	628.1	615.7	582.7	539.5	512.7	504.4	514.8	527.1	531.3
52.5°	562.2	549.8	514.8	477.7	457.2	453.0	463.3	473.6	479.7
55°	494.2	483.9	455.0	422.1	405.6	403.6	413.9	422.1	426.3
57.5°	438.6	428.3	401.6	372.7	358.3	356.2	366.5	372.7	374.7
60°	385.1	374.7	350.0	323.3	313.0	313.0	319.2	323.3	325.3
62.5°	335.7	325.3	302.6	280.1	271.8	271.8	271.8	273.9	280.1
65°	288.3	280.1	259.4	238.9	232.7	228.5	228.5	228.5	232.7
67.5°	245.0	236.8	220.3	201.8	195.6	189.4	187.4	191.5	191.5
70°	203.8	197.6	181.2	166.8	160.6	154.4	152.4	160.6	160.6
72.5°	166.8	160.6	150.4	135.9	129.7	127.7	131.8	135.9	138.0
75°	131.8	125.7	117.4	109.2	103.0	105.0	111.2	113.3	115.3
77.5°	98.8	96.8	88.5	82.3	82.3	84.4	88.5	92.6	94.8
80°	70.0	67.9	63.8	59.7	61.8	65.9	67.9	72.1	70.0
82.5°	43.2	43.2	41.2	41.2	43.2	47.4	49.4	51.4	53.6
85°	22.7	22.7	22.7	24.7	26.7	28.9	30.9	32.9	32.9
87.5°	6.2	8.2	8.2	10.3	12.4	12.4	14.4	14.4	14.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)