

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580328

Luminaire Tested: **HCC4W30D010BZ-HM43040927-41WDWB**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580328
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-10)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W30D010BZ-HM43040927-41WDWB
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2529.4 lumens
Efficiency: N/A
Efficacy: 90.3 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.14 / 1.07
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580328
CATALOG NUMBER: HCC4W30D010BZ-HM43040927-41WDWB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P580328

CATALOG NUMBER: HCC4W30D010BZ-HM43040927-41WDWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90			
2	104	98	93	89	102	96	92	88	93	89	86	90	87	84	87	84	82	80			
3	98	89	83	78	95	88	82	78	85	80	76	83	78	75	80	77	74	72			
4	91	82	75	70	89	81	74	69	78	73	69	76	72	68	74	70	67	65			
5	86	75	68	63	84	74	68	63	72	67	62	71	65	61	69	64	61	59			
6	80	70	62	57	79	69	62	57	67	61	57	66	60	56	64	59	56	54			
7	76	64	57	52	74	64	57	52	62	56	52	61	56	51	60	55	51	49			
8	71	60	53	48	70	59	53	48	58	52	48	57	51	47	56	51	47	46			
9	67	56	49	44	66	55	49	44	54	48	44	53	48	44	52	47	44	42			
10	64	52	46	41	62	52	45	41	51	45	41	50	45	41	49	44	41	39			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	207652
5°	208644
10°	210067
15°	212168
20°	208640
25°	199055
30°	180840
35°	145864
40°	101215
45°	66443
50°	44519
55°	31676
60°	27087
65°	31112
70°	33359
75°	32169
80°	28910
85°	26606



TEST NUMBER: P580328
 CATALOG NUMBER: HCC4W30D010BZ-HM43040927-41WDWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	160.6	6.3
10°-20°	466.8	18.5
20°-30°	666.9	26.4
30°-40°	595.8	23.6
40°-50°	305.6	12.1
50°-60°	138.9	5.5
60°-70°	103.6	4.1
70°-80°	70.5	2.8
80°-90°	20.9	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1294.3	51.2
0°-40°	1890.0	74.7
0°-60°	2334.5	92.3
0°-90°	2529.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2529.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1684	
5°	1685	161
15°	1662	467
25°	1463	667
35°	969	596
45°	381	306
55°	147	139
65°	107	104
75°	68	70
85°	19	21
90°	0	



TEST NUMBER: P580328
CATALOG NUMBER: HCC4W30D010BZ-HM43040927-41WDWB

CANDELA DISTRIBUTION (FULL):

	0°
0°	1683.5
2.5°	1677.2
5°	1685.1
7.5°	1685.1
10°	1677.2
12.5°	1669.4
15°	1661.5
17.5°	1638.1
20°	1589.5
22.5°	1529.9
25°	1462.6
27.5°	1377.9
30°	1269.7
32.5°	1131.7
35°	968.7
37.5°	794.8
40°	628.6
42.5°	490.7
45°	380.9
47.5°	297.8
50°	232.0
52.5°	181.8
55°	147.3
57.5°	123.9
60°	109.8
62.5°	106.6
65°	106.6
67.5°	103.4
70°	92.5
72.5°	80.0
75°	67.5
77.5°	53.2
80°	40.7
82.5°	29.8
85°	18.8
87.5°	7.8
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)