

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580361

Luminaire Tested: **HCC4W30D010BZ-HM43040930-41WWW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580361
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W30D010BZ-HM43040930-41WWW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2553.3 lumens
Efficiency: N/A
Efficacy: 91.2 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.03 / 1.1
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580361
CATALOG NUMBER: HCC4W30D010BZ-HM43040930-41WWW

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P580361

CATALOG NUMBER: HCC4W30D010BZ-HM43040930-41WWW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	111	106	103	100	108	104	101	98	100	97	95	96	94	92	93	91	89	87					87			
2	102	95	89	84	100	93	88	83	90	85	81	87	83	80	84	81	78	76					76			
3	94	85	78	72	92	84	77	72	81	75	71	78	73	69	76	72	68	66					66			
4	87	77	69	63	85	76	68	63	73	67	62	71	66	61	69	64	60	58					58			
5	81	70	62	56	79	69	61	56	67	60	55	65	59	54	63	58	54	52					52			
6	76	64	56	50	74	63	55	50	61	54	49	59	53	49	58	53	48	47					47			
7	71	58	50	45	69	58	50	45	56	49	44	55	49	44	53	48	44	42					42			
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38					38			
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35					35			
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32					32			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	176347	176347	176347
5°	184103	175572	167450
10°	188762	171916	156949
15°	192669	167321	145625
20°	191655	159194	133362
25°	183595	147189	121330
30°	169617	134409	109968
35°	148665	119543	99532
40°	129457	105627	89654
45°	112669	92120	80101
50°	100398	79405	70693
55°	89696	69804	61138
60°	80076	61007	52693
65°	71185	53498	50083
70°	62499	46090	46703
75°	52899	39317	43273
80°	40630	33527	39423
85°	23776	26182	33399



TEST NUMBER: P580361

CATALOG NUMBER: HCC4W30D010BZ-HM43040930-41WWW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	134.0	5.2
10°-20°	369.7	14.5
20°-30°	505.1	19.8
30°-40°	507.2	19.9
40°-50°	419.5	16.4
50°-60°	304.0	11.9
60°-70°	192.6	7.5
70°-80°	97.4	3.8
80°-90°	23.8	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1008.8	39.5
0°-40°	1515.9	59.4
0°-60°	2239.5	87.7
0°-90°	2553.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2553.3	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1430	1430	1430	1430	1430	
5°	1487	1465	1418	1371	1352	142
15°	1509	1450	1310	1189	1140	424
25°	1349	1260	1082	945	892	616
35°	987	928	794	696	661	619
45°	646	609	528	476	459	502
55°	417	380	325	296	284	375
65°	244	217	183	165	172	243
75°	111	96	82	86	91	119
85°	17	17	18	22	24	23
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P580361

CATALOG NUMBER: HCC4W30D010BZ-HM43040930-41WWW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	1429.7	1429.7	1429.7	1429.7	1429.7	1429.7	1429.7	1429.7	1429.7
2.5°	1456.7	1451.6	1443.3	1433.1	1421.4	1407.9	1396.1	1389.4	1386.1
5°	1486.9	1480.3	1465.0	1443.3	1418.0	1392.7	1370.9	1357.4	1352.4
7.5°	1505.4	1495.4	1473.5	1439.9	1401.2	1364.2	1332.2	1313.7	1308.7
10°	1507.1	1495.4	1466.7	1421.4	1372.6	1323.8	1285.1	1258.2	1253.1
12.5°	1508.8	1493.7	1458.4	1404.6	1344.0	1283.4	1236.3	1204.4	1195.9
15°	1508.8	1493.7	1449.9	1386.1	1310.3	1241.4	1189.3	1152.3	1140.4
17.5°	1495.4	1478.6	1426.4	1352.4	1270.0	1192.6	1132.1	1093.4	1081.5
20°	1460.1	1441.6	1382.7	1301.9	1212.8	1132.1	1071.5	1031.1	1016.0
22.5°	1409.5	1387.7	1325.5	1238.0	1148.9	1066.4	1007.5	965.5	952.0
25°	1349.0	1327.2	1259.9	1174.1	1081.5	1004.1	945.4	906.7	891.5
27.5°	1275.0	1251.5	1185.9	1100.0	1014.3	936.9	883.1	847.8	832.6
30°	1190.9	1165.7	1103.4	1021.1	943.7	869.7	817.5	788.9	772.1
32.5°	1093.4	1071.5	1016.0	942.0	869.7	799.0	755.2	730.0	716.6
35°	987.3	975.6	928.5	864.6	793.9	735.1	696.4	672.9	661.0
37.5°	893.2	881.4	841.0	787.2	725.0	671.2	639.2	619.0	608.9
40°	804.0	793.9	755.2	709.9	656.0	608.9	582.0	566.8	556.8
42.5°	716.6	711.5	679.5	637.5	590.4	550.0	528.1	516.4	507.9
45°	645.9	639.2	608.9	568.5	528.1	494.5	476.0	467.7	459.2
47.5°	583.6	575.3	543.4	507.9	470.9	440.7	423.9	415.4	412.1
50°	523.2	514.7	486.2	450.7	413.8	391.9	378.4	370.1	368.4
52.5°	469.2	460.9	429.0	395.3	366.7	348.2	336.4	328.0	324.6
55°	417.1	407.1	380.1	348.2	324.6	307.8	296.1	287.6	284.3
57.5°	370.1	359.9	336.4	306.1	284.3	269.1	259.0	250.6	247.3
60°	324.6	316.2	294.4	265.8	247.3	233.8	223.7	217.0	213.6
62.5°	282.6	275.9	254.0	228.8	213.6	201.8	193.5	186.7	190.1
65°	243.9	237.2	217.0	195.1	183.3	171.6	164.8	164.8	171.6
67.5°	206.9	200.2	183.3	164.8	154.8	146.3	141.3	146.3	151.4
70°	173.3	166.5	151.4	136.3	127.8	121.1	121.1	126.1	129.5
72.5°	141.3	134.6	122.8	111.0	104.3	99.3	104.3	107.6	111.0
75°	111.0	105.9	95.9	87.4	82.5	80.8	85.8	89.1	90.8
77.5°	82.5	79.1	72.3	65.6	62.3	64.0	68.9	70.6	72.3
80°	57.2	55.5	50.4	47.2	47.2	48.7	52.1	53.8	55.5
82.5°	35.3	35.3	31.9	30.2	31.9	35.3	37.0	38.7	38.7
85°	16.8	18.5	16.8	16.8	18.5	21.9	21.9	23.6	23.6
87.5°	5.1	5.1	6.8	6.8	8.5	8.5	8.5	8.5	10.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)