

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580346

Luminaire Tested: **HCC4S30D010BZ-HM43040930-41WDWB**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P580346  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-10)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC4S30D010BZ-HM43040930-41WDWB  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, WHITE BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2714.7 lumens  
Efficiency: N/A  
Efficacy: 97.0 lumens/watt  
Spacing Criteria (0/90/45): 1.14 / 1.14 / 1.07  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P580346  
CATALOG NUMBER: HCC4S30D010BZ-HM43040930-41WDWB

### Luminous Intensity Polar Plot





TEST NUMBER: P580346

CATALOG NUMBER: HCC4S30D010BZ-HM43040930-41WDWB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90					90			
2	104	98	93	89	102	96	92	88	93	89	86	90	87	84	87	84	82	80					80			
3	98	89	83	78	95	88	82	78	85	80	76	83	78	75	80	77	74	72					72			
4	91	82	75	70	89	81	74	69	78	73	69	76	72	68	74	70	67	65					65			
5	86	75	68	63	84	74	68	63	72	67	62	71	65	61	69	64	61	59					59			
6	80	70	62	57	79	69	62	57	67	61	57	66	60	56	64	59	56	54					54			
7	76	64	57	52	74	64	57	52	62	56	52	61	56	51	60	55	51	49					49			
8	71	60	53	48	70	59	53	48	58	52	48	57	51	47	56	51	47	46					46			
9	67	56	49	44	66	55	49	44	54	48	44	53	48	44	52	47	44	42					42			
10	64	52	46	41	62	52	45	41	51	45	41	50	45	41	49	44	41	39					39			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	222861
5°	223923
10°	225472
15°	227722
20°	223919
25°	213618
30°	194086
35°	156555
40°	108638
45°	71310
50°	47762
55°	33999
60°	29060
65°	33389
70°	35811
75°	34456
80°	31112
85°	28588



TEST NUMBER: P580346  
 CATALOG NUMBER: HCC4S30D010BZ-HM43040930-41WDWB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	172.4	6.3
10°-20°	501.0	18.5
20°-30°	715.7	26.4
30°-40°	639.4	23.6
40°-50°	328.0	12.1
50°-60°	149.0	5.5
60°-70°	111.2	4.1
70°-80°	75.6	2.8
80°-90°	22.4	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1389.1	51.2
0°-40°	2028.5	74.7
0°-60°	2505.5	92.3
0°-90°	2714.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2714.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1807	
5°	1808	172
15°	1783	501
25°	1570	716
35°	1040	639
45°	409	328
55°	158	149
65°	114	111
75°	72	76
85°	20	22
90°	0	



TEST NUMBER: P580346  
CATALOG NUMBER: HCC4S30D010BZ-HM43040930-41WDWB

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1806.8
2.5°	1800.2
5°	1808.5
7.5°	1808.5
10°	1800.2
12.5°	1791.7
15°	1783.3
17.5°	1758.1
20°	1705.9
22.5°	1642.0
25°	1569.6
27.5°	1478.8
30°	1362.7
32.5°	1214.6
35°	1039.7
37.5°	853.0
40°	674.7
42.5°	526.6
45°	408.8
47.5°	319.7
50°	248.9
52.5°	195.1
55°	158.1
57.5°	132.9
60°	117.8
62.5°	114.4
65°	114.4
67.5°	111.0
70°	99.3
72.5°	85.8
75°	72.3
77.5°	57.2
80°	43.8
82.5°	31.9
85°	20.2
87.5°	8.5
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)