

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580389

Luminaire Tested: **HCC4S30D010BZ-HM43040940-41WDC**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580389
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-7)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4S30D010BZ-HM43040940-41WDC
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2975.1 lumens
Efficiency: N/A
Efficacy: 106.3 lumens/watt
Spacing Criteria (0/90/45): 1.25 / 1.25 / 1.11
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580389
CATALOG NUMBER: HCC4S30D010BZ-HM43040940-41WDC

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P580389

CATALOG NUMBER: HCC4S30D010BZ-HM43040940-41WDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20								
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																											
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	97	95	94	92																											
2	107	101	97	93	104	100	96	92	96	93	90	93	91	88	91	88	86	85																											
3	101	93	88	84	98	92	87	83	89	85	82	87	83	80	85	82	79	77																											
4	95	86	80	76	93	85	79	75	83	78	74	81	77	73	79	75	72	71																											
5	89	80	73	69	87	79	73	68	77	72	68	75	71	67	74	70	66	65																											
6	84	74	67	63	82	73	67	62	72	66	62	70	65	62	69	65	61	60																											
7	79	69	62	57	78	68	62	57	67	61	57	65	60	57	64	60	56	55																											
8	75	64	57	53	73	63	57	53	62	57	53	61	56	52	60	56	52	51																											
9	70	60	53	49	69	59	53	49	58	53	49	57	52	48	56	52	48	47																											
10	67	56	50	45	66	55	49	45	55	49	45	54	49	45	53	48	45	43																											

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	240339
5°	243857
10°	251511
15°	268738
20°	284772
25°	281639
30°	252780
35°	196744
40°	133289
45°	83206
50°	36018
55°	12086
60°	3034
65°	2043
70°	1262
75°	858
80°	1279
85°	0



TEST NUMBER: P580389
 CATALOG NUMBER: HCC4S30D010BZ-HM43040940-41WDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	189.2	6.4
10°-20°	597.4	20.1
20°-30°	936.0	31.5
30°-40°	807.9	27.2
40°-50°	371.5	12.5
50°-60°	63.1	2.1
60°-70°	7.1	0.2
70°-80°	2.6	0.1
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1722.6	57.9
0°-40°	2530.5	85.1
0°-60°	2965.1	99.7
0°-90°	2975.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2975.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1948	
5°	1970	189
15°	2104	597
25°	2069	936
35°	1307	808
45°	477	372
55°	56	63
65°	7	7
75°	2	3
85°	0	0
90°	0	



TEST NUMBER: P580389
CATALOG NUMBER: HCC4S30D010BZ-HM43040940-41WDC

CANDELA DISTRIBUTION (FULL):

0°	
0°	1948.5
2.5°	1948.5
5°	1969.5
7.5°	1988.8
10°	2008.1
12.5°	2048.4
15°	2104.5
17.5°	2151.9
20°	2169.5
22.5°	2143.1
25°	2069.4
27.5°	1950.2
30°	1774.8
32.5°	1553.8
35°	1306.6
37.5°	1057.5
40°	827.8
42.5°	633.1
45°	477.0
47.5°	335.0
50°	187.7
52.5°	103.4
55°	56.2
57.5°	28.1
60°	12.3
62.5°	8.8
65°	7.0
67.5°	5.3
70°	3.5
72.5°	3.5
75°	1.8
77.5°	1.8
80°	1.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)