

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580394

Luminaire Tested: **HCC4W30D010MW-HM43040940-41RWWC**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580394
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-14)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W30D010MW-HM43040940-41RWWC
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2703.3 lumens
Efficiency: N/A
Efficacy: 96.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.15 / 1.21
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580394
CATALOG NUMBER: HCC4W30D010MW-HM43040940-41RWWC

Luminous Intensity Polar Plot





TEST NUMBER: P580394

CATALOG NUMBER: HCC4W30D010MW-HM43040940-41RWWC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100				
1	111	107	103	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88				88				
2	102	95	90	85	100	94	88	84	90	86	82	87	83	80	84	81	78	76				76				
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67				67				
4	87	77	69	63	85	76	68	63	73	67	62	71	66	61	69	64	60	58				58				
5	81	70	61	56	79	68	61	55	66	60	55	65	59	54	63	58	54	52				52				
6	75	63	55	49	74	62	55	49	61	54	49	59	53	48	58	52	48	46				46				
7	70	58	50	44	69	57	49	44	56	49	44	54	48	44	53	47	43	41				41				
8	66	53	45	40	64	53	45	40	51	44	40	50	44	39	49	43	39	37				37				
9	62	49	42	36	60	49	41	36	47	41	36	46	40	36	45	40	36	34				34				
10	58	46	38	33	57	45	38	33	44	38	33	43	37	33	42	37	33	31				31				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	160016	160016	160016
5°	166484	161494	159748
10°	171929	162923	159404
15°	177958	163414	159378
20°	178568	159470	157396
25°	172258	151503	152687
30°	160302	141074	145062
35°	144388	129090	133833
40°	127299	117429	122775
45°	111308	105796	110994
50°	98575	95197	100244
55°	86685	84083	87481
60°	77412	71787	73958
65°	68062	58343	57321
70°	59433	42988	39201
75°	49277	25925	20921
80°	37363	9944	6251
85°	17407	2547	2547



TEST NUMBER: P580394
 CATALOG NUMBER: HCC4W30D010MW-HM43040940-41RWWC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	125.1	4.6
10°-20°	365.1	13.5
20°-30°	528.8	19.6
30°-40°	557.9	20.6
40°-50°	482.8	17.9
50°-60°	357.7	13.2
60°-70°	206.2	7.6
70°-80°	72.0	2.7
80°-90°	7.6	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1019.1	37.7
0°-40°	1577.0	58.3
0°-60°	2417.5	89.4
0°-90°	2703.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2703.3	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1297	1297	1297	1297	1297	
5°	1345	1327	1304	1294	1290	129
15°	1394	1348	1280	1250	1248	392
25°	1266	1203	1113	1106	1122	579
35°	959	915	857	877	889	599
45°	638	621	606	629	636	495
55°	403	394	391	405	407	364
65°	233	219	200	189	196	233
75°	103	88	54	44	44	111
85°	12	7	2	2	2	19
90°	0	0	0	0	0	



TEST NUMBER: P580394

CATALOG NUMBER: HCC4W30D010MW-HM43040940-41RWWC

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	1297.3	1297.3	1297.3	1297.3	1297.3	1297.3	1297.3	1297.3	1297.3
2.5°	1316.6	1313.0	1307.8	1300.8	1293.7	1288.5	1286.7	1285.0	1285.0
5°	1344.6	1337.6	1327.1	1313.0	1304.3	1299.0	1293.7	1290.2	1290.2
7.5°	1363.9	1356.9	1341.1	1321.8	1309.5	1299.0	1292.0	1286.7	1286.7
10°	1372.7	1363.9	1344.6	1320.1	1300.8	1286.7	1276.2	1272.7	1272.7
12.5°	1383.2	1372.7	1346.4	1314.8	1290.2	1272.7	1262.2	1258.7	1258.7
15°	1393.6	1381.5	1348.1	1311.3	1279.7	1258.7	1249.9	1248.1	1248.1
17.5°	1388.5	1372.7	1334.1	1290.2	1255.2	1234.1	1225.3	1225.3	1227.2
20°	1360.4	1344.6	1300.8	1251.6	1214.9	1199.1	1192.1	1195.6	1199.1
22.5°	1318.3	1299.0	1251.6	1204.4	1165.8	1151.8	1151.8	1157.0	1162.3
25°	1265.7	1248.1	1202.6	1150.0	1113.2	1102.6	1106.2	1114.9	1121.9
27.5°	1206.1	1186.8	1139.5	1090.4	1053.6	1048.4	1057.0	1069.3	1072.8
30°	1125.5	1109.7	1069.3	1022.1	990.5	988.7	1001.0	1009.8	1018.5
32.5°	1048.4	1030.8	992.2	946.6	923.8	925.6	939.6	950.1	955.4
35°	958.9	943.1	915.1	878.3	857.3	860.8	876.6	887.1	888.8
37.5°	874.8	864.3	836.2	808.2	792.4	799.4	813.4	825.7	825.7
40°	790.6	781.8	760.8	738.1	729.3	738.1	752.0	762.5	762.5
42.5°	710.0	704.8	687.2	671.4	666.2	678.4	690.7	699.5	697.7
45°	638.1	632.8	620.6	608.3	606.5	618.8	629.3	634.6	636.3
47.5°	573.2	569.8	559.3	550.5	550.5	562.8	571.4	576.7	578.6
50°	513.7	510.2	501.4	494.4	496.1	508.4	515.4	520.7	522.4
52.5°	454.0	452.3	445.2	436.5	441.7	450.5	459.3	462.8	464.5
55°	403.1	403.1	394.5	387.5	391.0	399.7	405.0	406.8	406.8
57.5°	357.6	355.9	345.4	338.3	340.1	348.9	352.4	354.1	354.1
60°	313.8	312.0	301.5	291.0	291.0	296.2	298.0	299.8	299.8
62.5°	271.7	269.9	257.7	248.9	245.5	243.6	243.6	247.1	254.1
65°	233.2	231.4	219.2	205.1	199.9	194.6	189.3	192.9	196.4
67.5°	198.1	194.6	182.3	170.1	157.8	149.0	140.2	145.5	152.5
70°	164.8	161.3	147.2	133.2	119.2	105.1	98.1	105.1	108.7
72.5°	133.2	129.7	115.7	101.6	84.1	70.2	68.4	70.2	71.9
75°	103.4	101.6	87.6	71.9	54.4	43.9	43.9	43.9	43.9
77.5°	77.2	73.7	59.6	45.6	31.6	24.6	22.8	22.8	22.8
80°	52.6	49.1	36.8	26.3	14.0	10.5	10.5	8.8	8.8
82.5°	29.8	28.1	19.3	10.5	5.3	3.5	3.5	3.5	3.5
85°	12.3	10.5	7.0	3.5	1.8	1.8	1.8	1.8	1.8
87.5°	1.8	1.8	1.8	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)