

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580400

Luminaire Tested: **HCC4W35D010SL-HM43040827-41WWBB**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580400
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-17)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W35D010SL-HM43040827-41WWBB
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2637.1 lumens
Efficiency: N/A
Efficacy: 78.3 lumens/watt
Spacing Criteria (0/90/45): 1.11 / 1.04 / 1.12
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 33.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580400
CATALOG NUMBER: HCC4W35D010SL-HM43040827-41WWBB

Luminous Intensity Polar Plot





TEST NUMBER: P580400

CATALOG NUMBER: HCC4W35D010SL-HM43040827-41WWBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	108	104	101	109	105	102	100	101	99	97	97	95	94	94	92	91	89								
2	103	97	91	87	101	95	90	86	92	87	84	88	85	82	85	83	80	78								
3	96	87	80	75	94	86	79	74	83	78	73	80	76	72	78	74	71	69								
4	89	79	72	66	87	78	71	65	75	69	65	73	68	64	71	67	63	61								
5	83	72	64	58	81	71	64	58	69	62	58	67	61	57	65	60	56	55								
6	77	66	58	52	75	65	57	52	63	57	52	61	56	51	60	55	51	49								
7	72	60	53	47	71	59	52	47	58	51	47	57	51	46	55	50	46	44								
8	68	56	48	43	66	55	48	43	54	47	42	53	47	42	51	46	42	40								
9	64	52	44	39	62	51	44	39	50	43	39	49	43	39	48	43	39	37								
10	60	48	41	36	59	47	41	36	46	40	36	46	40	36	45	39	36	34								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	188312	188312	188312
5°	199518	187681	178271
10°	207800	184691	167820
15°	215756	180257	157795
20°	217776	171598	145963
25°	210732	158730	133593
30°	197034	143823	121562
35°	175618	127870	109214
40°	153513	111198	97206
45°	133723	94336	84096
50°	116689	80019	72113
55°	102276	66320	58364
60°	89475	53581	42875
65°	77985	39927	24079
70°	68125	25858	7826
75°	55854	13439	2097
80°	41696	6180	1492
85°	24625	2972	2972



TEST NUMBER: P580400
 CATALOG NUMBER: HCC4W35D010SL-HM43040827-41WWBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	144.1	5.5
10°-20°	403.3	15.3
20°-30°	557.6	21.1
30°-40°	560.7	21.3
40°-50°	452.4	17.2
50°-60°	305.9	11.6
60°-70°	155.7	5.9
70°-80°	49.9	1.9
80°-90°	7.6	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1105.0	41.9
0°-40°	1665.6	63.2
0°-60°	2423.9	91.9
0°-90°	2637.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2637.1	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1527	1527	1527	1527	1527	
5°	1611	1581	1516	1462	1440	155
15°	1690	1598	1412	1277	1236	476
25°	1548	1414	1166	1023	982	709
35°	1166	1053	849	743	725	729
45°	767	686	541	482	482	594
55°	476	410	308	269	271	427
65°	267	217	137	89	82	268
75°	117	82	28	6	4	126
85°	17	9	2	2	2	23
90°	0	0	0	0	0	



TEST NUMBER: P580400

CATALOG NUMBER: HCC4W35D010SL-HM43040827-41WWBB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	1526.7	1526.7	1526.7	1526.7	1526.7	1526.7	1526.7	1526.7	1526.7
2.5°	1568.0	1559.3	1550.6	1535.4	1518.1	1500.7	1489.7	1481.1	1476.8
5°	1611.4	1600.6	1581.0	1548.4	1515.8	1485.5	1461.5	1446.4	1439.8
7.5°	1646.2	1630.9	1598.3	1552.8	1502.8	1455.0	1424.7	1403.0	1394.2
10°	1659.1	1641.8	1598.3	1537.6	1474.6	1416.0	1372.5	1350.8	1339.9
12.5°	1674.4	1654.9	1600.6	1524.6	1446.4	1376.9	1326.9	1298.7	1287.9
15°	1689.6	1663.5	1598.3	1505.0	1411.6	1331.3	1277.0	1248.8	1235.7
17.5°	1689.6	1659.1	1581.0	1472.4	1366.0	1281.4	1220.6	1188.0	1177.1
20°	1659.1	1624.4	1539.8	1420.3	1307.3	1216.2	1157.5	1124.9	1112.0
22.5°	1611.4	1572.4	1481.1	1357.3	1237.9	1148.8	1090.2	1059.8	1046.8
25°	1548.4	1509.3	1413.8	1285.6	1166.3	1077.1	1022.8	994.6	981.6
27.5°	1474.6	1431.2	1335.6	1207.5	1090.2	1005.5	955.5	929.5	918.6
30°	1383.4	1342.2	1248.8	1122.8	1009.8	931.7	886.0	862.2	853.5
32.5°	1277.0	1242.2	1151.0	1033.7	927.3	855.7	814.3	794.9	786.1
35°	1166.3	1133.7	1053.3	944.7	849.2	781.9	742.7	729.7	725.3
37.5°	1062.0	1033.7	955.5	855.7	768.8	710.1	675.4	666.8	662.4
40°	953.4	933.8	862.2	771.0	690.6	638.4	610.2	603.7	603.7
42.5°	855.7	833.9	771.0	688.4	616.7	564.7	545.1	538.6	540.8
45°	766.6	744.9	686.3	610.2	540.8	497.4	482.1	482.1	482.1
47.5°	684.1	664.5	610.2	532.1	475.6	440.8	425.7	425.7	427.8
50°	608.1	595.0	534.2	466.9	417.0	384.4	373.5	371.4	375.8
52.5°	536.4	521.2	466.9	406.1	358.3	332.3	321.5	319.2	321.5
55°	475.6	458.3	410.5	351.8	308.4	282.3	269.3	267.2	271.4
57.5°	417.0	404.0	353.9	301.9	260.7	234.6	223.7	219.3	221.5
60°	362.7	349.7	304.0	254.1	217.2	191.1	175.9	171.5	173.8
62.5°	312.7	301.9	258.4	210.6	173.8	149.8	134.7	123.8	128.1
65°	267.2	256.3	217.2	169.4	136.8	110.7	89.0	80.4	82.5
67.5°	228.1	215.0	178.0	134.7	102.1	73.8	49.9	45.6	45.6
70°	188.9	175.9	143.3	104.2	71.7	39.1	21.7	21.7	21.7
72.5°	152.0	141.2	110.7	78.2	45.6	17.4	8.7	8.7	8.7
75°	117.2	108.6	82.5	54.3	28.2	8.7	6.5	4.4	4.4
77.5°	86.9	78.2	58.7	36.9	17.4	4.4	4.4	4.4	4.4
80°	58.7	52.2	39.1	21.7	8.7	2.1	2.1	2.1	2.1
82.5°	34.7	30.3	21.7	10.9	4.4	2.1	2.1	2.1	2.1
85°	17.4	13.0	8.7	4.4	2.1	2.1	2.1	2.1	2.1
87.5°	4.4	2.1	2.1	2.1	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)