

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580408

Luminaire Tested: **HCC4S35D010MW-HM43040827-41MDW**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P580408  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-6)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC4S35D010MW-HM43040827-41MDW  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" MEDIUM DISTRIBUTION, WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3136.7 lumens  
Efficiency: N/A  
Efficacy: 93.1 lumens/watt  
Spacing Criteria (0/90/45): 1.04 / 1.04 / 1.01  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 33.7  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P580408  
CATALOG NUMBER: HCC4S35D010MW-HM43040827-41MDW

### Luminous Intensity Polar Plot





TEST NUMBER: P580408

CATALOG NUMBER: HCC4S35D010MW-HM43040827-41MDW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	104	101	109	105	102	100	101	99	97	97	95	94	94	92	91	89			89
2	104	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	81	79			79
3	97	88	82	76	94	87	81	76	84	79	75	81	77	73	79	75	72	70			70
4	90	80	73	68	88	79	73	67	77	71	67	75	70	66	73	68	65	63			63
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57			57
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	54	52			52
7	74	63	55	50	73	62	55	50	61	54	50	59	54	49	58	53	49	47			47
8	70	58	51	46	68	58	51	46	56	50	46	55	50	45	54	49	45	44			44
9	66	54	47	42	65	54	47	42	53	46	42	52	46	42	51	46	42	40			40
10	62	51	44	39	61	50	44	39	49	43	39	48	43	39	48	42	39	37			37

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	265921
5°	264522
10°	259690
15°	254219
20°	243346
25°	226275
30°	200267
35°	158061
40°	118283
45°	90986
50°	73802
55°	61224
60°	54149
65°	50112
70°	46234
75°	42462
80°	38570
85°	30711



TEST NUMBER: P580408  
 CATALOG NUMBER: HCC4S35D010MW-HM43040827-41MDW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	202.0	6.4
10°-20°	558.3	17.8
20°-30°	758.1	24.2
30°-40°	656.7	20.9
40°-50°	412.3	13.1
50°-60°	259.3	8.3
60°-70°	170.4	5.4
70°-80°	94.0	3.0
80°-90°	25.7	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1518.3	48.4
0°-40°	2175.0	69.3
0°-60°	2846.6	90.8
0°-90°	3136.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3136.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2156	
5°	2136	202
15°	1991	558
25°	1663	758
35°	1050	657
45°	522	412
55°	285	259
65°	172	170
75°	89	94
85°	22	26
90°	0	



TEST NUMBER: P580408

CATALOG NUMBER: HCC4S35D010MW-HM43040827-41MDW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2155.9
2.5°	2142.9
5°	2136.4
7.5°	2114.7
10°	2073.4
12.5°	2032.1
15°	1990.8
17.5°	1934.3
20°	1853.9
22.5°	1762.7
25°	1662.6
27.5°	1547.4
30°	1406.1
32.5°	1234.5
35°	1049.7
37.5°	880.2
40°	734.6
42.5°	619.4
45°	521.6
47.5°	447.7
50°	384.6
52.5°	330.3
55°	284.7
57.5°	245.6
60°	219.5
62.5°	195.6
65°	171.7
67.5°	147.8
70°	128.2
72.5°	106.4
75°	89.1
77.5°	69.6
80°	54.3
82.5°	37.0
85°	21.7
87.5°	8.7
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)