

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580418

Luminaire Tested: **HCC4W35D010MB-HM43040830-41WDWB**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580418
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-10)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W35D010MB-HM43040830-41WDWB
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3793.0 lumens
Efficiency: N/A
Efficacy: 112.6 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.14 / 1.07
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 33.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580418
CATALOG NUMBER: HCC4W35D010MB-HM43040830-41WDWB

Luminous Intensity Polar Plot





TEST NUMBER: P580418

CATALOG NUMBER: HCC4W35D010MB-HM43040830-41WDWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90	90	90	90
2	104	98	93	89	102	96	92	88	93	89	86	90	87	84	87	84	82	80	80	80	80
3	98	89	83	78	95	88	82	78	85	80	76	83	78	75	80	77	74	72	72	72	72
4	91	82	75	70	89	81	74	69	78	73	69	76	72	68	74	70	67	65	65	65	65
5	86	75	68	63	84	74	68	63	72	67	62	71	65	61	69	64	61	59	59	59	59
6	80	70	62	57	79	69	62	57	67	61	57	66	60	56	64	59	56	54	54	54	54
7	76	64	57	52	74	64	57	52	62	56	52	61	56	51	60	55	51	49	49	49	49
8	71	60	53	48	70	59	53	48	58	52	48	57	51	47	56	51	47	46	46	46	46
9	67	56	49	44	66	55	49	44	54	48	44	53	48	44	52	47	44	42	42	42	42
10	64	52	46	41	62	52	45	41	51	45	41	50	45	41	49	44	41	39	39	39	39

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	311398
5°	312873
10°	315025
15°	318182
20°	312875
25°	298474
30°	271196
35°	218744
40°	151774
45°	99638
50°	66759
55°	47525
60°	40605
65°	46639
70°	50021
75°	48134
80°	43401
85°	39910



TEST NUMBER: P580418
 CATALOG NUMBER: HCC4W35D010MB-HM43040830-41WDWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	240.8	6.3
10°-20°	700.0	18.5
20°-30°	1000.1	26.4
30°-40°	893.4	23.6
40°-50°	458.2	12.1
50°-60°	208.3	5.5
60°-70°	155.3	4.1
70°-80°	105.7	2.8
80°-90°	31.3	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1940.8	51.2
0°-40°	2834.2	74.7
0°-60°	3500.7	92.3
0°-90°	3793.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3793.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2525	
5°	2527	241
15°	2492	700
25°	2193	1000
35°	1453	893
45°	571	458
55°	221	208
65°	160	155
75°	101	106
85°	28	31
90°	0	



TEST NUMBER: P580418
CATALOG NUMBER: HCC4W35D010MB-HM43040830-41WDWB

CANDELA DISTRIBUTION (FULL):

0°	
0°	2524.6
2.5°	2515.2
5°	2526.9
7.5°	2526.9
10°	2515.2
12.5°	2503.4
15°	2491.7
17.5°	2456.4
20°	2383.6
22.5°	2294.2
25°	2193.1
27.5°	2066.1
30°	1904.1
32.5°	1697.1
35°	1452.7
37.5°	1191.8
40°	942.6
42.5°	735.8
45°	571.2
47.5°	446.6
50°	347.9
52.5°	272.7
55°	221.0
57.5°	185.7
60°	164.6
62.5°	159.8
65°	159.8
67.5°	155.1
70°	138.7
72.5°	119.9
75°	101.0
77.5°	79.9
80°	61.1
82.5°	44.6
85°	28.2
87.5°	11.8
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)