

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580448

Luminaire Tested: **HCC4S35D010MW-HM43040835-41RWWC**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580448
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-14)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4S35D010MW-HM43040835-41RWWC
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3634.2 lumens
Efficiency: N/A
Efficacy: 107.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.15 / 1.21
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 33.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580448
CATALOG NUMBER: HCC4S35D010MW-HM43040835-41RWWC

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P580448

CATALOG NUMBER: HCC4S35D010MW-HM43040835-41RWWC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	111	107	103	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88				88
2	102	95	90	85	100	94	88	84	90	86	82	87	83	80	84	81	78	76				76
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67				67
4	87	77	69	63	85	76	68	63	73	67	62	71	66	61	69	64	60	58				58
5	81	70	61	56	79	68	61	55	66	60	55	65	59	54	63	58	54	52				52
6	75	63	55	49	74	62	55	49	61	54	49	59	53	48	58	52	48	46				46
7	70	58	50	44	69	57	49	44	56	49	44	54	48	44	53	47	43	41				41
8	66	53	45	40	64	53	45	40	51	44	40	50	44	39	49	43	39	37				37
9	62	49	42	36	60	49	41	36	47	41	36	46	40	36	45	40	36	34				34
10	58	46	38	33	57	45	38	33	44	38	33	43	37	33	42	37	33	31				31

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	215115	215115	215115
5°	223811	217100	214773
10°	231133	219022	214300
15°	239253	219690	214275
20°	240064	214377	211594
25°	231582	203669	205275
30°	215492	189656	195026
35°	194109	173525	179925
40°	171144	157860	165074
45°	149632	142253	149231
50°	132501	127992	134766
55°	116577	113028	117566
60°	104054	96530	99417
65°	91498	78394	77022
70°	79881	57810	52689
75°	66243	34837	28070
80°	50220	13425	8382
85°	23351	3397	3397



TEST NUMBER: P580448

CATALOG NUMBER: HCC4S35D010MW-HM43040835-41RWWC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	168.2	4.6
10°-20°	490.9	13.5
20°-30°	710.9	19.6
30°-40°	750.0	20.6
40°-50°	649.1	17.9
50°-60°	480.9	13.2
60°-70°	277.2	7.6
70°-80°	96.8	2.7
80°-90°	10.2	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1370.0	37.7
0°-40°	2120.1	58.3
0°-60°	3250.1	89.4
0°-90°	3634.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3634.2	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1744	1744	1744	1744	1744	
5°	1808	1784	1753	1739	1735	174
15°	1874	1812	1720	1680	1678	527
25°	1702	1617	1496	1487	1508	779
35°	1289	1230	1152	1178	1195	805
45°	858	834	816	846	856	666
55°	542	530	526	544	547	489
65°	314	295	269	254	264	313
75°	139	118	73	59	59	150
85°	16	9	2	2	2	26
90°	0	0	0	0	0	



TEST NUMBER: P580448

CATALOG NUMBER: HCC4S35D010MW-HM43040835-41RWWC

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	1744.0	1744.0	1744.0	1744.0	1744.0	1744.0	1744.0	1744.0	1744.0
2.5°	1770.0	1765.2	1758.2	1748.7	1739.3	1732.2	1729.8	1727.5	1727.5
5°	1807.6	1798.2	1784.0	1765.2	1753.4	1746.4	1739.3	1734.6	1734.6
7.5°	1833.6	1824.1	1802.9	1776.9	1760.5	1746.4	1736.9	1729.8	1729.8
10°	1845.4	1833.6	1807.6	1774.7	1748.7	1729.8	1715.7	1711.0	1711.0
12.5°	1859.4	1845.4	1810.0	1767.6	1734.6	1711.0	1696.9	1692.2	1692.2
15°	1873.6	1857.1	1812.3	1762.9	1720.4	1692.2	1680.4	1678.0	1678.0
17.5°	1866.5	1845.4	1793.5	1734.6	1687.5	1659.1	1647.3	1647.3	1649.7
20°	1828.9	1807.6	1748.7	1682.7	1633.2	1612.0	1602.6	1607.3	1612.0
22.5°	1772.3	1746.4	1682.7	1619.1	1567.2	1548.4	1548.4	1555.5	1562.5
25°	1701.6	1678.0	1616.8	1546.1	1496.5	1482.4	1487.1	1498.9	1508.3
27.5°	1621.5	1595.5	1531.9	1465.9	1416.4	1409.4	1421.1	1437.6	1442.3
30°	1513.0	1491.8	1437.6	1374.0	1331.6	1329.2	1345.7	1357.5	1369.3
32.5°	1409.4	1385.8	1334.0	1272.6	1242.0	1244.4	1263.3	1277.3	1284.4
35°	1289.1	1268.0	1230.2	1180.8	1152.4	1157.2	1178.4	1192.6	1194.9
37.5°	1176.0	1161.9	1124.1	1086.5	1065.2	1074.7	1093.5	1110.1	1110.1
40°	1062.9	1051.1	1022.8	992.2	980.4	992.2	1011.0	1025.2	1025.2
42.5°	954.5	947.4	923.8	902.7	895.6	912.0	928.5	940.3	938.0
45°	857.8	850.8	834.2	817.8	815.5	832.0	846.0	853.1	855.5
47.5°	770.6	765.9	751.8	740.0	740.0	756.6	768.3	775.3	777.7
50°	690.5	685.9	674.1	664.6	667.0	683.5	692.8	699.9	702.3
52.5°	610.4	608.1	598.6	586.8	593.9	605.7	617.4	622.1	624.5
55°	542.1	542.1	530.3	520.9	525.6	537.4	544.4	546.7	546.7
57.5°	480.7	478.4	464.3	454.9	457.2	469.0	473.7	476.0	476.0
60°	421.8	419.5	405.3	391.3	391.3	398.3	400.6	403.0	403.0
62.5°	365.3	362.9	346.4	334.6	329.9	327.5	327.5	332.3	341.7
65°	313.5	311.1	294.6	275.7	268.6	261.6	254.5	259.2	263.9
67.5°	266.3	261.6	245.1	228.6	212.1	200.3	188.5	195.6	205.0
70°	221.5	216.8	197.9	179.2	160.3	141.4	132.0	141.4	146.1
72.5°	179.2	174.4	155.6	136.7	113.1	94.3	91.9	94.3	96.7
75°	139.0	136.7	117.8	96.7	73.1	58.9	58.9	58.9	58.9
77.5°	103.7	99.0	80.1	61.3	42.4	33.0	30.7	30.7	30.7
80°	70.7	66.0	49.5	35.4	18.9	14.2	14.2	11.8	11.8
82.5°	40.0	37.7	26.0	14.2	7.1	4.7	4.7	4.7	4.7
85°	16.5	14.2	9.4	4.7	2.4	2.4	2.4	2.4	2.4
87.5°	2.4	2.4	2.4	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)