

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580432

Luminaire Tested: **HCC4S35D010SL-HM43040830-41WWBB**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P580432  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-17)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC4S35D010SL-HM43040830-41WWBB  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2853.0 lumens  
Efficiency: N/A  
Efficacy: 84.7 lumens/watt  
Spacing Criteria (0/90/45): 1.11 / 1.04 / 1.12  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 33.7  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P580432  
CATALOG NUMBER: HCC4S35D010SL-HM43040830-41WWBB

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P580432

CATALOG NUMBER: HCC4S35D010SL-HM43040830-41WWBB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	111	108	104	101	109	105	102	100	101	99	97	97	95	94	94	92	91	89					89			
2	103	97	91	87	101	95	90	86	92	87	84	88	85	82	85	83	80	78					78			
3	96	87	80	75	94	86	79	74	83	78	73	80	76	72	78	74	71	69					69			
4	89	79	72	66	87	78	71	65	75	69	65	73	68	64	71	67	63	61					61			
5	83	72	64	58	81	71	64	58	69	62	58	67	61	57	65	60	56	55					55			
6	77	66	58	52	75	65	57	52	63	57	52	61	56	51	60	55	51	49					49			
7	72	60	53	47	71	59	52	47	58	51	47	57	51	46	55	50	46	44					44			
8	68	56	48	43	66	55	48	43	54	47	42	53	47	42	51	46	42	40					40			
9	64	52	44	39	62	51	44	39	50	43	39	49	43	39	48	43	39	37					37			
10	60	48	41	36	59	47	41	36	46	40	36	46	40	36	45	39	36	34					34			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	203730	203730	203730
5°	215850	203047	192882
10°	224821	199809	181560
15°	233430	195019	170718
20°	235615	185657	157895
25°	227989	171713	144535
30°	213157	155602	131517
35°	189983	138320	118173
40°	166088	120295	105176
45°	144678	102046	90986
50°	126246	86562	77985
55°	110663	71740	63159
60°	96802	57948	46353
65°	84348	43195	26034
70°	73751	27986	8475
75°	60477	14583	2240
80°	45034	6677	1705
85°	26606	3397	3397



TEST NUMBER: P580432  
 CATALOG NUMBER: HCC4S35D010SL-HM43040830-41WWBB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	155.9	5.5
10°-20°	436.3	15.3
20°-30°	603.2	21.1
30°-40°	606.6	21.3
40°-50°	489.5	17.2
50°-60°	331.0	11.6
60°-70°	168.4	5.9
70°-80°	53.9	1.9
80°-90°	8.3	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1195.4	41.9
0°-40°	1802.0	63.2
0°-60°	2622.4	91.9
0°-90°	2853.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2853.0	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	1652	1652	1652	1652	1652	
5°	1743	1710	1640	1581	1558	168
15°	1828	1729	1527	1382	1337	515
25°	1675	1530	1262	1107	1062	767
35°	1262	1140	919	804	785	788
45°	829	742	585	522	522	643
55°	515	444	334	291	294	462
65°	289	235	148	96	89	290
75°	127	89	31	7	5	137
85°	19	9	2	2	2	25
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P580432

CATALOG NUMBER: HCC4S35D010SL-HM43040830-41WWBB

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	1651.7	1651.7	1651.7	1651.7	1651.7	1651.7	1651.7	1651.7	1651.7
2.5°	1696.3	1686.9	1677.6	1661.2	1642.3	1623.5	1611.8	1602.4	1597.7
5°	1743.3	1731.6	1710.5	1675.2	1639.9	1607.1	1581.2	1564.8	1557.8
7.5°	1781.0	1764.5	1729.3	1679.9	1625.9	1574.2	1541.2	1517.7	1508.4
10°	1795.0	1776.3	1729.3	1663.4	1595.3	1531.9	1484.9	1461.4	1449.6
12.5°	1811.4	1790.3	1731.6	1649.4	1564.8	1489.6	1435.6	1405.0	1393.3
15°	1828.0	1799.7	1729.3	1628.2	1527.2	1440.3	1381.5	1350.9	1336.9
17.5°	1828.0	1795.0	1710.5	1592.9	1477.8	1386.2	1320.5	1285.2	1273.5
20°	1795.0	1757.5	1665.8	1536.6	1414.4	1315.8	1252.2	1217.1	1202.9
22.5°	1743.3	1701.1	1602.4	1468.4	1339.2	1242.9	1179.4	1146.6	1132.4
25°	1675.2	1632.9	1529.5	1391.0	1261.7	1165.4	1106.6	1076.1	1062.0
27.5°	1595.3	1548.3	1444.9	1306.3	1179.4	1087.8	1033.7	1005.6	993.8
30°	1496.6	1452.0	1350.9	1214.7	1092.5	1007.9	958.7	932.8	923.4
32.5°	1381.5	1344.0	1245.3	1118.4	1003.3	925.7	881.1	860.0	850.5
35°	1261.7	1226.4	1139.5	1022.1	918.6	845.8	803.5	789.4	784.8
37.5°	1149.0	1118.4	1033.7	925.7	831.8	768.3	730.7	721.3	716.6
40°	1031.5	1010.3	932.8	834.1	747.1	690.8	660.2	653.2	653.2
42.5°	925.7	902.2	834.1	744.8	667.3	610.9	589.8	582.7	585.0
45°	829.4	805.9	742.4	660.2	585.0	538.1	521.6	521.6	521.6
47.5°	740.2	718.9	660.2	575.6	514.6	476.9	460.5	460.5	462.9
50°	657.9	643.7	578.0	505.1	451.1	415.9	404.1	401.7	406.4
52.5°	580.3	563.9	505.1	439.4	387.7	359.5	347.8	345.4	347.8
55°	514.6	495.8	444.1	380.6	333.6	305.4	291.3	289.0	293.7
57.5°	451.1	437.0	382.9	326.6	281.9	253.8	242.0	237.3	239.6
60°	392.4	378.2	328.9	274.9	234.9	206.7	190.3	185.6	187.9
62.5°	338.3	326.6	279.5	227.9	187.9	162.1	145.7	133.9	138.6
65°	289.0	277.3	234.9	183.2	148.0	119.8	96.3	86.9	89.2
67.5°	246.7	232.6	192.7	145.7	110.4	79.9	54.1	49.3	49.3
70°	204.5	190.3	155.1	112.7	77.6	42.3	23.5	23.5	23.5
72.5°	164.4	152.8	119.8	84.6	49.3	18.8	9.4	9.4	9.4
75°	126.9	117.5	89.2	58.8	30.6	9.4	7.1	4.7	4.7
77.5°	94.0	84.6	63.4	39.9	18.8	4.7	4.7	4.7	4.7
80°	63.4	56.4	42.3	23.5	9.4	2.4	2.4	2.4	2.4
82.5°	37.5	32.9	23.5	11.8	4.7	2.4	2.4	2.4	2.4
85°	18.8	14.0	9.4	4.7	2.4	2.4	2.4	2.4	2.4
87.5°	4.7	2.4	2.4	2.4	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)