

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580488

Luminaire Tested: **HCC4S35D010MB-HM43040927-41WWWB**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580488
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-18)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4S35D010MB-HM43040927-41WWWB
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2836.3 lumens
Efficiency: N/A
Efficacy: 84.2 lumens/watt
Spacing Criteria (0/90/45): 1.13 / 1.07 / 1.15
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 33.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580488
CATALOG NUMBER: HCC4S35D010MB-HM43040927-41WWWB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P580488

CATALOG NUMBER: HCC4S35D010MB-HM43040927-41WWWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87								
2	102	95	89	84	99	93	87	83	89	85	81	86	82	79	83	80	77	75								
3	94	85	77	72	92	83	76	71	80	75	70	78	73	69	75	71	68	66								
4	87	76	68	62	85	75	68	62	72	66	61	70	65	60	68	63	60	58								
5	81	69	61	55	79	68	60	55	66	59	54	64	58	53	62	57	53	51								
6	75	63	55	49	73	62	54	49	60	53	48	59	53	48	57	52	47	46								
7	70	58	50	44	68	57	49	44	55	48	43	54	48	43	53	47	43	41								
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37								
9	61	49	41	36	60	48	41	36	47	41	36	46	40	36	45	40	36	34								
10	58	45	38	33	57	45	38	33	44	38	33	43	37	33	42	37	33	31								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	180393	180393	180393
5°	189687	180153	173405
10°	196339	178003	165541
15°	202336	174766	158472
20°	202576	167569	149336
25°	194945	156634	140016
30°	181025	144122	130762
35°	162262	129767	120989
40°	142387	115771	111842
45°	124443	102499	103145
50°	109877	89709	92933
55°	96900	79524	83567
60°	86589	70406	73169
65°	76701	61904	61904
70°	67043	52834	52834
75°	57284	44750	50088
80°	45318	39991	45318
85°	29295	34532	42457



TEST NUMBER: P580488
 CATALOG NUMBER: HCC4S35D010MB-HM43040927-41WWWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	138.6	4.9
10°-20°	390.2	13.8
20°-30°	546.7	19.3
30°-40°	563.2	19.9
40°-50°	479.5	16.9
50°-60°	355.3	12.5
60°-70°	223.0	7.9
70°-80°	110.8	3.9
80°-90°	29.1	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1075.4	37.9
0°-40°	1638.7	57.8
0°-60°	2473.4	87.2
0°-90°	2836.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2836.3	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1462	1462	1462	1462	1462	
5°	1532	1506	1455	1414	1400	147
15°	1584	1513	1369	1269	1241	446
25°	1432	1333	1151	1051	1029	655
35°	1078	997	862	806	804	672
45°	713	665	588	576	591	554
55°	451	415	370	377	389	407
65°	263	237	212	208	212	262
75°	120	107	94	101	105	128
85°	21	21	24	28	30	27
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P580488

CATALOG NUMBER: HCC4S35D010MB-HM43040927-41WWWB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	1462.5	1462.5	1462.5	1462.5	1462.5	1462.5	1462.5	1462.5	1462.5
2.5°	1494.4	1488.7	1481.3	1468.2	1455.0	1443.8	1432.4	1426.8	1424.9
5°	1532.0	1520.7	1505.7	1481.3	1455.0	1432.4	1413.7	1404.3	1400.5
7.5°	1558.2	1547.0	1522.6	1485.0	1447.5	1413.7	1383.6	1370.5	1366.8
10°	1567.6	1554.5	1520.7	1470.0	1421.2	1379.9	1346.1	1329.2	1321.7
12.5°	1575.2	1558.2	1515.0	1455.0	1394.9	1344.2	1308.6	1286.0	1280.3
15°	1584.5	1565.7	1513.2	1440.0	1368.6	1308.6	1269.1	1248.4	1241.0
17.5°	1575.2	1554.5	1492.6	1409.9	1329.2	1263.5	1220.3	1201.6	1194.0
20°	1543.3	1520.7	1451.2	1363.0	1276.6	1209.1	1165.8	1147.0	1137.7
22.5°	1494.4	1470.0	1398.7	1304.7	1216.5	1150.9	1109.5	1090.7	1085.1
25°	1432.4	1408.0	1333.0	1237.2	1150.9	1087.0	1051.4	1034.4	1028.8
27.5°	1359.3	1334.9	1261.6	1167.7	1085.1	1025.1	996.9	980.0	976.2
30°	1271.0	1246.6	1175.3	1088.9	1011.9	955.6	933.0	919.9	918.1
32.5°	1173.3	1152.8	1087.0	1008.1	934.9	888.0	871.1	861.8	859.9
35°	1077.6	1055.1	996.9	925.6	861.8	820.4	805.5	803.5	803.5
37.5°	980.0	957.4	910.6	844.8	790.4	752.9	747.2	749.0	749.0
40°	884.3	863.6	822.3	767.8	719.0	690.9	689.0	692.7	694.6
42.5°	794.1	777.2	739.7	692.7	651.5	628.9	630.8	638.3	643.9
45°	713.4	698.3	664.6	623.3	587.6	570.8	576.4	585.7	591.3
47.5°	640.2	627.1	595.2	557.6	527.6	516.3	523.8	535.0	542.6
50°	572.6	561.3	531.3	491.9	467.5	459.9	469.4	480.6	484.3
52.5°	512.5	501.3	469.4	435.6	416.8	413.1	422.4	431.8	437.5
55°	450.6	441.2	414.9	384.9	369.8	368.0	377.3	384.9	388.6
57.5°	399.9	390.5	366.1	339.8	326.6	324.8	334.2	339.8	341.7
60°	351.0	341.7	319.1	294.7	285.4	285.4	291.0	294.7	296.6
62.5°	306.1	296.6	275.9	255.4	247.8	247.8	247.8	249.6	255.4
65°	262.8	255.4	236.6	217.8	212.1	208.4	208.4	208.4	212.1
67.5°	223.5	215.9	200.9	184.0	178.4	172.8	170.8	174.6	174.6
70°	185.9	180.2	165.2	152.1	146.5	140.8	138.9	146.5	146.5
72.5°	152.1	146.5	137.0	123.9	118.2	116.4	120.2	123.9	125.8
75°	120.2	114.5	107.0	99.5	93.9	95.8	101.4	103.3	105.1
77.5°	90.1	88.2	80.7	75.1	75.1	77.0	80.7	84.5	86.3
80°	63.8	61.9	58.2	54.4	56.3	60.0	61.9	65.8	63.8
82.5°	39.5	39.5	37.5	37.5	39.5	43.2	45.1	47.0	48.8
85°	20.7	20.7	20.7	22.5	24.4	26.3	28.2	30.0	30.0
87.5°	5.6	7.5	7.5	9.4	11.2	11.2	13.2	13.2	13.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)