

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580470

Luminaire Tested: **HCC4S35D010MB-HM43040840-41WWWB**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580470
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-18)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4S35D010MB-HM43040840-41WWWB
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 4000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3726.0 lumens
Efficiency: N/A
Efficacy: 110.6 lumens/watt
Spacing Criteria (0/90/45): 1.13 / 1.07 / 1.15
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 33.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580470
CATALOG NUMBER: HCC4S35D010MB-HM43040840-41WWWB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P580470

CATALOG NUMBER: HCC4S35D010MB-HM43040840-41WWWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87				
2	102	95	89	84	99	93	87	83	89	85	81	86	82	79	83	80	77	75				
3	94	85	77	72	92	83	76	71	80	75	70	78	73	69	75	71	68	66				
4	87	76	68	62	85	75	68	62	72	66	61	70	65	60	68	63	60	58				
5	81	69	61	55	79	68	60	55	66	59	54	64	58	53	62	57	53	51				
6	75	63	55	49	73	62	54	49	60	53	48	59	53	48	57	52	47	46				
7	70	58	50	44	68	57	49	44	55	48	43	54	48	43	53	47	43	41				
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37				
9	61	49	41	36	60	48	41	36	47	41	36	46	40	36	45	40	36	34				
10	58	45	38	33	57	45	38	33	44	38	33	43	37	33	42	37	33	31				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	236984	236984	236984
5°	249181	236663	227811
10°	257937	233839	217481
15°	265801	229599	208171
20°	266120	220139	196184
25°	256107	205765	183935
30°	237811	189343	171782
35°	213172	170468	158934
40°	187053	152096	146943
45°	163482	134665	135520
50°	144341	117860	122101
55°	127286	104491	109781
60°	113774	92485	96136
65°	100779	81312	81312
70°	88032	69387	69387
75°	75203	58761	65814
80°	59596	52564	59596
85°	38353	45287	55902



TEST NUMBER: P580470
 CATALOG NUMBER: HCC4S35D010MB-HM43040840-41WWWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	182.0	4.9
10°-20°	512.6	13.8
20°-30°	718.2	19.3
30°-40°	739.9	19.9
40°-50°	629.9	16.9
50°-60°	466.7	12.5
60°-70°	292.9	7.9
70°-80°	145.5	3.9
80°-90°	38.2	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1412.8	37.9
0°-40°	2152.7	57.8
0°-60°	3249.4	87.2
0°-90°	3726.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3726.0	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1921	1921	1921	1921	1921	
5°	2012	1978	1911	1857	1840	193
15°	2082	1988	1798	1667	1630	585
25°	1882	1751	1512	1381	1352	861
35°	1416	1310	1132	1058	1056	883
45°	937	873	772	757	777	727
55°	592	545	486	496	510	535
65°	345	311	279	274	279	344
75°	158	141	123	133	138	169
85°	27	27	32	37	40	35
90°	0	0	0	0	0	



TEST NUMBER: P580470

CATALOG NUMBER: HCC4S35D010MB-HM43040840-41WWWB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3
2.5°	1963.2	1955.8	1946.0	1928.7	1911.4	1896.6	1881.8	1874.4	1871.9
5°	2012.5	1997.7	1978.0	1946.0	1911.4	1881.8	1857.2	1844.8	1839.9
7.5°	2047.0	2032.3	2000.2	1950.8	1901.6	1857.2	1817.7	1800.4	1795.5
10°	2059.4	2042.1	1997.7	1931.1	1867.0	1812.8	1768.4	1746.1	1736.4
12.5°	2069.3	2047.0	1990.4	1911.4	1832.5	1765.9	1719.0	1689.5	1682.1
15°	2081.5	2056.9	1987.9	1891.7	1798.0	1719.0	1667.2	1640.1	1630.2
17.5°	2069.3	2042.1	1960.7	1852.2	1746.1	1659.8	1603.2	1578.4	1568.5
20°	2027.4	1997.7	1906.5	1790.5	1677.1	1588.3	1531.6	1506.9	1494.6
22.5°	1963.2	1931.1	1837.4	1714.1	1598.2	1511.9	1457.6	1433.0	1425.6
25°	1881.8	1849.8	1751.1	1625.3	1511.9	1428.0	1381.2	1358.9	1351.5
27.5°	1785.6	1753.6	1657.3	1534.0	1425.6	1346.7	1309.6	1287.4	1282.5
30°	1669.7	1637.7	1543.9	1430.5	1329.4	1255.4	1225.7	1208.5	1206.1
32.5°	1541.5	1514.4	1428.0	1324.4	1228.2	1166.6	1144.3	1132.1	1129.6
35°	1415.7	1386.1	1309.6	1215.9	1132.1	1077.8	1058.0	1055.5	1055.5
37.5°	1287.4	1257.9	1196.2	1109.8	1038.4	989.0	981.6	984.1	984.1
40°	1161.7	1134.6	1080.3	1008.7	944.6	907.6	905.2	910.1	912.6
42.5°	1043.3	1021.0	971.7	910.1	855.8	826.3	828.7	838.5	845.9
45°	937.2	917.5	873.1	818.8	772.0	749.8	757.1	769.5	776.9
47.5°	841.0	823.8	781.9	732.5	693.1	678.2	688.1	702.9	712.7
50°	752.2	737.5	698.0	646.2	614.2	604.3	616.6	631.4	636.3
52.5°	673.3	658.6	616.6	572.2	547.5	542.6	554.9	567.3	574.7
55°	591.9	579.5	545.0	505.6	485.9	483.4	495.7	505.6	510.5
57.5°	525.4	513.0	481.0	446.5	429.1	426.7	439.0	446.5	448.9
60°	461.2	448.9	419.3	387.2	374.9	374.9	382.3	387.2	389.7
62.5°	402.1	389.7	362.6	335.4	325.5	325.5	325.5	328.0	335.4
65°	345.3	335.4	310.8	286.1	278.6	273.8	273.8	273.8	278.6
67.5°	293.5	283.6	263.9	241.7	234.4	226.9	224.5	229.4	229.4
70°	244.1	236.7	217.0	199.7	192.4	185.0	182.5	192.4	192.4
72.5°	199.7	192.4	180.1	162.8	155.3	152.9	157.8	162.8	165.2
75°	157.8	150.4	140.6	130.7	123.3	125.8	133.2	135.7	138.1
77.5°	118.4	115.9	106.1	98.7	98.7	101.2	106.1	110.9	113.4
80°	83.9	81.4	76.4	71.5	74.0	78.9	81.4	86.3	83.9
82.5°	51.8	51.8	49.3	49.3	51.8	56.8	59.2	61.7	64.2
85°	27.1	27.1	27.1	29.6	32.0	34.5	37.0	39.5	39.5
87.5°	7.4	9.9	9.9	12.4	14.8	14.8	17.3	17.3	17.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)