

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P592777

Luminaire Tested: **HCC4S35D010SL-HM43040850-41RWWC**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P592777
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-14)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4S35D010SL-HM43040850-41RWWC
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 5000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3802.5 lumens
Efficiency: N/A
Efficacy: 112.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.15 / 1.21
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 33.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P592777
CATALOG NUMBER: HCC4S35D010SL-HM43040850-41RWWC

Luminous Intensity Polar Plot





TEST NUMBER: P592777

CATALOG NUMBER: HCC4S35D010SL-HM43040850-41RWWC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	103	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88								
2	102	95	90	85	100	94	88	84	90	86	82	87	83	80	84	81	78	76								
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67								
4	87	77	69	63	85	76	68	63	73	67	62	71	66	61	69	64	60	58								
5	81	70	61	56	79	68	61	55	66	60	55	65	59	54	63	58	54	52								
6	75	63	55	49	74	62	55	49	61	54	49	59	53	48	58	52	48	46								
7	70	58	50	44	69	57	49	44	56	49	44	54	48	44	53	47	43	41								
8	66	53	45	40	64	53	45	40	51	44	40	50	44	39	49	43	39	37								
9	62	49	42	36	60	49	41	36	47	41	36	46	40	36	45	40	36	34								
10	58	46	38	33	57	45	38	33	44	38	33	43	37	33	42	37	33	31								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	225069	225069	225069
5°	234187	227154	224703
10°	241830	229155	224220
15°	250337	229867	224197
20°	251169	224300	221399
25°	242293	213100	214774
30°	225462	198430	204056
35°	203099	181566	188252
40°	179066	165171	172706
45°	156557	148830	156156
50°	138642	133902	141021
55°	121974	118254	123028
60°	108890	100995	104005
65°	95730	82042	80612
70°	83596	60479	55142
75°	69293	36410	29357
80°	52564	14064	8808
85°	24484	3538	3538



TEST NUMBER: P592777
 CATALOG NUMBER: HCC4S35D010SL-HM43040850-41RWWC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	176.0	4.6
10°-20°	513.6	13.5
20°-30°	743.8	19.6
30°-40°	784.8	20.6
40°-50°	679.2	17.9
50°-60°	503.1	13.2
60°-70°	290.0	7.6
70°-80°	101.3	2.7
80°-90°	10.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1433.4	37.7
0°-40°	2218.2	58.3
0°-60°	3400.5	89.4
0°-90°	3802.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3802.5	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1825	1825	1825	1825	1825	
5°	1891	1867	1835	1820	1815	182
15°	1960	1896	1800	1758	1756	551
25°	1780	1692	1566	1556	1578	815
35°	1349	1287	1206	1233	1250	842
45°	898	873	853	885	895	697
55°	567	555	550	570	572	511
65°	328	308	281	266	276	328
75°	145	123	76	62	62	157
85°	17	10	2	2	2	27
90°	0	0	0	0	0	



TEST NUMBER: P592777

CATALOG NUMBER: HCC4S35D010SL-HM43040850-41RWWC

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	1824.7	1824.7	1824.7	1824.7	1824.7	1824.7	1824.7	1824.7	1824.7
2.5°	1851.8	1847.0	1839.5	1829.6	1819.8	1812.3	1810.0	1807.5	1807.5
5°	1891.4	1881.5	1866.6	1847.0	1834.6	1827.2	1819.8	1814.8	1814.8
7.5°	1918.4	1908.6	1886.4	1859.2	1842.0	1827.2	1817.3	1810.0	1810.0
10°	1930.8	1918.4	1891.4	1856.7	1829.6	1810.0	1795.1	1790.2	1790.2
12.5°	1945.5	1930.8	1893.7	1849.4	1814.8	1790.2	1775.4	1770.5	1770.5
15°	1960.4	1943.1	1896.2	1844.5	1800.1	1770.5	1758.2	1755.7	1755.7
17.5°	1953.0	1930.8	1876.5	1814.8	1765.6	1735.9	1723.7	1723.7	1726.1
20°	1913.5	1891.4	1829.6	1760.6	1708.8	1686.7	1676.8	1681.7	1686.7
22.5°	1854.3	1827.2	1760.6	1694.0	1639.8	1620.0	1620.0	1627.4	1634.9
25°	1780.3	1755.7	1691.6	1617.5	1565.8	1551.0	1556.0	1568.3	1578.1
27.5°	1696.5	1669.4	1602.8	1533.7	1482.0	1474.6	1486.9	1504.1	1509.1
30°	1583.0	1560.9	1504.1	1437.6	1393.2	1390.7	1408.0	1420.3	1432.7
32.5°	1474.6	1450.0	1395.7	1331.6	1299.5	1301.9	1321.7	1336.4	1343.9
35°	1348.8	1326.7	1287.2	1235.4	1205.8	1210.8	1232.9	1247.8	1250.2
37.5°	1230.4	1215.6	1176.2	1136.7	1114.6	1124.4	1144.1	1161.4	1161.4
40°	1112.1	1099.7	1070.2	1038.1	1025.8	1038.1	1057.8	1072.6	1072.6
42.5°	998.7	991.3	966.6	944.4	937.0	954.3	971.6	983.8	981.4
45°	897.5	890.2	872.9	855.7	853.2	870.4	885.3	892.7	895.2
47.5°	806.4	801.4	786.6	774.3	774.3	791.5	803.9	811.3	813.8
50°	722.5	717.6	705.2	695.4	697.8	715.1	725.0	732.4	734.9
52.5°	638.7	636.2	626.3	614.0	621.3	633.7	646.1	651.0	653.5
55°	567.2	567.2	554.8	544.9	549.9	562.2	569.6	572.1	572.1
57.5°	503.0	500.5	485.8	475.9	478.4	490.7	495.7	498.0	498.0
60°	441.4	438.9	424.1	409.4	409.4	416.8	419.1	421.6	421.6
62.5°	382.2	379.7	362.5	350.1	345.2	342.7	342.7	347.7	357.5
65°	328.0	325.5	308.2	288.5	281.1	273.7	266.3	271.2	276.2
67.5°	278.6	273.7	256.5	239.2	221.9	209.6	197.3	204.7	214.6
70°	231.8	226.8	207.2	187.4	167.7	147.9	138.1	147.9	152.9
72.5°	187.4	182.4	162.8	143.0	118.4	98.7	96.2	98.7	101.0
75°	145.4	143.0	123.3	101.0	76.4	61.6	61.6	61.6	61.6
77.5°	108.5	103.5	83.9	64.1	44.4	34.5	32.0	32.0	32.0
80°	74.0	69.0	51.8	37.0	19.8	14.8	14.8	12.4	12.4
82.5°	41.9	39.5	27.1	14.8	7.4	4.9	4.9	4.9	4.9
85°	17.3	14.8	9.9	4.9	2.5	2.5	2.5	2.5	2.5
87.5°	2.5	2.5	2.5	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)