

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580504

Luminaire Tested: **HCC4W35D010SL-HM43040930-41WWBB**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580504
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-17)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W35D010SL-HM43040930-41WWBB
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2445.7 lumens
Efficiency: N/A
Efficacy: 72.6 lumens/watt
Spacing Criteria (0/90/45): 1.11 / 1.04 / 1.12
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 33.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580504
CATALOG NUMBER: HCC4W35D010SL-HM43040930-41WWBB

Luminous Intensity Polar Plot





TEST NUMBER: P580504

CATALOG NUMBER: HCC4W35D010SL-HM43040930-41WWBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	104	101	109	105	102	100	101	99	97	97	95	94	94	92	91	89			89
2	103	97	91	87	101	95	90	86	92	87	84	88	85	82	85	83	80	78			78
3	96	87	80	75	94	86	79	74	83	78	73	80	76	72	78	74	71	69			69
4	89	79	72	66	87	78	71	65	75	69	65	73	68	64	71	67	63	61			61
5	83	72	64	58	81	71	64	58	69	62	58	67	61	57	65	60	56	55			55
6	77	66	58	52	75	65	57	52	63	57	52	61	56	51	60	55	51	49			49
7	72	60	53	47	71	59	52	47	58	51	47	57	51	46	55	50	46	44			44
8	68	56	48	43	66	55	48	43	54	47	42	53	47	42	51	46	42	40			40
9	64	52	44	39	62	51	44	39	50	43	39	49	43	39	48	43	39	37			37
10	60	48	41	36	59	47	41	36	46	40	36	46	40	36	45	39	36	34			34

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	174645	174645	174645
5°	185044	174062	165333
10°	192732	171290	155646
15°	200101	167168	146341
20°	201985	159155	135357
25°	195435	147189	123889
30°	182720	133383	112731
35°	162849	118580	101293
40°	142354	103131	90153
45°	124007	87480	77991
50°	108208	74205	66855
55°	94857	61482	54149
60°	82962	49684	39767
65°	72294	37037	22327
70°	63184	23946	7249
75°	51851	12486	1906
80°	38641	5754	1421
85°	22785	2830	2830



TEST NUMBER: P580504
 CATALOG NUMBER: HCC4W35D010SL-HM43040930-41WWBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	133.6	5.5
10°-20°	374.0	15.3
20°-30°	517.1	21.1
30°-40°	520.0	21.3
40°-50°	419.6	17.2
50°-60°	283.7	11.6
60°-70°	144.4	5.9
70°-80°	46.2	1.9
80°-90°	7.1	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1024.7	41.9
0°-40°	1544.7	63.2
0°-60°	2248.0	91.9
0°-90°	2445.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2445.7	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1416	1416	1416	1416	1416	
5°	1494	1466	1406	1355	1335	144
15°	1567	1482	1309	1184	1146	441
25°	1436	1311	1082	949	910	657
35°	1082	977	788	689	673	676
45°	711	636	502	447	447	551
55°	441	381	286	250	252	396
65°	248	201	127	83	76	248
75°	109	76	26	6	4	117
85°	16	8	2	2	2	22
90°	0	0	0	0	0	



TEST NUMBER: P580504

CATALOG NUMBER: HCC4W35D010SL-HM43040930-41WWBB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9
2.5°	1454.1	1446.1	1438.0	1424.0	1407.8	1391.7	1381.6	1373.6	1369.6
5°	1494.5	1484.4	1466.3	1436.0	1405.8	1377.7	1355.4	1341.4	1335.3
7.5°	1526.7	1512.6	1482.3	1440.1	1393.8	1349.5	1321.3	1301.1	1293.0
10°	1538.8	1522.7	1482.3	1426.0	1367.6	1313.2	1272.9	1252.8	1242.7
12.5°	1552.8	1534.7	1484.4	1413.9	1341.4	1277.0	1230.6	1204.5	1194.4
15°	1567.0	1542.8	1482.3	1395.8	1309.1	1234.6	1184.2	1158.1	1146.0
17.5°	1567.0	1538.8	1466.3	1365.5	1266.9	1188.3	1131.9	1101.7	1091.6
20°	1538.8	1506.5	1428.0	1317.2	1212.5	1127.9	1073.5	1043.3	1031.2
22.5°	1494.5	1458.2	1373.6	1258.8	1148.1	1065.4	1011.0	982.8	970.8
25°	1436.0	1399.8	1311.1	1192.3	1081.5	999.0	948.7	922.5	910.3
27.5°	1367.6	1327.3	1238.6	1119.8	1011.0	932.5	886.2	862.0	852.0
30°	1282.9	1244.7	1158.1	1041.3	936.5	864.0	821.8	799.6	791.5
32.5°	1184.2	1152.1	1067.5	958.7	860.0	793.5	755.3	737.1	729.1
35°	1081.5	1051.4	976.9	876.2	787.5	725.1	688.8	676.8	672.7
37.5°	984.8	958.7	886.2	793.5	713.0	658.6	626.4	618.3	614.3
40°	884.1	866.0	799.6	715.0	640.5	592.1	565.9	559.9	559.9
42.5°	793.5	773.4	715.0	638.4	572.0	523.7	505.6	499.5	501.5
45°	710.9	690.8	636.4	565.9	501.5	461.2	447.1	447.1	447.1
47.5°	634.4	616.3	565.9	493.4	441.1	408.9	394.7	394.7	396.8
50°	563.9	551.9	495.5	433.1	386.7	356.5	346.4	344.4	348.4
52.5°	497.5	483.4	433.1	376.7	332.4	308.2	298.1	296.1	298.1
55°	441.1	425.0	380.7	326.3	285.9	261.8	249.8	247.7	251.8
57.5°	386.7	374.6	328.3	280.0	241.7	217.5	207.5	203.4	205.5
60°	336.3	324.3	282.0	235.7	201.4	177.3	163.1	159.2	161.2
62.5°	290.0	280.0	239.6	195.4	161.2	138.9	124.9	114.8	118.8
65°	247.7	237.6	201.4	157.1	126.9	102.7	82.6	74.5	76.5
67.5°	211.4	199.4	165.1	124.9	94.6	68.5	46.3	42.3	42.3
70°	175.2	163.1	133.0	96.7	66.4	36.3	20.1	20.1	20.1
72.5°	140.9	130.9	102.7	72.5	42.3	16.1	8.1	8.1	8.1
75°	108.8	100.7	76.5	50.4	26.2	8.1	6.1	4.0	4.0
77.5°	80.6	72.5	54.4	34.3	16.1	4.0	4.0	4.0	4.0
80°	54.4	48.3	36.3	20.1	8.1	2.0	2.0	2.0	2.0
82.5°	32.3	28.2	20.1	10.1	4.0	2.0	2.0	2.0	2.0
85°	16.1	12.1	8.1	4.0	2.0	2.0	2.0	2.0	2.0
87.5°	4.0	2.0	2.0	2.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)