

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580474

Luminaire Tested: **HCC4W35D010MB-HM43040927-41NDH**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P580474  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-2)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC4W35D010MB-HM43040927-41NDH  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" NARROW DISTRIBUTION, HAZE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2605.4 lumens  
Efficiency: N/A  
Efficacy: 77.3 lumens/watt  
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.91  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 33.7  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P580474  
CATALOG NUMBER: HCC4W35D010MB-HM43040927-41NDH

### Luminous Intensity Polar Plot





TEST NUMBER: P580474  
 CATALOG NUMBER: HCC4W35D010MB-HM43040927-41NDH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20									20
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	99	97	97	96	95	93	93	93	93	93																
	1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93	93	93	93	93	93	93	93	93	93	93	93																
	2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	86	86	85	82	86	83	81	86	83	81	86																	
	3	101	95	89	85	99	93	88	84	91	86	83	88	85	82	86	83	81	79	79	79	77	73	70	76	72	69	67	67																	
	4	96	88	82	78	94	87	81	77	85	80	76	82	79	75	81	77	74	73	73	73	73	73	73	73	73	73	73	73	73																
	5	91	82	76	71	89	81	75	71	79	74	70	77	73	70	76	72	69	67	67	67	67	67	67	67	67	67	67	67	67																
	6	86	76	70	66	84	76	70	65	74	69	65	73	68	64	71	67	64	63	63	63	63	63	63	63	63	63	63	63	63																
	7	81	72	65	61	80	71	65	61	70	64	60	68	64	60	67	63	60	58	58	58	58	58	58	58	58	58	58	58	58																
	8	77	67	61	57	76	67	61	56	65	60	56	64	59	56	63	59	56	54	54	54	54	54	54	54	54	54	54	54	54																
	9	73	63	57	53	72	63	57	53	62	56	52	61	56	52	60	55	52	51	51	51	51	51	51	51	51	51	51	51	51																
	10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48	48	48	48	48	48	48	48	48	48	48	48																

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	337918
5°	331779
10°	314699
15°	294252
20°	267249
25°	236482
30°	196706
35°	141844
40°	88543
45°	51058
50°	28822
55°	13720
60°	7869
65°	6042
70°	4039
75°	2669
80°	2628
85°	2689



TEST NUMBER: P580474  
 CATALOG NUMBER: HCC4W35D010MB-HM43040927-41NDH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	250.5	9.6
10°-20°	642.8	24.7
20°-30°	790.6	30.3
30°-40°	587.2	22.5
40°-50°	238.7	9.2
50°-60°	66.1	2.5
60°-70°	20.6	0.8
70°-80°	6.9	0.3
80°-90°	2.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1683.9	64.6
0°-40°	2271.1	87.2
0°-60°	2575.9	98.9
0°-90°	2605.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2605.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2740	
5°	2680	250
15°	2304	643
25°	1738	791
35°	942	587
45°	293	239
55°	64	66
65°	21	21
75°	6	7
85°	2	2
90°	0	



TEST NUMBER: P580474  
CATALOG NUMBER: HCC4W35D010MB-HM43040927-41NDH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2739.6
2.5°	2713.4
5°	2679.6
7.5°	2612.1
10°	2512.6
12.5°	2409.4
15°	2304.3
17.5°	2178.6
20°	2036.0
22.5°	1891.5
25°	1737.6
27.5°	1570.7
30°	1381.1
32.5°	1165.3
35°	942.0
37.5°	731.8
40°	549.9
42.5°	401.6
45°	292.7
47.5°	210.2
50°	150.2
52.5°	103.2
55°	63.8
57.5°	41.3
60°	31.9
62.5°	26.3
65°	20.7
67.5°	15.1
70°	11.2
72.5°	9.3
75°	5.6
77.5°	3.7
80°	3.7
82.5°	1.9
85°	1.9
87.5°	1.9
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)