

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580515

Luminaire Tested: **HCC4S35D010MW-HM43040935-41WDC**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P580515  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-7)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC4S35D010MW-HM43040935-41WDC  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, SPECULAR TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3565.8 lumens  
Efficiency: N/A  
Efficacy: 105.8 lumens/watt  
Spacing Criteria (0/90/45): 1.25 / 1.25 / 1.11  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 33.7  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P580515  
CATALOG NUMBER: HCC4S35D010MW-HM43040935-41WDC

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P580515

CATALOG NUMBER: HCC4S35D010MW-HM43040935-41WDC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20																	
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																											
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	97	95	94	92																											
2	107	101	97	93	104	100	96	92	96	93	90	93	91	88	91	88	86	85																											
3	101	93	88	84	98	92	87	83	89	85	82	87	83	80	85	82	79	77																											
4	95	86	80	76	93	85	79	75	83	78	74	81	77	73	79	75	72	71																											
5	89	80	73	69	87	79	73	68	77	72	68	75	71	67	74	70	66	65																											
6	84	74	67	63	82	73	67	62	72	66	62	70	65	62	69	65	61	60																											
7	79	69	62	57	78	68	62	57	67	61	57	65	60	57	64	60	56	55																											
8	75	64	57	53	73	63	57	53	62	57	53	61	56	52	60	56	52	51																											
9	70	60	53	49	69	59	53	49	58	53	49	57	52	48	56	52	48	47																											
10	67	56	50	45	66	55	49	45	55	49	45	54	49	45	53	48	45	43																											

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	288061
5°	292282
10°	301448
15°	322115
20°	341320
25°	337575
30°	302986
35°	235819
40°	159760
45°	99743
50°	43156
55°	14451
60°	3626
65°	2452
70°	1515
75°	1001
80°	1492
85°	0



TEST NUMBER: P580515  
 CATALOG NUMBER: HCC4S35D010MW-HM43040935-41WDC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	226.7	6.4
10°-20°	716.1	20.1
20°-30°	1121.9	31.5
30°-40°	968.3	27.2
40°-50°	445.3	12.5
50°-60°	75.6	2.1
60°-70°	8.6	0.2
70°-80°	3.0	0.1
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2064.8	57.9
0°-40°	3033.1	85.1
0°-60°	3553.9	99.7
0°-90°	3565.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3565.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2335	
5°	2361	227
15°	2522	716
25°	2480	1122
35°	1566	968
45°	572	445
55°	67	76
65°	8	9
75°	2	3
85°	0	0
90°	0	



TEST NUMBER: P580515  
CATALOG NUMBER: HCC4S35D010MW-HM43040935-41WDC

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2335.4
2.5°	2335.4
5°	2360.6
7.5°	2383.8
10°	2406.8
12.5°	2455.3
15°	2522.5
17.5°	2579.2
20°	2600.3
22.5°	2568.7
25°	2480.4
27.5°	2337.5
30°	2127.3
32.5°	1862.5
35°	1566.1
37.5°	1267.5
40°	992.2
42.5°	758.8
45°	571.8
47.5°	401.5
50°	224.9
52.5°	124.0
55°	67.2
57.5°	33.6
60°	14.7
62.5°	10.6
65°	8.4
67.5°	6.3
70°	4.2
72.5°	4.2
75°	2.1
77.5°	2.1
80°	2.1
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)