

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580520

Luminaire Tested: **HCC4W35D010MB-HM43040935-41RWWC**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580520
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-14)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W35D010MB-HM43040935-41RWWC
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3240.1 lumens
Efficiency: N/A
Efficacy: 96.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.15 / 1.21
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 33.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580520
CATALOG NUMBER: HCC4W35D010MB-HM43040935-41RWWC

Luminous Intensity Polar Plot





TEST NUMBER: P580520

CATALOG NUMBER: HCC4W35D010MB-HM43040935-41RWWC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	103	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88								
2	102	95	90	85	100	94	88	84	90	86	82	87	83	80	84	81	78	76								
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67								
4	87	77	69	63	85	76	68	63	73	67	62	71	66	61	69	64	60	58								
5	81	70	61	56	79	68	61	55	66	60	55	65	59	54	63	58	54	52								
6	75	63	55	49	74	62	55	49	61	54	49	59	53	48	58	52	48	46								
7	70	58	50	44	69	57	49	44	56	49	44	54	48	44	53	47	43	41								
8	66	53	45	40	64	53	45	40	51	44	40	50	44	39	49	43	39	37								
9	62	49	42	36	60	49	41	36	47	41	36	46	40	36	45	40	36	34								
10	58	46	38	33	57	45	38	33	44	38	33	43	37	33	42	37	33	31								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	191778	191778	191778
5°	199543	193563	191483
10°	206059	195275	191066
15°	213317	195874	191034
20°	214022	191130	188662
25°	206473	181594	183023
30°	192120	169090	173875
35°	173073	154703	160410
40°	152579	140744	147169
45°	133427	126816	133043
50°	118129	114099	120163
55°	103932	100771	104835
60°	92781	86046	88636
65°	81546	69901	68704
70°	71226	51535	46991
75°	59095	31072	25020
80°	44821	12004	7458
85°	20804	2972	2972



TEST NUMBER: P580520
 CATALOG NUMBER: HCC4W35D010MB-HM43040935-41RWWC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	150.0	4.6
10°-20°	437.7	13.5
20°-30°	633.8	19.6
30°-40°	668.7	20.6
40°-50°	578.7	17.9
50°-60°	428.7	13.2
60°-70°	247.1	7.6
70°-80°	86.3	2.7
80°-90°	9.1	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1221.5	37.7
0°-40°	1890.2	58.3
0°-60°	2897.6	89.4
0°-90°	3240.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3240.1	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1555	1555	1555	1555	1555	
5°	1612	1591	1563	1551	1546	155
15°	1670	1616	1534	1498	1496	470
25°	1517	1441	1334	1326	1345	694
35°	1149	1097	1027	1051	1065	718
45°	765	744	727	754	763	594
55°	483	473	469	485	488	436
65°	279	263	240	227	235	279
75°	124	105	65	52	52	133
85°	15	8	2	2	2	23
90°	0	0	0	0	0	



TEST NUMBER: P580520

CATALOG NUMBER: HCC4W35D010MB-HM43040935-41RWWC

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	1554.8	1554.8	1554.8	1554.8	1554.8	1554.8	1554.8	1554.8	1554.8
2.5°	1578.0	1573.8	1567.5	1559.1	1550.7	1544.4	1542.2	1540.2	1540.2
5°	1611.6	1603.2	1590.6	1573.8	1563.3	1557.0	1550.7	1546.5	1546.5
7.5°	1634.7	1626.3	1607.4	1584.3	1569.6	1557.0	1548.5	1542.2	1542.2
10°	1645.2	1634.7	1611.6	1582.3	1559.1	1542.2	1529.7	1525.5	1525.5
12.5°	1657.8	1645.2	1613.7	1575.8	1546.5	1525.5	1512.9	1508.6	1508.6
15°	1670.5	1655.8	1615.9	1571.7	1533.9	1508.6	1498.2	1496.0	1496.0
17.5°	1664.2	1645.2	1599.0	1546.5	1504.5	1479.3	1468.7	1468.7	1470.9
20°	1630.5	1611.6	1559.1	1500.2	1456.1	1437.3	1428.8	1433.0	1437.3
22.5°	1580.1	1557.0	1500.2	1443.6	1397.2	1380.5	1380.5	1386.8	1393.1
25°	1517.1	1496.0	1441.4	1378.4	1334.3	1321.6	1325.9	1336.3	1344.8
27.5°	1445.6	1422.5	1365.8	1307.0	1262.8	1256.5	1267.0	1281.7	1286.0
30°	1348.9	1330.0	1281.7	1225.0	1187.2	1185.0	1199.8	1210.3	1220.8
32.5°	1256.5	1235.5	1189.3	1134.7	1107.4	1109.4	1126.2	1138.8	1145.1
35°	1149.4	1130.4	1096.8	1052.7	1027.4	1031.7	1050.6	1063.2	1065.3
37.5°	1048.5	1035.9	1002.3	968.7	949.8	958.1	975.0	989.7	989.7
40°	947.6	937.1	911.9	884.6	874.1	884.6	901.4	914.0	914.0
42.5°	851.0	844.7	823.7	804.8	798.5	813.2	827.8	838.4	836.3
45°	764.9	758.5	743.9	729.1	727.0	741.7	754.3	760.6	762.7
47.5°	687.1	682.9	670.2	659.8	659.8	674.5	685.0	691.3	693.4
50°	615.6	611.5	600.9	592.6	594.6	609.3	617.8	624.0	626.2
52.5°	544.2	542.1	533.7	523.2	529.5	540.0	550.5	554.7	556.8
55°	483.3	483.3	472.8	464.3	468.6	479.0	485.3	487.5	487.5
57.5°	428.7	426.6	414.0	405.5	407.7	418.1	422.3	424.4	424.4
60°	376.1	374.1	361.4	348.8	348.8	355.1	357.2	359.3	359.3
62.5°	325.7	323.6	308.9	298.4	294.2	292.0	292.0	296.3	304.7
65°	279.4	277.4	262.7	245.8	239.5	233.2	226.9	231.1	235.4
67.5°	237.4	233.2	218.5	203.8	189.1	178.6	168.2	174.4	182.8
70°	197.5	193.3	176.5	159.7	142.9	126.1	117.7	126.1	130.3
72.5°	159.7	155.4	138.7	121.8	100.8	84.1	81.9	84.1	86.1
75°	124.0	121.8	105.1	86.1	65.2	52.5	52.5	52.5	52.5
77.5°	92.5	88.2	71.5	54.6	37.8	29.4	27.3	27.3	27.3
80°	63.1	58.8	44.2	31.5	16.9	12.6	12.6	10.5	10.5
82.5°	35.7	33.6	23.2	12.6	6.3	4.2	4.2	4.2	4.2
85°	14.7	12.6	8.4	4.2	2.1	2.1	2.1	2.1	2.1
87.5°	2.1	2.1	2.1	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)