

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580558

Luminaire Tested: **HCC4S40D010MW-HM43040827-41WWBB**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580558
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-17)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4S40D010MW-HM43040827-41WWBB
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3050.2 lumens
Efficiency: N/A
Efficacy: 74.4 lumens/watt
Spacing Criteria (0/90/45): 1.11 / 1.04 / 1.12
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 41
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580558
CATALOG NUMBER: HCC4S40D010MW-HM43040827-41WWBB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P580558

CATALOG NUMBER: HCC4S40D010MW-HM43040827-41WWBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20				
RC	80					70					50					30				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	108	104	101	109	105	102	100	101	99	97	97	95	94	94	92	91	89		
2	103	97	91	87	101	95	90	86	92	87	84	88	85	82	85	83	80	78		
3	96	87	80	75	94	86	79	74	83	78	73	80	76	72	78	74	71	69		
4	89	79	72	66	87	78	71	65	75	69	65	73	68	64	71	67	63	61		
5	83	72	64	58	81	71	64	58	69	62	58	67	61	57	65	60	56	55		
6	77	66	58	52	75	65	57	52	63	57	52	61	56	51	60	55	51	49		
7	72	60	53	47	71	59	52	47	58	51	47	57	51	46	55	50	46	44		
8	68	56	48	43	66	55	48	43	54	47	42	53	47	42	51	46	42	40		
9	64	52	44	39	62	51	44	39	50	43	39	49	43	39	48	43	39	37		
10	60	48	41	36	59	47	41	36	46	40	36	46	40	36	45	39	36	34		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	217816	217816	217816
5°	230782	217100	206204
10°	240377	213624	194123
15°	249545	208491	182517
20°	251917	198481	168816
25°	243749	183581	154511
30°	227898	166369	140604
35°	203114	147882	126334
40°	177553	128620	112438
45°	154673	109110	97284
50°	134957	92549	83396
55°	118297	76707	67525
60°	103487	61969	49585
65°	90156	46202	27844
70°	78800	29861	9052
75°	64623	15536	2383
80°	48160	7174	1776
85°	28446	3538	3538



TEST NUMBER: P580558

CATALOG NUMBER: HCC4S40D010MW-HM43040827-41WWBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	166.7	5.5
10°-20°	466.4	15.3
20°-30°	644.9	21.1
30°-40°	648.5	21.3
40°-50°	523.3	17.2
50°-60°	353.8	11.6
60°-70°	180.1	5.9
70°-80°	57.7	1.9
80°-90°	8.8	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1278.0	41.9
0°-40°	1926.5	63.2
0°-60°	2803.6	91.9
0°-90°	3050.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3050.2	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1766	1766	1766	1766	1766	
5°	1864	1829	1753	1690	1665	180
15°	1954	1849	1633	1477	1429	550
25°	1791	1635	1349	1183	1135	820
35°	1349	1218	982	859	839	843
45°	887	794	626	558	558	687
55°	550	475	357	312	314	494
65°	309	251	158	103	95	310
75°	136	95	33	8	5	146
85°	20	10	2	2	2	27
90°	0	0	0	0	0	



TEST NUMBER: P580558

CATALOG NUMBER: HCC4S40D010MW-HM43040827-41WWBB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	1765.9	1765.9	1765.9	1765.9	1765.9	1765.9	1765.9	1765.9	1765.9
2.5°	1813.6	1803.6	1793.5	1775.9	1755.8	1735.8	1723.2	1713.1	1708.1
5°	1863.9	1851.3	1828.7	1791.0	1753.4	1718.2	1690.5	1673.0	1665.4
7.5°	1904.0	1886.4	1848.8	1796.1	1738.2	1683.0	1647.8	1622.6	1612.7
10°	1919.2	1899.0	1848.8	1778.5	1705.6	1637.8	1587.6	1562.4	1549.9
12.5°	1936.6	1914.1	1851.3	1763.3	1673.0	1592.6	1534.8	1502.1	1489.6
15°	1954.2	1924.1	1848.8	1740.8	1632.7	1539.8	1477.0	1444.3	1429.3
17.5°	1954.2	1919.2	1828.7	1703.0	1579.9	1482.1	1411.7	1374.0	1361.5
20°	1919.2	1878.9	1780.9	1642.8	1512.1	1406.6	1338.8	1301.1	1286.1
22.5°	1863.9	1818.6	1713.1	1570.0	1431.7	1328.8	1261.0	1225.8	1210.8
25°	1791.0	1745.7	1635.2	1487.0	1348.9	1245.9	1183.1	1150.5	1135.3
27.5°	1705.6	1655.4	1544.9	1396.7	1261.0	1163.0	1105.2	1075.2	1062.5
30°	1600.1	1552.4	1444.3	1298.7	1168.1	1077.6	1024.8	997.2	987.2
32.5°	1477.0	1436.8	1331.3	1195.7	1072.6	989.7	942.0	919.3	909.4
35°	1348.9	1311.2	1218.3	1092.6	982.1	904.3	859.0	844.0	839.0
37.5°	1228.3	1195.7	1105.2	989.7	889.2	821.4	781.2	771.1	766.1
40°	1102.7	1080.1	997.2	891.8	798.8	738.5	705.9	698.3	698.3
42.5°	989.7	964.6	891.8	796.2	713.4	653.1	630.5	622.9	625.5
45°	886.7	861.6	793.8	705.9	625.5	575.2	557.7	557.7	557.7
47.5°	791.2	768.7	705.9	615.4	550.1	509.9	492.3	492.3	494.8
50°	703.3	688.3	617.9	540.1	482.3	444.6	432.0	429.6	434.6
52.5°	620.5	602.9	540.1	469.7	414.4	384.3	371.7	369.3	371.7
55°	550.1	530.0	474.7	406.9	356.7	326.5	311.5	308.9	314.0
57.5°	482.3	467.2	409.4	349.2	301.4	271.3	258.7	253.7	256.3
60°	419.5	404.5	351.7	293.9	251.2	221.1	203.5	198.4	201.0
62.5°	361.7	349.2	299.0	243.7	201.0	173.3	155.7	143.2	148.2
65°	308.9	296.4	251.2	196.0	158.3	128.1	103.0	92.9	95.4
67.5°	263.8	248.6	205.9	155.7	118.0	85.4	57.7	52.8	52.8
70°	218.5	203.5	165.8	120.6	82.8	45.2	25.1	25.1	25.1
72.5°	175.9	163.3	128.1	90.5	52.8	20.1	10.1	10.1	10.1
75°	135.6	125.6	95.4	62.8	32.6	10.1	7.5	5.0	5.0
77.5°	100.4	90.5	67.8	42.7	20.1	5.0	5.0	5.0	5.0
80°	67.8	60.3	45.2	25.1	10.1	2.5	2.5	2.5	2.5
82.5°	40.2	35.2	25.1	12.6	5.0	2.5	2.5	2.5	2.5
85°	20.1	15.0	10.1	5.0	2.5	2.5	2.5	2.5	2.5
87.5°	5.0	2.5	2.5	2.5	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)