

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580557

Luminaire Tested: **HCC4W40D010MW-HM43040827-41RWWH**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580557
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-15)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W40D010MW-HM43040827-41RWWH
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3854.2 lumens
Efficiency: N/A
Efficacy: 94.0 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.08 / 1.16
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 41
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580557
CATALOG NUMBER: HCC4W40D010MW-HM43040827-41RWWH

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P580557

CATALOG NUMBER: HCC4W40D010MW-HM43040827-41RWWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	104	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88																			
2	103	96	90	85	100	94	89	84	90	86	82	87	84	80	84	81	79	77																			
3	95	86	79	73	92	84	78	73	81	76	71	79	74	70	76	72	69	67																			
4	88	77	70	64	86	76	69	63	74	67	62	71	66	62	69	65	61	59																			
5	81	70	62	56	79	69	61	56	67	60	55	65	59	55	63	58	54	52																			
6	76	64	56	50	74	63	55	50	61	54	49	60	54	49	58	53	49	47																			
7	71	58	51	45	69	58	50	45	56	49	45	55	49	44	54	48	44	42																			
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38																			
9	62	50	42	37	61	49	42	37	48	41	37	47	41	37	46	41	37	35																			
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32																			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	249430	249430	249430
5°	255966	249429	244773
10°	261769	247291	237534
15°	269134	243786	231272
20°	268391	234433	221911
25°	257087	219483	211277
30°	236486	202147	199996
35°	208037	183448	184969
40°	180000	164221	171096
45°	156435	145917	154673
50°	138834	128702	137375
55°	123157	112899	117759
60°	109679	97912	97912
65°	97511	81371	76234
70°	84245	61597	54348
75°	70628	40699	33503
80°	53487	19605	17829
85°	28446	7076	7076



TEST NUMBER: P580557
 CATALOG NUMBER: HCC4W40D010MW-HM43040827-41RWWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	191.5	5.0
10°-20°	542.9	14.1
20°-30°	765.6	19.9
30°-40°	791.0	20.5
40°-50°	670.5	17.4
50°-60°	487.8	12.7
60°-70°	285.0	7.4
70°-80°	105.9	2.7
80°-90°	13.9	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1500.1	38.9
0°-40°	2291.0	59.4
0°-60°	3449.4	89.5
0°-90°	3854.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3854.2	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2022	2022	2022	2022	2022	
5°	2067	2050	2014	1984	1977	198
15°	2108	2042	1909	1829	1811	592
25°	1889	1784	1613	1555	1552	864
35°	1382	1321	1218	1221	1228	863
45°	897	872	836	867	887	698
55°	573	545	525	543	548	515
65°	334	306	279	261	261	332
75°	148	123	85	68	70	159
85°	20	13	5	5	5	28
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P580557

CATALOG NUMBER: HCC4W40D010MW-HM43040827-41RWWH

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	2022.2	2022.2	2022.2	2022.2	2022.2	2022.2	2022.2	2022.2	2022.2
2.5°	2039.7	2034.7	2029.7	2022.2	2012.1	2004.6	1997.1	1992.0	1992.0
5°	2067.3	2059.8	2049.7	2032.1	2014.5	1999.5	1984.5	1976.9	1976.9
7.5°	2087.4	2077.4	2057.3	2032.1	2002.0	1979.5	1956.8	1946.7	1941.8
10°	2090.0	2079.9	2052.3	2014.5	1974.4	1939.2	1914.1	1899.1	1896.5
12.5°	2094.9	2082.4	2047.3	1994.5	1941.8	1899.1	1871.4	1856.4	1851.3
15°	2107.6	2090.0	2042.2	1974.4	1909.1	1858.8	1828.7	1816.1	1811.1
17.5°	2094.9	2069.8	2012.1	1931.7	1858.8	1803.6	1773.4	1760.9	1760.9
20°	2044.7	2019.6	1951.8	1863.9	1786.0	1733.3	1703.1	1695.6	1690.6
22.5°	1974.4	1946.7	1874.0	1780.9	1703.1	1655.4	1635.3	1625.2	1622.8
25°	1889.0	1861.3	1783.5	1688.0	1612.7	1572.5	1554.9	1554.9	1552.4
27.5°	1793.5	1758.4	1678.0	1595.1	1522.2	1492.1	1484.5	1484.5	1487.1
30°	1660.4	1635.3	1567.5	1487.1	1419.3	1399.1	1399.1	1404.2	1404.2
32.5°	1517.3	1499.7	1439.4	1369.0	1316.3	1303.7	1308.8	1318.7	1321.3
35°	1381.6	1361.5	1321.3	1258.5	1218.3	1213.3	1220.8	1228.4	1228.4
37.5°	1248.5	1228.4	1200.7	1150.5	1120.3	1122.8	1132.9	1143.0	1150.5
40°	1117.9	1102.7	1082.7	1042.4	1019.9	1029.9	1042.4	1052.5	1062.6
42.5°	1002.3	987.2	972.1	942.0	927.0	939.5	954.5	964.6	974.6
45°	896.8	886.7	871.7	846.6	836.5	849.0	866.6	876.6	886.7
47.5°	806.3	801.3	781.2	758.6	753.5	766.2	781.2	793.8	801.3
50°	723.5	715.9	698.3	675.7	670.7	690.8	700.8	708.4	715.9
52.5°	643.1	635.5	615.4	595.4	595.4	610.4	617.9	620.5	628.0
55°	572.7	565.2	545.1	530.0	525.0	537.5	542.6	542.6	547.6
57.5°	507.4	499.9	479.8	462.2	459.7	467.2	467.2	467.2	469.7
60°	444.6	437.1	417.0	401.9	396.9	399.4	396.9	394.4	396.9
62.5°	386.9	379.3	359.2	341.7	336.6	336.6	329.0	326.5	329.0
65°	334.1	321.5	306.5	288.9	278.8	271.3	261.2	261.2	261.2
67.5°	281.4	271.3	253.7	236.1	223.5	211.0	196.0	201.0	203.5
70°	233.6	226.1	205.9	188.4	170.8	155.7	143.2	148.2	150.7
72.5°	190.9	180.8	163.3	143.2	128.1	108.1	100.4	105.5	105.5
75°	148.2	138.1	123.1	103.0	85.4	67.8	67.8	70.3	70.3
77.5°	110.5	100.4	85.4	67.8	52.8	40.2	42.7	42.7	42.7
80°	75.3	67.8	55.3	40.2	27.6	22.6	22.6	22.6	25.1
82.5°	42.7	37.7	30.2	20.1	12.6	12.6	12.6	12.6	12.6
85°	20.1	15.0	12.6	7.5	5.0	5.0	5.0	5.0	5.0
87.5°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)